

Open Carrier Double-Balanced Mixer For Microwave Telecommunications

MC2413
V2


Features

- LO 4.5 TO 7.0 GHz
- RF 4.5 TO 7.0 GHz
- IF DC TO 2.0 GHz
- LO DRIVE +13 dBm (NOMINAL)
- MICROSTRIP INTERFACE

Description

The MC2413 is a double balanced mixer, designed for use in military, commercial and test equipment applications. The design utilizes Schottky ring quad diodes and broadband soft dielectric and ferrite baluns to attain excellent performance. This mixer can also be used as a phase detector and/or bi-phase modulator since the IF port is DC coupled to the diodes. The use of high temperature solder and welded assembly processes used internally makes it ideal for use in manual, semi-automated assembly. Environmental screening available to MIL-STD-883, MIL-STD-202, or MIL-DTL-28837, consult factory.

Product Image



Ordering Information

Part Number	Package
MC2413	Open Carrier
MC2413-2	Open Carrier







Electrical Specifications: $Z_0 = 50\Omega$ $Lo = +13$ dBm (Downconverter application only)

Parameter	Test Conditions	Units	Typical	Guaranteed	
				+25°C	-54° to +85°C
SSB Conversion Loss (max) & SSB Noise Figure (max)	$f_R = 4.5$ to 7 GHz, $f_L = 4.5$ to 7 GHz, $f_I = 0.01$ to 1 GHz	dB	5.2	6.5	7.0
	$f_R = 4.5$ to 7 GHz, $f_L = 4.5$ to 7 GHz, $f_I = 0.01$ to 2 GHz	dB	5.5	7.0	7.5
Isolation, L to R (min)	$f_L = 4.5$ to 7 GHz	dB	27	20	18
Isolation, L to I (min)	$f_L = 4.5$ to 7 GHz	dB	40	25	23
Isolation, R to I (min)	$f_L = 4.5$ to 7 GHz	dB	20	10	8
1 dB Conversion Comp.	$f_L = +13$ dBm	dBm	+6		
Input IP3	$f_{R1} = 6$ GHz at -10 dBm, $f_{R2} = 6.01$ GHz at -10 dBm, $f_L = 5$ GHz at +13 dBm	dBm	+16		

Open Carrier Double-Balanced Mixer For Microwave Telecommunications

MC2413
V2

Typical Performance Curves




Open Carrier Double-Balanced Mixer For Microwave Telecommunications

MC2413
V2

Absolute Maximum Ratings

Parameter	Absolute Maximum
Operating Temperature	-54°C to +85°C
Storage Temperature	-65°C to +100°C
Peak Input Power	+23 dBm max @ +25°C +20 dBm max @ +85°C
Peak Input Current	50 mA DC

Outline Drawing: Open Carrier * MC2413



*For the base model, only the IF1 port is connected.
For the “-2” model, only the IF2 port is connected.

* Dimensions are inches (millimeters) ± 0.015 (0.38) unless otherwise specified.