







PRODUCT NO.
10098678-001LF
10098678-001TRLF
10098678-002C-TRLF





spec ref				dr		wcadmin	2010/04/26		projection				MM		size		A3	scale		3.000
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED				eng		Jeffrey Lim		2014/05/20				ecn no		ELX-S-14794-1				
ASME Y14.5						chr		-		-				rel level		Released				
						appr		Chen-Hong Tan		2014/05/20				product family						
surface		linear		0.X		±				title		SAS PLUG R/A		dwg no		10098678		rev		D
				0.XX		±0.20														
				0.XXX		±														
		angular		0°		±2°		www.fci.com		cat. no.		Product - Customer Drw		sheet 1 of 3						




Copyright FCI.


PRODUCT NO.
SEE TABLE




(CO-PLANARITY OF SOLDERTAILS
AND HOLD-DOWN PLATE)




SECTION L-L
SCALE 8.000




SECTION J-J
SCALE 8.000



SECTION K-K
SCALE 8.000


spec ref				dr	wcadmin	2010/04/26	projection 	MM 	size	A3	scale	3.000	
tolerance std				eng	Jeffrey Lim	2014/05/20			ecn no				ELX-S-14794-1
ASME Y14.5				chr	-	-			rel level				Released
				appr	Chen-Hong Tan	2014/05/20			product family				
surface ✓	linear	0.X	±		title SAS PLUG R/A TYPE ASSY				dwg no	10098678		rev D	
		0.XX	±0.20										
		0.XXX	±										
	angular	0°	±2°	www.fci.com	cat. no.			Product - Customer Drw			sheet 2 of 3		

PRODUCT NO.	PACKAGING
10098678-001LF	TRAY
10098678-001TRLF	TAPE & REEL
10098678-002C-TRLF	



SCALE 2.500

10098678-002C-TRLF WITH
PICK-UP CAP ATTACHED



SCALE 3.000

RECOMMENDED SMT PAD DIMENSIONS

NOTES:

- MATERIAL:
HOUSING & CAP: HIGH TEMPERATURE THERMOPLASTIC, BLACK, UL94V-0
CONTACT & HOLD DOWN: COPPER ALLOY
- FINISH:
CONTACT: 1.27um MIN. NICKEL UNDERPLATE OVERALL,
1.91um MIN. 100% MATTE TIN(LEAD-FREE) ON SOLDER TAIL,
0.38um MIN. GOLD ON CONTACT AREA
HOLD DOWN: 1.91um MIN. 100% MATTE TIN(LEAD-FREE) OVER
1.27um MIN. NICKEL UNDERPLATE OVERALL
- RECOMMENDED PCB THICKNESS: 1.40mm
- THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATIONS AS DESCRIBED IN GS-47-0004
- THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE
FOR 10 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE
REFLOW OVEN
- THIS CONNECTOR IS COMPLY WITH SFF-8482 SPECIFICATION
- THIS CONNECTOR IS COMPLY WITH CUSTOMER
GENERAL SPECIFICATION FOR THE ENVIRONMENT(GSE)
- THE PLATING OF THIS CONNECTOR IS COMPLY WITH CUSTOMER
TESTING AND PLATING SPECIFICATION EL-MF864-00
- A SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW OR NOTE WHICH HAS BEEN
MODIFIED WITH THE CURRENT DRAWING REVISION

spec ref				dr	wcadmin	2010/04/26	projection 	MM 	size	A3	scale	3.000		
tolerance std				eng	Jeffrey Lim	2014/05/20			ecn no				ELX-S-14794-1	
ASME Y14.5				chr	-	-			rel level				Released	
				appr	Chen-Hong Tan	2014/05/20			product family					
surface 	linear	0.X	±		title				SAS PLUG R/A	dwg no	10098678		rev	D
		0.XX	±0.20											
		0.XXX	±											
	angular	0°	±2°	www.fci.com	cat. no.				Product - Customer Drw				sheet 3 of 3	