




PRODUCT NUMBER
SEE TABLE



SECTION A-A



mat'l. code				surface	tolerance	projection	product family
				ISO 1302 ✓	ISO 406 ISO 1101		HEADERS
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title
E	REDRAWN	RLS	11/21/88		angles .XX±.01/.3	INCH/MM	VERTICAL STACKING 2-ROW HEADER
F	REVISED	MRC	5/23/91		linear .XXX±.005/.13		.500/12.70 W/O MOUNTING HOLES
G	V13306	JWB	12/17/91	0°±2'	.XXXX±.0020/.051	scale 2:1	dwg no
H	V50569	MDF	8/11/95	dr	M. FETROW	8/11/95	sheet 1 of 4 size
J	V71450	HTB	10/7/97	enr	L. FYE	8/11/95	69916 A3
K	M05-0089	ERE	5/20/05	chr	T. BREWBAKER	8/11/95	type
L	M06-0289	AGS	7/29/06	appd	L. FYE	8/11/95	Product Customer Drawing
sheet	revision	L	L	L	L		
index	sheet	1	2	3	4		




FCIconnect.com

Copyright FCI

D


POSITION TABLE	
PRODUCT NO	SIZE
XXXXX-001	2X5
-002	2X6
-003	2X7
-004	2X8
-005	2X9
-006	2X10
-007	2X11
-008	2X12
-009	2X13
-010	2X14
-011	2X15
-012	2X16
-013	2X17
-014	2X18
-015	2X19
-016	2X20
-017	2X21
-018	2X22
-019	2X23
-020	2X24
-021	2X25
-022	2X26
-023	2X27
-024	2X28
-025	2X29
-026	2X30
-027	2X31
-028	2X32
-029	2X33
-030	2X34
-031	2X35
XXXXX-032	2X36

PART NUMBER INFORMATION



NOTES

- SEE POSITION TABLE FOR PRODUCT NO AND SIZE TABULATION. HOUSING DASH NO IS SAME AS HEADER DASH NO.
- DIM B =
(NO OF COLUMNS - 1) TIMES .100 (ENGLISH)
(NO OF COLUMNS - 1) TIMES 2.54 (METRIC)
- MOLDING MATERIAL: 20% MIN GLASS FILLED NYLON PER UL 94V-0. COLOR: BLACK, OXYGEN INDEX 36.
- TERMINAL MATERIAL: 3/4 HARD PHOS BRONZE ALLOY UNS C51000.
- PIN RETENTION TO BE 3 LBS./1.4 KGS MINIMUM PER PIN IN EITHER DIRECTION.
- COMPANY LOGO TO BE MOLDED IN APPROX LOCATION SHOWN.
- UL/CSA APPROVED.
- ADD "LF" SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION.
- THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 15 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.5mm MINIMUM THICK CIRCUIT BOARD. SEE APPLICATION NOTES/PROCEDURES IF THEY ARE AVAILABLE.
- THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
- PLATING OPTIONS:
MAY BE EITHER GOLD OR GXT PLATED AT MANUFACTURER'S OPTION.

RECOMMENDED PC BOARD LAYOUT
SCALE 2/1

mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family HEADERS
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title
L					angles .XX±.01/.3	INCH/MM	VERTICAL STACKING 2-ROW HEADER
					linear .XXX±.005/.13		.500/12.70 W/O MOUNTING HOLES
					0°±2' .XXX±.0020/.051	scale 2:1	
			dr	M. FETROW	8/11/95	FCI	dwg no
			enr	L. FYE	8/11/95		sheet2 of 4 size
			chr	T. BREWBAKER	8/11/95		69916 A3
			app	L. FYE	8/11/95		type Product Customer Drawing
sheet index	revision sheet						

form: A3



FCIconnect.com

Copyright FCI

PRODUCT NO NOTE 8	TERMINAL PLATING NOTE 11
69916-XXX	30u"/0.76u MIN Au OVER 50u"/1.27u Ni.
69916-033	30u"/0.76u MIN Au OVER 50u"/1.27u Ni.
69916-034	30u"/0.76u MIN Au OVER 50u"/1.27u Ni.
86363-XXX	15u"/0.38u Pd Ni WITH GOLD FLASH
88809-021	30u"/0.76u MIN Au OVER 50u"/1.27u Ni.

mat'l. code				surface ISO 1302 ☒		tolerance ISO 406 ISO 1101		projection 		product family HEADERS					
litr		ecn no		dr		date		tolerances unless otherwise specified				title			
L								angles		linear		.XX±.01/.3		INCH/MM	
								0°±2°				.XXX±.005/.13			
												.XXXX±.0020/.051		scale 2:1	
								dr		M. FETROW		8/11/95			
								enrg		L. FYE		8/11/95			
								chr		T. BREWBAKER		8/11/95			
								appd		L. FYE		8/11/95			
sheet		revision													
index		sheet													

dwg no		sheet 3 of 4		size	
69916				A3	
type		Product		Customer Drawing	

form: A3



FCIconnect.com

Copyright FCI

PRODUCT NO NOTE 8	SIZE	DIM "B"	DIM "C"	DIM "L"	TAIL LENGTH DIM "T"	MATING LENGTH DIM "M"	TOTAL PIN LENGTH DIM "P"
69916-XXX	NOTE 1	NOTE 2	DIM "B" +.130/3.30	DIM "B" +.210/5.33	.103/2.62 MIN .130/3.30 MAX	.275±.010 6.99±0.25	.555/14.10
69916-033	2 x 8	.700/17.78	.83/21.1	.91/23.1	.148±.008 3.76±0.20	.275±.010 6.99±0.25	.585/14.86
69916-034	2 x 15	1.400/35.56	1.53/38.9	1.61/41.0	.148±.008 3.76±0.20	.275±.010 6.99±0.25	.585/14.86
86363-XXX	NOTE 1	NOTE 2	DIM "B" +.130/3.30	DIM "B" +.210/5.33	.103/2.62 MIN .130/3.30 MAX	.275±.010 6.99±0.25	.555/14.10
88809-021	2 x 25	2.400/60.96	2.53/64.3	2.61/66.3	.130±.015 3.30±0.38	.290±.010 7.37±0.25	.585/14.86

mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101	projection 	product family HEADERS		
ltr	ecn	no	dr	date		tolerances unless otherwise specified		title		
L						angles	.XX±.01/.3	INCH/MM ↔		
						linear	.XXX±.005/.13			
						0°±2°	.XXXX±.0020/.051	scale 2:1		
						dr	M. FETROW 8/11/95			
						enr	L. FYE 8/11/95			
						chr	T. BREWBAKER 8/11/95			
						appd	L. FYE 8/11/95			
sheet	revision							dwg no		
index	sheet							sheet 4 of 4 size		
								69916 A3		
								type Product Customer Drawing		

form: A3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

FCI:

[69916-012LF](#) [69916-032LF](#) [69916-001](#) [69916-002](#) [69916-003](#) [69916-004](#) [69916-006](#) [69916-008](#) [69916-009](#)
[69916-010](#) [69916-011](#) [69916-013](#) [69916-014](#) [69916-016](#) [69916-017](#) [69916-018](#) [69916-020](#) [69916-021](#) [69916-022](#)
[69916-024](#) [69916-026](#) [69916-028](#) [69916-031](#) [69916-001LF](#) [69916-002LF](#) [69916-003LF](#) [69916-004LF](#) [69916-](#)
[006LF](#) [69916-009LF](#) [69916-010LF](#) [69916-011LF](#) [69916-013LF](#) [69916-014LF](#) [69916-016LF](#) [69916-017LF](#) [69916-](#)
[018LF](#) [69916-020LF](#) [69916-021LF](#) [69916-022LF](#) [69916-024LF](#) [69916-026LF](#) [69916-028LF](#) [69916-031LF](#) [69916-](#)
[012](#) [69916-007](#) [69916-005](#) [69916-027](#)