




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
G	14		C1	REVISED PER ECO-14-003208	14MAR2014	NK	DR



- 1 WIRE SIZE IS #16-#14 AWG
- 2 INSULATION DIA: 3.0-4.9[.12-.19]
- 3 MATERIAL THICKNESS IS 0.8[.03]
- 4 DIMENSION APPLIES FROM EDGE OF METAL WIRE BARREL TO END OF PIN
- 5 STAMP AMP 16-14* APPROX AS SHOWN
- 6 MAX RECOMMENDED OPERATING TEMPERATURE 105°C[221°F]

SECTION A-A

SECTION B-B

LOOSE PIECE	STANDARD	1000	181631
PACKAGING	LABELLING	QTY	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN jr ruth	02FEB06	 TE Connectivity				
		CHK T MICHIELUTTI	02FEB06					
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD T MICHIELUTTI	02FEB06	NAME TERMINAL, WIRE PIN, PLASTI-GRIP,				
	0 PLC ± -	PRODUCT SPEC —						
	1 PLC ± 0.5[.02]	APPLICATION SPEC —						
	2 PLC ± -	—						
	3 PLC ± -	—		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
	4 PLC ± -	—		A2	00779	C=181631	—	
MATERIAL —	FINISH —	WEIGHT —						
CUSTOMER DRAWING						SCALE 8:1	SHEET 1 of 1	REV C1