

High-Frequency Amplifier Transistor (11V, 50mA, 3.2GHz)

2SC4726H / 2SC4726 / 2SC4083 / 2SC3838K 2SC4043S

●Features

- 1) High transition frequency. (Typ. $f_T = 1.5\text{GHz}$)
- 2) Small $r_{bb'}$ · C_c and high gain. (Typ. 4ps)
- 3) Small NF.






● Absolute maximum ratings ($T_a = 25^\circ\text{C}$)

Parameter	Symbol	Limits	Unit
Collector-base voltage	V_{CB0}	20	V
Collector-emitter voltage	V_{CE0}	11	V
Emitter-base voltage	V_{EB0}	3	V
Collector current	I_C	50	mA
Collector power dissipation	2SC4726H, 2SC4726	0.15	W
	2SC4083, 2SC3838K	0.2	
	2SC4043S	0.3	
Junction temperature	T_J	150	$^\circ\text{C}$
Storage temperature	T_{stg}	$-55 \sim +150$	$^\circ\text{C}$

●Packaging specifications and h_{FE}

Type	2SC4726H	2SC4726	2SC4083	2SC3838K	2SC4043S
Package	EMT3H	EMT3	UMT3	SMT3	SPT
h_{FE}	NP	NP	NP	NP	P
Marking	AD	AD	1D	AD	—
Code	T2L	TL	T106	T146	TP
Basic ordering unit (pieces)	8000	3000	3000	3000	5000

●External dimensions (Units : mm)

2SC4726H		(1) Emitter (2) Base (3) Collector
2SC4726		(1) Emitter (2) Base (3) Collector
2SC4083		(1) Emitter (2) Base (3) Collector
2SC3838K		(1) Emitter (2) Base (3) Collector
2SC4043S		(1) Emitter (2) Collector (3) Base

2SC4726H / 2SC4726 / 2SC4083 / 2SC3838K / 2SC4043S

Transistors

●Absolute maximum ratings (Ta = 25°C)

Parameter		Symbol	Min.	Typ.	Max.	Unit	Conditions
Collector-base breakdown voltage		BV_{CBO}	20	—	—	V	$I_C = 10\mu A$
Collector-emitter breakdown voltage		BV_{CEO}	11	—	—	V	$I_C = 1mA$
Emitter-base breakdown voltage		BV_{EBO}	3	—	—	V	$I_E = 10\mu A$
Collector cutoff current		I_{CBO}	—	—	0.5	μA	$V_{CB} = 10V$
Emitter cutoff current		I_{EBO}	—	—	0.5	μA	$V_{EB} = 2V$
Collector-emitter saturation voltage		$V_{CE(sat)}$	—	—	0.5	V	$I_C/I_E = 10mA/5mA$
DC current transfer ratio	2SC4726H, 2SC4726 2SC4083, 2SC3838K	h_{FE}	56	—	180	—	$V_{CE}/I_C = 10V/5mA$
	2SC4043S		82	—	180		
Transition frequency		f_T	1.4	3.2	—	GHz	$V_{CE} = 10V, I_E = 10mA, f = 500MHz$
Output capacitance		C_{ob}	—	0.8	1.5	pF	$V_{CB} = 10V, I_E = 0A, f = 1MHz$
Collector-base time constant		$\tau_{cb} \cdot C_c$	—	4	12	ps	$V_{CB} = 10V, I_C = 10mA, f = 31.8MHz$
Noise factor		NF	—	3.5	—	dB	$V_{CE} = 6V, I_C = 2mA, f = 500MHz, R_g = 50\Omega$