







- 1** MATERIAL: CONNECTOR - NYLON UL94V-2 (WHITE)
CONTACTS - 0.30[.012] THICK COPPER ALLOY
(BRIGHT TIN-LEAD 0.00203[.000080] MIN. THICK
FOR CONTACTS 640607-2 THRU 2-640607-4)
(MATTE WHISKER MITIGATED TIN 0.00203[.000080] MIN
THICKNESS OVER NICKEL UNDERPLATE FOR
3-640607-2 THRU 5-640607-4).
- 2 CONTACTS ACCEPT 24 AWG WIRE WITH 2.41[.095] MAX INSULATION DIAMETER.
- 3 CONTACTS MUST ACCEPT 1.14±0.03[.045±.001] SQUARE POST AND REMAIN LOCKED IN POSITION.
- 4** IDENTIFICATION NUMBER FOR LAST CIRCUIT MAY NOT APPEAR ON ALL ASSEMBLIES.
- 5 DIMENSIONS IN BRACKETS ARE IN INCHES.
- 6 HOUSING FEATURES ARE: FEED-THRU WITHOUT LOCKING RAMP.
- 7** OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



95.10	[3.744]	24	5-640607-4
91.14	[3.588]	23	5-640607-3
87.17	[3.432]	22	5-640607-2
83.21	[3.276]	21	5-640607-1
79.25	[3.120]	20	5-640607-0
75.29	[2.964]	19	4-640607-9
71.32	[2.808]	18	4-640607-8
67.36	[2.652]	17	4-640607-7
63.40	[2.496]	16	4-640607-6
59.44	[2.340]	15	4-640607-5
55.47	[2.184]	14	4-640607-4
51.51	[2.028]	13	4-640607-3
47.55	[1.872]	12	4-640607-2
43.59	[1.716]	11	4-640607-1
39.62	[1.560]	10	4-640607-0
35.66	[1.404]	9	3-640607-9
31.70	[1.248]	8	3-640607-8
27.74	[1.092]	7	3-640607-7
23.77	[.936]	6	3-640607-6
19.81	[.780]	5	3-640607-5
15.85	[.624]	4	3-640607-4
11.89	[.468]	3	3-640607-3
7.92	[.312]	2	3-640607-2
95.10	[3.744]	24	2-640607-4
91.14	[3.588]	23	2-640607-3
87.17	[3.432]	22	2-640607-2
83.21	[3.276]	21	2-640607-1
79.25	[3.120]	20	2-640607-0
75.29	[2.964]	19	1-640607-9
71.32	[2.808]	18	1-640607-8
67.36	[2.652]	17	1-640607-7
63.40	[2.496]	16	1-640607-6
59.44	[2.340]	15	1-640607-5
55.47	[2.184]	14	1-640607-4
51.51	[2.028]	13	1-640607-3
47.55	[1.872]	12	1-640607-2
43.59	[1.716]	11	1-640607-1
39.62	[1.560]	10	1-640607-0
35.66	[1.404]	9	640607-9
31.70	[1.248]	8	640607-8
27.74	[1.092]	7	640607-7
23.77	[.936]	6	640607-6
19.81	[.780]	5	640607-5
15.85	[.624]	4	640607-4
11.89	[.468]	3	640607-3
7.92	[.312]	2	640607-2
DIM A		NO OF CIRCUITS	PART NO

SUPERSEDED
7

7 SUPERSEDED

7 SUPERSEDED

SUPERSEDED
7

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL
1

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±	-
1 PLC	±	-
2 PLC	±	-
3 PLC	±	0.13 [.005]
4 PLC	±	-
ANGLES	±	-
FINISH	1	

DWN
B. LEWIS
12FEB91

CHK
R. SWING
12FEB91

APVD
D. CLARK
19FEB91

PRODUCT SPEC
108-1051

APPLICATION SPEC
114-1020

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
MTA-156 CONNECTOR ASSEMBLY,
24 AWG, STANDARD
-

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-640607

RESTRICTED TO
-

SCALE
4:1

SHEET
1 OF 1

REV
S2