


TYPES 2N6326, 2N6327, 2N6328 N-P-N SILICON POWER TRANSISTORS


PARAMETER MEASUREMENT INFORMATION



- NOTES:
- V_{gen} is a -30 V pulse (from 0 V) into a $50\text{-}\Omega$ termination.
 - The V_{gen} waveform is supplied by a generator with the following characteristics: $t_r \leq 15\text{ ns}$, $t_f \leq 15\text{ ns}$, $Z_{out} = 50\ \Omega$, $t_w = 20\ \mu\text{s}$, duty cycle $\leq 2\%$.
 - Waveforms are monitored on an oscilloscope with the following characteristics: $t_r \leq 15\text{ ns}$, $R_{in} \geq 10\text{ M}\Omega$, $C_{in} \leq 11.5\text{ pF}$.
 - Resistors must be noninductive types.
 - The d.c. power supplies may require additional bypassing in order to minimize ringing.

FIGURE 1

INDUCTIVE LOAD SWITCHING



NOTE A: Input pulse width is increased until $I_{CM} = 4.5\text{ A}$.

FIGURE 2

TEXAS
INSTRUMENTS

TYPES 2N6326, 2N6327, 2N6328 N-P-N SILICON POWER TRANSISTORS

MAXIMUM SAFE OPERATING AREAS




FIGURE 3




FIGURE 4

NOTE 8: Above this point the safe operating area has not been defined.

THERMAL INFORMATION




FIGURE 5




FIGURE 6

UNITED KINGDOM
Regional Technology Centre
Texas Instruments Limited
Manton Lane
Bedford MK41 7PA
Telephone: (0234) 67466
Telex: 82178
Technical Enquiry Service
Telephone: (0234) 223000

FRANCE
Texas Instruments France
Boite Postale 5
06270 Villeneuve Loubet
Telephone: (93) 200101
Telex: 470127

GERMANY
Texas Instruments
Deutschland GmbH.
Haggertystrasse 1
8050 Freising
Telephone: 08161 800
Telex: 526529

ITALY
Texas Instruments
Semiconduttori Italia S.P.A.
Divisione Semiconduttori
Viale delle Scienze 1
02015 Cittaducale (Rieti)
Telephone: (0746) 6941
Telex: 611003