

732.680



DATI TECNICI - TECHNICAL DATA - DONNEES TECHNIQUES

Contatti in interruzione per aumento della temperatura	Cut-off contacts for temperature raising	Coupeure par élévation de température	
Temperatura max. testa	Max. head temperature	Température maxi de la tête	100°C
Temperatura max. bulbo	Max. bulb temperature	Température maxi du bulbe	125°C
Bulbo rame	Copper bulb	Bulbe en cuivre	Ø6,5x95 mm
Lunghezza capillare	Capillary length	Longueur capillaire	1000 mm
Raggio min. di curvatura del capillare	Min. capillary bending radius	Rayon min. de courbure du capillaire	5 mm
Gradiente termico	Temperature rate of change	Vitesse de variation de la température	1°K/min
Classe di protezione	Protection class	Classe de protection	

LS1

TIPI STANDARD - STANDARD TYPES - TYPES STANDARDS

Codice	Code	Code	541510
Temperatura limitatore regolabile	Adjustable limit temperature	Température limite réglable	90°/110°C
Tolleranza	Tolerance	Tolérance	+0°/-6°K
Riarmo manuale	Manual reset	Réarmement manuel	
Portata sui contatti	Contacts rating	Pouvoir de coupure	15 (2,5A 250 V - 10A 380 V -
Contatti	Contacts	Contacts	Ag. 1000/1000
Codice	Code	Code	541550
Temperatura limitatore fissa	Fixed limit temperature	Température limite fixe	100°C
Tolleranza	Tolerance	Tolérance	+0°/-6°K
Riarmo manuale	Manual reset	Réarmement manuel	
Portata sui contatti	Contacts rating	Pouvoir de coupure	15 (2,5A 250 V - 10A 380 V -
Contatti	Contacts	Contacts	Ag. 1000/1000
Codice	Code	Code	541680
Temperatura limitatore fissa	Fixed limit temperature	Température limite fixe	100°C
Tolleranza	Tolerance	Tolérance	+0°/-6°K
Riarmo manuale	Manual reset	Réarmement manuel	
Portata sui contatti	Contacts rating	Pouvoir de coupure	15 (2,5A 250 V -
Contatti	Contacts	Contacts	Ag. 1000/1000
Portata contatto di segnalazione (c - 1)	Contacts rating for warning purpose (c - 1)	Pouvoir de coupure du contact de signalisation (c - 1)	0,5A 250 V -

LS3

TIPI STANDARD - STANDARD TYPES - TYPES STANDARDS

Codice	Code	Code	541750
Temperatura limitatore fissa	Fixed limit temperature	Température limite fixe	100°C
Tolleranza	Tolerance	Tolérance	+0°/-6°K
Differenziale	Temperature differential	Différentiel de température	$\Delta t = 12^\circ \pm 3^\circ K$
Riarmo automatico	Automatic reset	Réenclenchement automatique	
Contatti dorati	Gold-plated contacts	Contacts dorés	Cu/Au
Portata sui contatti	Contacts rating	Pouvoir de coupure	0,3A 100 mV cc
Resistenza di contatto	Contact resistance	Resistance de contact	$\leq 10 \text{ m}\Omega$
Codice	Code	Code	541752
Temperatura limitatore fissa	Fixed limit temperature	Température limite fixe	100°C
Tolleranza	Tolerance	Tolérance	+0°/-6°K
Differenziale	Temperature differential	Différentiel de température	$\Delta t = 12^\circ \pm 3^\circ K$
Riarmo automatico	Automatic reset	Réenclenchement automatique	
Contatti dorati	Gold-plated contacts	Contacts dorés	Cu/Au
Portata sui contatti	Contacts rating	Pouvoir de coupure	0,3A 100 mV cc
Cavo bipolare	Bipolar cable	Cable bipolaire	2x2,5 mm ² L = 800 mm
Codice	Code	Code	541780
Temperatura limitatore regolabile	Adjustable limit temperature	Température limite réglable	90°/110°C
Tolleranza	Tolerance	Tolérance	+0°/-6°K
Differenziale	Temperature differential	Différentiel de température	$\Delta t = 12^\circ \pm 3^\circ K$
Riarmo automatico	Automatic reset	Réenclenchement automatique	
Contatti dorati	Gold-plated contacts	Contacts dorés	Cu/Au
Portata sui contatti	Contacts rating	Pouvoir de coupure	0,3A 100 mV cc
Resistenza di contatto	Contact resistance	Resistance de contact	$\leq 10 \text{ m}\Omega$

Versioni speciali su richiesta / Special versions on request / Versions spéciales sur demande

Con riserva di apportare modifiche senza avviso - We reserve the right to make changes without notice - Sous réserve de apporter des modifications sans préavis

IMIT S.p.A. - 28043 CASTELLETTO TICINO (NO) - Italia - Tel. (0331) 972600 - Telex 200342 IMIT I - Telefax (0331) 973100

01889-270577 ALTECNIC LTD

767 P02 18.05.00