

Technical data sheet · LÜTZE SUPERFLEX® N PUR



PUR C-track cable · For the highest requirements

Identification	Type	5×1.0
	Part-No.	110999
Use/Area of application		
Application	• Machine and device construction, transport and conveyor technology • Through full PUR jacket suited for c-tracks, extremely harsh operating conditions, aggressive coolants and lubricants • Special for industrial environments, machines and plants	
Properties	• Extreme space-saving design • Low capacitance, very good electrical properties • Halogen-free, no corrosive gases • Very good alternating bending strength • Low adhesion, abrasion-proof, nick-resistant, tear-propagation-resistant • hydrolisis-resistant, microbe-resistant, and rot-resistant • Weathering, ozone and UV resistant (normal lighting conditions • Good industrial- and salt water resistance • Excellent coolant and lubricant resistance • Widely resistant to oils, greases, alcohol-free benzines and kerosene • Free from paint wetting disruptive substances (LABS-free), RoHS-compliant	
Technical data		
Voltage	U ₀ /U	300/500 V
Test voltage	3000 V	
Insulation resistance	min. 100 MΩ × km	
Temperature range	moving	-25 °C to +80 °C

23.11.2007 – Subject to technical modification

Part-No. 110999

USA: LUTZE INC.

13330 South Ridge Drive • Charlotte, NC 28273
Tel.: +1 (704) 504-0222 • Fax: +1 (704) 504-0223
www.lutze.com • info@lutze.com

United Kingdom: LÜTZE Ltd.

Unit 3 Sandy Hill Park
Sandy Way, Amington • GB-Tamworth, Staffs, B77 4DU
Tel.: +44 (0)1827 31333-0 • Fax: +44 (0)1827 31333-2
www.lutze.com • sales.gb@lutze.co.uk

Technical data sheet · LÜTZE SUPERFLEX® N PUR

Minimum bending radius	fixed	-40 °C to +80 °C
	moving	Cable diameter × 10
	fixed	Cable diameter × 4
Halogen-free	according to DIN EN 50264-1; EN 50267-2-1; EN 60684-2	
Number of strands/cross-section	5 × 1,0	
Outer-Ø	6.7 approx. mm	
Weight	6.8 kg/100 m	
Cu-Index	5.0 kg/100 m	

Design

Conductor structure	Bare copper wire, finest multi-strand according to DIN VDE 0295 class 6, IEC 60228 class 6
Conductor insulation	Special-TPE conductor insulation
Conductor labelling	Conductors black with white number print according to DIN EN 50334
Ground conductor	green/yellow according to DIN EN 50334 in the top layer
Stranding	Conductors twisted without mechanical stress, layer pitch optimised
Banding	Non-woven material over stranded cable
Outer jacket	Full polyurethane jacket, matt, adhesion-free surface
Jacket colour	grey RAL 7001

General

Note	CE These products are in conformity to the EC Low Voltage Directive 73/23/EWG or 93/68/EWG respectively
------	---

Logo

halogenfree

low capacity

23.11.2007 – Subject to technical modification

Part-No. 110999

USA: LUTZE INC.

13330 South Ridge Drive • Charlotte, NC 28273
Tel.: +1 (704) 504-0222 • Fax: +1 (704) 504-0223
www.lutze.com • info@lutze.com

United Kingdom: LÜTZE Ltd.

Unit 3 Sandy Hill Park
Sandy Way, Amington • GB-Tamworth, Staffs, B77 4DU
Tel.: +44 (0)1827 31333-0 • Fax: +44 (0)1827 31333-2
www.lutze.com • sales.gb@lutze.co.uk