


LOC	DIST	REVISIONS					
AA	22	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	REV PER EC 0S11-0201-04	13JUN2005	AF	SF





MATERIAL:
HOUSING — PCT POLYESTER, BLACK, UL94V-0.
OVERMOLDED TERMINAL ARRAY — PBT, BROWN.
TERMINALS — 0.33 [.013] THICK PHOS BRONZE
PLATED WITH 1.27µm [.000050] MIN THICK
HARD GOLD IN LOCALIZED AREA AND 3.81µm
[.000150] MIN THICK MATTE TIN IN SOLDER
AREA OVER 1.27µm [.000050] MIN THICK
NICKEL UNDERPLATE.
SHIELD — 0.25 [.010] THICK COPPER ALLOY
PLATED WITH 2.03µm [.000080] MIN THICK TIN
OVER 1.27µm [.000040] MINIMUM THICK NICKEL.

JACK CAVITY CONFORMS TO FCC RULES AND
REGULATIONS, PART 68 SUBPART F.


DATE CODE LABEL LOCATED ON REAR OF PART
APPROXIMATELY AS SHOWN:
FIRST 2 DIGITS ARE LAST 2 DIGITS OF YEAR,
SECOND 2 DIGITS ARE MANUFACTURING
WORK WEEK,
LAST DIGIT IS DAY OF WEEK, WITH SUNDAY = 1.



PARTIAL REAR VIEW



PC BOARD LAYOUT VIEWED FROM COMPONENT SIDE
SCALE 2:1



SUGGESTED PANEL CUTOUT DIMENSIONS
SCALE 2:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A. FERNANDEZ-DOCK5 13JUN2005	Tyco Electronics Corporation Harriaburg, Pa 17105-3608	
DIMENSIONS: mm [INCHES]		CHK J. WESTMAN 13JUN2005	NAME S. FLICKINGER 13JUN2005	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-1163-2	APPLICATION SPEC 114-2048	
MATERIAL		WEIGHT —	SIZE A1	RESTRICTED TO —
CUSTOMER DRAWING		SCALE 4:1	SHEET 1 OF 1	REV A