


Universal topJob tool
only 1 tool for all topJob terminal blocks
sizes 2.5 mm² – 16 mm²/AWG 14 – 6
– ideal in areas with limited wiring space

Multipole operating tools
for front-entry terminal blocks (insulated)


Operating tools, for wiring of
side-entry rail-mounted terminal blocks




Item-No.	Pack.-unit pcs	Item-No.	Pack.-unit pcs	Item-No.	Pack.-unit pcs
topJob tool , specially designed blade for <u>all</u> topJob terminal blocks		Operating tools , solid non-conducting material suitable for series 279		Operating tool , for side-entry rail-mounted terminal blocks series 279 and 280	
777-310	1	1-way 209-129	1	210-143	1
		suitable for series 279		Operating tool , for side-entry rail-mounted terminal blocks series 281, 282, 283 and 284	
		2-way 279-432	1	210-141	1
		3-way 279-433	1		
		10-way 279-440	1		
		suitable for series 264*, 280, 281**			
		1-way 209-130	1		
		2-way 280-432	1		
		3-way 280-433	1		
		4-way 280-434	1		
		5-way 280-435	1		
		6-way 280-436	1		
		7-way 280-437	1		
		8-way 280-438	1		
		9-way 280-439	1		
		10-way 280-440	1		
		suitable for series 281			
		5-way 281-440	1		
		* only 1- and 2-way			
		** only up to 3-way			



Operation of topJob terminal blocks for wire sizes from 2.5 mm² – 16 mm²/AWG 14 – 6, ideal with the universal topJob tool.



Commoning of front-entry through terminal blocks with comb type jumper bars with the aid of a 10-way operating tool.



The plunger is placed into the upper operating slot of the side-entry terminal block and the clamp is hooked into the lateral operating hole. The contact is fully opened by pressing the handles together until they engage – both hands are then free for the preparation and introduction of the conductor into the terminal block. When operating the handles beyond the locked position the ratchet allows the tool to open and be removed from the terminal block.