



PRODUCT NO

10088047-100LF

A

A



SCALE 6.000

## NOTES:

## 1. MATERIAL:

HOUSING: 30% G/F LCP, UL 94V-0, COLOR: BLACK.

CONTACT &amp; DETECT PIN: COPPER ALLOY, THICKNESS=0.15MM.

CONTACT PLATING: 50 $\mu$  MIN. OF Ni UNDERPLATE, GOLD FLASH OVER ALL, CONTACT AREA PLATING 30 $\mu$  GOLD.DETECT PIN PLATING: 50 $\mu$  MIN. OF Ni UNDERPLATE, GOLD FLASH ON CONTACT AREA, TIN PLATED ON SOLDER AREA.

BRACKET: STAINLESS STEEL, THICKNESS=0.20MM, GOLD FLASH ON SOLDER AREA.

## 2. PRODUCT PERFORMANCE SPEC. PER GS-12-451.

## 3. PACKAGE SPEC. PER GS-14-1162.

## 4. "■" REPRESENT CRITICAL DIMS AND NEED TO MEET Cpk&gt;1.5

## 5. THIS PRODUCT IS RoHS COMPLIANT, AND MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS PER GS-22-008.

Copyright FCI.

D

D

rev	ecn no	dr	date
A	DG08-0339	S H	2008-12-04
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com		surface	tolerance std	projection	MM
TOLERANCES UNLESS OTHERWISE SPECIFIED					
Dr	DAVID TENG	2008-07-07	ANGULAR	0.X	$\pm 0.30$
Eng	DAVID TENG	2008-07-07	LINEAR	0.XX	$\pm 0.15$
Chr	PAUL WANG	2008-07-07		0.XXX	$\pm 0.08$
Appr	JOSEPH HSIA	2008-07-07	Product family	ECN	DG08-0339
				Spec ref	
 TFLASH CONNECTOR ASSEMBLY		dwg no		10088047	Rev. A
<sup>+</sup> TFLASH CARD READER		catalog no		10088047	CUSTOMER
				sheet 1 of 2	




Copyright FCI.


PRODUCT NO  
10088047-100LF

1 2 3 4


A




B



C



D



SCALE 6.000



1 TFLASH CONNECTOR ASSEMBLY  
2 TFLASH CARD READER

dwg no 10088047 Rev. A  
catalog no 10088047 CUSTOMER sheet 2 of 2

REV F - 2006-04-17

2


3

4

PDM: Rev:A

STATUS: Released

Printed: May 28, 2010



RECOMMENDED PCB LAYOUT

NOTE:  
1.CO-PLANARITY FROM SEATING PLANE 0.10MM MAX.  
2.TOLERANCE FOR PCB LAYOUT: ±0.05MM.

TOLERANCES UNLESS OTHERWISE SPECIFIED	
	0.X ±0.30
LINEAR	0.XX ±0.15
	0.XXX ±0.08
ANGULAR	0° ±2°