

PRODUCT NUMBER
98424-X52-XX-XXXLF

PLATING

S = 0.38µm GOLD/GXT
ON CONTACT AREA
2µm MIN MATTE
TIN ON TAIL

G = 0.76µm GOLD/GXT
ON CONTACT AREA
2µm MIN MATTE TIN ON TAIL

F = GOLD FLASH
ON CONTACT AREA
2µm MIN MATTE TIN ON TAIL

T = 2.0-6.0µm FULL MATTE TIN

1.27µm Ni MIN UNDERLAYER

NOTES:

1. MATERIAL HOUSING: HIGH TEMP. THERMOPLASTIC UL-94VO
- = STANDARD COLOR CREAM
B = OPTIONAL COLOR BLACK

2. MATERIAL TERMINAL: COPPER ALLOY

3. TO DETERMINE DIMENSIONS:
N = NUMBER OF POSITIONS PER ROW

4. 7N MIN. PIN RETENTION IN EITHER DIRECTION.

5. PACKAGING:

= STANDARD PACKAGING IN POLYBAGS
- = POLYBAGS PACKAGING WHEN POLARISATION FEATURE APPLICABLE
U = TUBE AVAILABLE FROM 08 TO 50 POS

A = TAPE AND REEL WITH PICK UP CAP, AS AVAILABLE

K = TAPE AND REEL WITHOUT PICK UP CAP, AS AVAILABLE.

C = TAPE AND REEL WITH SPECIAL LARGE CAP, ONLY FOR 98424-Y52-06CLF
FOR ALL SPECIAL PACKAGING, FCI TO BE CONTACTED

UV = TUBE WITHOUT PICK UP CAP FOR CUSTOMER DEDICATED PART

AV = TAPE & REEL WITH PICK UP CAP FOR CUSTOMER DEDICATED PART

KV = TAPE & REEL WITHOUT PICK UP CAP FOR CUSTOMER DEDICATED PART

6. DIM "C" = (N x 2) + 1.4

EXAMPLE: N = 7

DIM "C" = (7 x 2) + 1.4 = 15.4 mm

7. FOR POLARIZATION, SPECIFIED PIN

EXAMPLE : A03 = ROW A, POSITION 03 TO OMIT PIN
OMIT FROM PRODUCT NUMBER IF THIS FEATURE IS NOT APPLICABLE

8. RoHS COMPATIBLE PRODUCT SPECIFICATIONS

a - PLATING:

- "LF" MEANS THE PRODUCT IS LEAD-FREE,
2µm MINIMUM MATTE TIN OVER 1.27µm
MINIMUM NICKEL UNDERPLATE.

b - MANUFACTURING PROCESS COMPATIBILITY







- THE HOUSING WILL WITHSTAND EXPOSURE TO
260°C PEAK TEMPERATURE FOR 30 SECONDES
MAX IN A CONVECTION, INFRA-RED OR VAPOR
PHASE OR REFLOW OVEN.

c - LABELLING:





- MEETS PACKAGING SPECS AS PER GS-14-920

d - THIS PRODUCT MEETS EUROPEAN DIRECTIVES
AND OTHER COUNTRY REGULATIONS AS DISCRIBED
IN GS-47-0004.





RoHS COMPATIBLE, SEE NOTE 8
POLARIZATION (SEE NOTE 7)
PACKAGING OPTIONAL LETTER (SEE NOTE 5)
TOTAL NB OF POSITIONS, 04 TO 50
COLOR OPTION NOTE 1



mat'l. code				surface		tolerance		projection		product family	
SEE NOTES				ISO 1302	ISO 406	ISO 101	ISO 101	MINITEK			
ltr	ecn	no	dr	date	tolerances unless otherwise specified			title			
W	B-26204	JCA		17.02.27	angles	linear	X.X ±0.3	mm		SHR HEADER	
X	F-35976	DDE		20.01.24			X.XX ±0.13			2.00 VERTICAL SMT	
							X.XXX ±0.05	scale 1:1			
S	B-19190	LMU		14.10.24	dr	L.MULIN	04.09.27				
T	B-19797	AMA		14.12.16	engr	J.COMPAGNON	04.09.27				
U	B-19988	LMU		15.01.13	chr						
V	F-23051	AMA		16.01.15	appd	JMC	04.09.27				
sheet	revision	X	B								
index	sheet	1	2								



2x3 POS AND 2x4 POS CONFIGURATION
NO LATCHING AVAILABLE FOR 2x2 POS



2x5 POS UP TO 2x25 POS CONFIGURATION

LATCHING FEATURES WHEN USED IN COMBINATION
WITH ACTIVE LATCH HOUSING 10073599

mat'l. code SEE NOTES				surface ISO 1302 ✓	tolerance ISO 406 ISO 101	projection mm	product family MINITEK
ltr	ecn no	dr	date	tolerances unless otherwise specified		scale 1:1	title SHR HEADER 2.00 VERTICAL SMT
A	F08-0113	LMU	08.01.17	angles	linear		
B	F-35976	DDE	20.01.24				
				dr	L.MULIN	07.11.06	dwg no 98424 sheet 2 of - size A3
				engr	J.COMPAGNON	07.11.06	
				chr			
				appd	JM.C	07.11.06	type CUSTOMER Drawing
sheet index	revision sheet						