



DIMENSIONS In inches (and millimeters)


3x4 Rear Mount Keyboard




Standard Versions




Shielded/Backlit Versions




4x4 Front Mount Keyboard



Standard Versions




Shielded/Backlit Versions




DIMENSIONS In inches (and millimeters)

4x4 Rear Mount Keyboard



Standard Versions

Shielded/Backlit Versions



CODE AND TRUTH TABLES

Dots in the chart indicate connected terminals when switch is closed. Terminals are identified on the keyboard.

12 Button Keypads

3x4		MATRIX CODES																
		Standard						Shielded/Backlit										
BUTTON LOCATION	1																	
	2	•						•										
	3			•						•								
	4				•							•						
	5					•							•					
	6						•							•				
	7							•							•			
	8								•							•		
	9									•							•	
	10										•							•
	11											•						
	12												•					
		5	6	7	1	2	3	4	6	7	8	2	3	4	5	1	9	10
		TERMINAL LOCATION																

Shielded keypad = Shielded
Backlit keypad = NC
Shielded and backlit keypad =
Shielded

Shielded keypad = NC
Backlit keypad = EL Panel 1
Shielded and backlit keypad =
EL Panel 1

Shielded keypad = NC
Backlit keypad = EL Panel 2
Shielded and backlit keypad =
EL Panel 2

16 Button Keypads

4x4		MATRIX CODES																		
		Standard								Shielded/Backlit										
BUTTON LOCATION	1	•								•									Shielded keypad = Shielded Backlit keypad = NC Shielded and backlit keypad = Shielded Shielded keypad = NC Backlit keypad = EL Panel 1 Shielded and backlit keypad = EL Panel 1 Shielded keypad = NC Backlit keypad = EL Panel 2 Shielded and backlit keypad = EL Panel 2	
	2		•								•									
	3			•								•								
	4				•								•							
	5					•								•						
	6						•								•					
	7							•								•				
	8								•								•			
	9									•								•		
	10										•									
	11											•								
	12												•							
	13													•						
	14														•					
	15															•				
	16																•			
		5	6	7	8	1	2	3	4	6	7	8	9	2	3	4	5	1	10	11
		TERMINAL LOCATION																		

SPECIFICATIONS

Rating Criteria

Rating at 12 Vdc: 5 milliamps for .5 seconds

Contact Bounce: < 12 milliseconds

Contact Resistance: < 300 milliohms max.

Voltage Breakdown: 250 Vac between components

Mechanical Operation Life: 1,000,000 operations per key

Insulation Resistance: > 10¹² ohms @ 500 Vdc

Push Out Force Per Pin: 5 lbs.

Operating Features

Travel: .040 minimum

Operating Force: 175 ± 40 grams

Operating Temperature: -30°C to +80°C

Material and Finishes

Terminal Pin: Phosphor bronze

PC Board: FR-4 glass cloth epoxy

Keypad: Silicone rubber, durometer 50 ± 5

Housing: ABS, cycolac FR15

Housing Color: Black

Shielding Effectiveness


Results shown are typical for a standard Grayhill Series 84S keyboard. A conductive gasket will generally increase the shielding, depending on the size and shape of the gasket and its material. Data derived for E-Field Radiation.

Test Method:

Measurements were made with the keyboard mounted to a brass plate, which in turn was mounted to a shielded enclosure containing the receiving equipment. A signal generator provided the frequency source that was radiated from the transmitting antenna to the enclosed receiving antenna. The spacing between antennas was maintained constant throughout the frequency range. The effectiveness rating is determined by establishing a reference reading without obstruction between the two antennas and determining the difference between that reading and the test setup reading.

Note:

When measured in actual equipment, shielding effectiveness is determined by many factors. This method accurately represents the shielding effectiveness of the Grayhill Series 84S under Ideal test conditions.




Frequency M Hz	Rating in dB
0.1	≥ 66.2
10	≥ 94.8
100	90.5
400	64.2
800	42.3
2,000	40.5
6,000	33.1
10,000	34.4
18,000	37.0


STANDARD LEGENDS

Available through Grayhill Distributors


To order one of the configurations below, use the dash number shown here; select the keypad size and code, and order the part number with the appropriate legend dash number.




-102



-006




-152



-056

ORDERING INFORMATION



Grayhill Series Number

Keyboard Size: A = 3x4, B = 4x4

Circuitry: B2 = Matrix (terminal pin header)

E.L. Panel Backlighting Option

EL = Backlit, Blank = Non-backlit

EMI/RFI Shielding Option

S = Shielded, Blank = Non-shielded

Mounting Option: F = Front panel mount, R = Rear panel mount

Standard Legend Choices

12 Position legends

102 = Black legends on a white button

152 = White legends on a black button

16 Position legends

006 = Black legends on a white button

056 = White legends on a black button

Available from your local Grayhill Distributor.

For prices and discounts, contact a local Sales Office, an authorized local Distributor or Grayhill.