

TO-18 Metal-Can Package Transistors (NPN)

Maximum Ratings							Electrical Characteristics (Ta=25°C, Unless Otherwise Specified)																			
Type No.	V _{CBO} (V) Min	V _{CEO} (V) Min	V _{EBO} (V) Min	P _D (W) @ Tc=25°C	I _C (A)	I _{CM} (A)	I _{CBO} (μA) Max	V _{CB} @ (V)	I _{CES} (μA) Max	V _{CE} @ (V)	h _{FE} Min	@ Max	I _C & (mA)	V _{CE} (V)	V _{CE(SAT)} (V) & Max	V _{BE(SAT)} (V) Max	I _C @ (mA)	C _{ob} (pF) Min	Max	Typ	f _i (MHz) Min	@ Typ	I _C (mA) Max	t _{on} (ns) Max	NF @ Freq (dB) (MHz) Max	
2N2483	60	60	6	0.36		0.05	0.01	45			40	120	0.01	5	0.35		1		6	80		60	80	0.5		15
											75		0.1	5												
											100		0.5	5												
											175		1	5												
											500	10	5													
2N2484	60	60	6	0.36	0.05		0.01	45			250		1	5	0.35		1		6			60	80	0.5		3
											200		0.5	5												
											175		0.1	5												
											100	500	0.01	5												
											30		0.001	5												
											800	10	5													
2N2586	60	45	6	0.3	0.03		0.002	45				600	10	5	0.5	0.7	0.9	10	2			45		0.5		3.5
											150		0.5	5												
											120	360	0.01	5												
											80		1	5												
2N2897	60	45	7	0.5	1		0.05	60			35		1	10	1		1.3	150	15			100		50		
											50	200	150	10												
2N3117	60	60	6	0.36	0.05		0.01	45			400		1	5	0.35		1		4.5			60		0.5		1
											300		0.1	5												
											250	500	0.01	5												
											100		0.001	5												
2N3647	40	10		0.4	0.5		0.025	40			25	150	150	1												
2N3700	140	80	7	0.5	1		0.01	90			100	300	150	10	0.2		1.1	150	12			100		400	50	4 0.001
											90		10	10	0.5		500									
											50		0.1	10												
											50		500	10												
											15		1000	10												
2N6430	200	200	6	0.5	0.05		0.1	160			25		1	10	0.5		0.9	20	4			50		500	10	
											40		10	10												
											50	200	30	10												
2N706	25	15	3	0.3	0.05		0.5	15			20		10	1	0.6		0.9	10	6			200		10	75	
2N706A	25	15	5	0.3	0.05		10	25			20	60	10	1	0.6	0.7	0.9	10	5			200		10	75	
2N708	40	15	5	0.36			0.025	20			30	120	10	1	0.4	0.72	0.8	10	6			300		10	70	
											15		0.5	1												
2N718	60	30	5	0.4	0.5		1	30			40	120	150	10	1.5		1.3	150	35			50		15		
2N718A	75	50	7	0.5	0.5		0.01	60			20		500	10	1.5		1.3	150	25			60		50	12	
											40	120	150	10												
											35		10	10												
											20		0.1	10												
2N720	120	80	5	0.4	0.4		2	60			40	120	150	10	5		1.3	150	20							
2N720A	120	80	7	0.5		0.5	0.01	90			20		0.1	10	1.2		0.9	50	15			50		50		
											35		10	10	5		1.3	150								
											40	120	150	10												
2N834	40	20	5	0.3	0.2		0.5	20	0.01	30	25		10	1	0.25		0.9	10	4			350		10	75	
															0.4		50									
2N910	100	60	7	0.5	1		0.025	75			35		0.1	10	0.4	0.6	0.8	10	15			60		50	12	
											75		10	10	1.2		0.9	50								
2N911	100	60	7	0.5	0.5		0.025	75			20		0.1	10	0.4	0.6	0.8	10				50		50	15	
											75		10	10	1.2		0.9	50								
											15		10	10												