



DO NOT  
SCALE FROM  
THIS PRINT

SLM-1XX-01-X-X



No OF POSITIONS  
-01 THRU -50 (PER ROW)LEAD STYLE  
-01: USE C-29-XBODY SPECIFICATION  
-S: SINGLE (USE HTMS-50-S)  
-D: DOUBLE (USE HTMS-50-D)

## PLATING SPECIFICATION



- G: 20μ" GOLD IN CONTACT AREA, 3μ" GOLD ON TAIL
- T: MATTE TIN CONTACT AND TAIL
- L: 10μ" SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL
- S: 30μ" SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL
- F: 3μ" FLASH SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL
- H: 30μ" HEAVY GOLD IN CONTACT AREA, 3μ" GOLD ON TAIL



(NO OF POSITIONS x .050 [1.27] + .009 [.23] + .005 [.13] )  
(SEE NOTE 6)

SECTION "A"-"A"  
SCALE 4 : 1SECTION "B"-"B"  
SCALE 4 : 1  
(ROTATED 90°)

| PACKAGING TABLE |               |       |
|-----------------|---------------|-------|
| ROW SPEC        | TUBES *       | PLUG  |
| -D: DOUBLE      | PT-1-24-03-09 | TP-09 |
| -S: SINGLE      | PT-1-24-01-12 | TP-12 |



PACKAGING VIEW

## NOTES:

1. Ⓢ REPRESENTS A CRITICAL DIMENSION.
2. MAXIMUM CUT FLASH: .010 [.25]
3. MINIMUM PUSHOUT FORCE: 1 LBS.
4. MAXIMUM ALLOWABLE BOW: .005 IN/IN [.013 MM/MM] (NO FLASH ALLOWED IN HOLES).
5. TUBE ONLY -05 THRU -50 POSITIONS. POSITIONS -01 THRU -04 TO BE BULK PACKAGED.
6. ADDER OF .009 ONLY REQUIRED FOR CUT TO POSITIONS LENGTHS.

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONS ARE IN INCHES.

TOLERANCES ARE:  
DECIMALS ANGLES  
.X: ±.1 [2.5]  
.XX: ±.01 [.3] 2°  
.XXX: ±.005 [.13]  
.XXXX: ±.0020 [.051]

## PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION  
CONFIDENTIAL AND PROPRIETARY TO  
SAMTEC, INC. AND SHALL NOT BE REPRODUCED  
OR TRANSFERRED TO OTHER DOCUMENTS OR  
DISCLOSED TO OTHERS OR USED FOR ANY  
PURPOSE OTHER THAN THAT WHICH IT WAS  
OBTAINED WITHOUT THE EXPRESSED WRITTEN  
CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 2:1

DESCRIPTION:  
LOW PROFILE .050 [1.27] SOCKET STRIP ASM.

DWG. NO.

SLM-1XX-01-X-X

BY:KOLB

1/25/89

SHEET 1 OF 1

**samtec**

520 PARK EAST BLVD., NEW ALBANY, IN 47150  
PHONE: 812-944-6733 FAX: 812-948-5047  
e-Mail: info@SAMTEC.com code 55322