



SEMITRANS® 3

IGBT4 Modules

SKM300GAR12E4

Features


- IGBT4 = 4. generation medium fast trench IGBT (Infineon)
- CAL4 = Soft switching 4. generation CAL-diode
- Isolated copper baseplate using DBC technology (Direct Bonded Copper)
- Increased power cycling capability
- With integrated gate resistor
- For higher switching frequencies up to 12kHz
- UL recognized, file no. E63532

Typical Applications*

- DC/DC – converter
- Brake chopper
- Switched reluctance motor

Remarks

- Case temperature limited to $T_c = 125^\circ\text{C}$ max.
- Recommended $T_{op} = -40 \dots +150^\circ\text{C}$
- Product reliability results valid for $T_j = 150^\circ\text{C}$



GAR

Absolute Maximum Ratings				
Symbol	Conditions		Values	Unit
IGBT				
V _{CES}	T _j = 25 °C		1200	V
I _C	T _j = 175 °C	T _c = 25 °C	422	A
		T _c = 80 °C	324	A
I _{Cnom}			300	A
I _{CRM}	I _{CRM} = 3xI _{Cnom}		900	A
V _{GES}			-20 ... 20	V
t _{psc}	V _{CC} = 800 V V _{GE} ≤ 15 V V _{CES} ≤ 1200 V	T _j = 150 °C	10	µs
T _j			-40 ... 175	°C
Inverse diode				
I _F	T _j = 175 °C	T _c = 25 °C	353	A
		T _c = 80 °C	264	A
I _{Fnom}			300	A
I _{FRM}	I _{FRM} = 3xI _{Fnom}		900	A
I _{FSM}	t _p = 10 ms, sin 180°, T _j = 25 °C		1548	A
T _j			-40 ... 175	°C
Freewheeling diode				
I _F	T _j = 175 °C	T _c = 25 °C	353	A
		T _c = 80 °C	264	A
I _{Fnom}			300	A
I _{FRM}	I _{FRM} = 3xI _{Fnom}		900	A
I _{FSM}	t _p = 10 ms, sin 180°, T _j = 25 °C		1548	A
T _j			-40 ... 175	°C
Module				
I _{t(RMS)}	T _{terminal} = 80 °C		500	A
T _{stg}			-40 ... 125	°C
V _{isol}	AC sinus 50 Hz, t = 1 min		4000	V

Characteristics						
Symbol	Conditions		min.	typ.	max.	Unit
IGBT						
V _{CE(sat)}	I _C = 300 A	T _j = 25 °C		1.85	2.10	V
	V _{GE} = 15 V chiplevel	T _j = 150 °C		2.25	2.45	V
V _{CE0}	chiplevel	T _j = 25 °C		0.8	0.9	V
		T _j = 150 °C		0.7	0.8	V
r _{CE}	V _{GE} = 15 V chiplevel	T _j = 25 °C		3.50	4.00	mΩ
		T _j = 150 °C		5.17	5.50	mΩ
V _{GE(th)}	V _{GE} =V _{CE} , I _C = 12 mA		5	5.8	6.5	V
I _{CES}	V _{GE} = 0 V	T _j = 25 °C			4.0	mA
	V _{CE} = 1200 V	T _j = 150 °C				mA
C _{ies}	V _{CE} = 25 V V _{GE} = 0 V	f = 1 MHz		17.6		nF
C _{oes}		f = 1 MHz		1.16		nF
C _{res}		f = 1 MHz		0.94		nF
Q _G	V _{GE} = - 8 V...+ 15 V			1700		nC
R _{Gint}	T _j = 25 °C			2.5		Ω



SEMITRANS® 3

IGBT4 Modules

SKM300GAR12E4

Features

- IGBT4 = 4. generation medium fast trench IGBT (Infineon)
- CAL4 = Soft switching 4. generation CAL-diode
- Isolated copper baseplate using DBC technology (Direct Bonded Copper)
- Increased power cycling capability
- With integrated gate resistor
- For higher switching frequencies up to 12kHz
- UL recognized, file no. E63532


Typical Applications*

- DC/DC – converter
- Brake chopper
- Switched reluctance motor

Remarks

- Case temperature limited to $T_c = 125^\circ\text{C}$ max.
- Recommended $T_{op} = -40 \dots +150^\circ\text{C}$
- Product reliability results valid for $T_j = 150^\circ\text{C}$

Characteristics						
Symbol	Conditions		min.	typ.	max.	Unit
t _{d(on)}	V _{CC} = 600 V	T _j = 150 °C		220		ns
t _r	I _C = 300 A	T _j = 150 °C		44		ns
E _{on}	V _{GE} = ±15 V	T _j = 150 °C		27		mJ
t _{d(off)}	R _{G on} = 1.5 Ω	T _j = 150 °C		520		ns
t _f	R _{G off} = 1.5 Ω	T _j = 150 °C		117		ns
E _{off}	di/dt _{on} = 6100 A/μs	T _j = 150 °C		39		mJ
	di/dt _{off} = 3000 A/μs	T _j = 150 °C				
R _{th(j-c)}	per IGBT				0.11	K/W
Inverse diode						
V _F = V _{EC}	I _F = 300 A	T _j = 25 °C		2.17	2.49	V
	V _{GE} = 0 V	T _j = 150 °C		2.11	2.42	V
	chipelevel					
V _{F0}	chipelevel	T _j = 25 °C		1.3	1.5	V
		T _j = 150 °C		0.9	1.1	V
r _F	chipelevel	T _j = 25 °C		2.9	3.3	mΩ
		T _j = 150 °C		4.0	4.4	mΩ
I _{RRM}	I _F = 300 A	T _j = 150 °C		345		A
Q _{rr}	di/dt _{off} = 7300 A/μs	T _j = 150 °C		54		μC
E _{rr}	V _{GE} = ±15 V	T _j = 150 °C		23		mJ
	V _{CC} = 600 V					
R _{th(j-c)}	per diode				0.17	K/W
Freewheeling diode						
V _F = V _{EC}	I _F = 300 A	T _j = 25 °C		2.17	2.49	V
	V _{GE} = 0 V	T _j = 150 °C		2.11	2.42	V
	chipelevel					
V _{F0}	chipelevel	T _j = 25 °C		1.3	1.5	V
		T _j = 150 °C		0.9	1.1	V
r _F	chipelevel	T _j = 25 °C		2.9	3.3	mΩ
		T _j = 150 °C		4.0	4.4	mΩ
I _{RRM}	I _F = 300 A	T _j = 150 °C		345		A
Q _{rr}	di/dt _{off} = 7300 A/μs	T _j = 150 °C		54		μC
E _{rr}	V _{GE} = ±15 V	T _j = 150 °C		23		mJ
	V _{CC} = 600 V					
R _{th(j-c)}	per Diode				0.17	K/W
Module						
L _{CE}				15	20	nH
R _{CC'+EE'}	terminal-chip	T _C = 25 °C		0.25		mΩ
		T _C = 125 °C		0.5		mΩ
R _{th(c-s)}	per module			0.02	0.038	K/W
M _s	to heat sink M6		3		5	Nm
M _t		to terminals M6	2.5		5	Nm
						Nm
w					325	g



GAR




Fig. 1: Typ. output characteristic, inclusive $R_{CC'+EE'}$




Fig. 2: Rated current vs. temperature $I_C = f(T_C)$




Fig. 3: Typ. turn-on /-off energy = $f(I_C)$




Fig. 4: Typ. turn-on /-off energy = $f(R_G)$




Fig. 5: Typ. transfer characteristic




Fig. 6: Typ. gate charge characteristic




Fig. 7: Typ. switching times vs. I_C




Fig. 8: Typ. switching times vs. gate resistor R_G




Fig. 9: Transient thermal impedance




Fig. 10: Typ. CAL diode forward charact., incl. $R_{CC'}+EE'$




Fig. 11: CAL diode peak reverse recovery current






Fig. 12: Typ. CAL diode peak reverse recovery charge



SEMITRANS 3



GAR

This is an electrostatic discharge sensitive device (ESDS), international standard IEC 60747-1, Chapter IX

* The specifications of our components may not be considered as an assurance of component characteristics. Components have to be tested for the respective application. Adjustments may be necessary. The use of SEMIKRON products in life support appliances and systems is subject to prior specification and written approval by SEMIKRON. We therefore strongly recommend prior consultation of our staff.