



REV.	DATE	DESCRIPTION
A	08/19/98	MODIFY CONTACT PIN PLATING
B	05/01/04	UPDATE DRAWING FORMAT
C	12/17/07	REVISE BODY LENGTH AND MOUNTING HOLES



				UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex					
8					DRAWN	G.R.S.						12/17/07
7					CHECKED							
6						ISSUED		PART DESCRIPTION N PANEL RECEPTACLE PLUG				
5						SHEET	1 OF 1					
4						PART NO. 172196						
3	INSULATOR	TEFLON	NATURAL		1							
2	CONTACT BODY	BRASS	NEXCOTE		1							
1	BODY WITH PANEL	BRASS	NEXCOTE	1								
	DESCRIPTION	MATERIAL	FINISH	QTY	CAD FILE		DWG. NO.	172196.DWG	REV. C	SIZE A	SCALE NA	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[172196](#)