




2. JACK CAVITY CONFORMS TO FCC RULES AND REGULATIONS PART 68, SUBPART F.

 SUGGESTED PANEL OPENING DIMENSIONS.

△4 SUGGESTED CLEARANCE BETWEEN TOP OF CONNECTOR AND TOP PANEL OPENING.

5. 0.051[.002] WHITE POLYESTER INSULATOR APPLIED TO BACK OF HOUSING.

6 SEE TABLE FOR COLOR OF LEDS AND NUMBER REQUIRED.

7. THIS MODULAR JACK WITH INTEGRATED LED IS NOT IR REFLOW SOLDERING PROCESS COMPATIBLE.

 PACKAGED 30 PIECES PER TUBE. SEE DETAIL "A".

9 MANUFACTURING DATE CODE:
LOCATED APPROX. AS SHOWN.
FIRST 2 DIGITS = LAST 2 DIGITS OF YEAR.
NEXT 2 DIGITS = MANUFACTURING WORK WEEK.
LAST DIGIT = DAY OF WEEK WITH SUNDAY = 1.

10 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



RECOMMENDED PRINTED CIRCUIT BOARD
(COMPONENT SIDE)

		TIN-LEAD	2.54	[.100]		TUBE	GREEN	YELLOW	7-406507-4
		MATTE TIN	3.05	[.120]		TRAY	ORANGE/GREEN	ORANGE/GREEN	3-406507-7
	OBSOLETE	MATTE TIN	3.05	[.120]		TRAY	GREEN	GREEN	3-406507-5
	OBSOLETE	MATTE TIN	3.05	[.120]		TRAY	GREEN	YELLOW	3-406507-4
	OBSOLETE	MATTE TIN	3.05	[.120]		TRAY	YELLOW	GREEN	3-406507-1
		MATTE TIN	2.54	[.100]		TUBE	GREEN	YELLOW	2-406507-4
		MATTE TIN	2.54	[.100]		TRAY	ORANGE/GREEN	ORANGE/GREEN	1-406507-7
	OBSOLETE	MATTE TIN	2.54	[.100]		TRAY	YELLOW	YELLOW	1-406507-6
		MATTE TIN	2.54	[.100]		TRAY	GREEN	GREEN	1-406507-5
		MATTE TIN	2.54	[.100]		TRAY	GREEN	YELLOW	1-406507-4
	OBSOLETE	MATTE TIN	2.54	[.100]		TRAY	YELLOW	-	1-406507-3
	OBSOLETE	MATTE TIN	2.54	[.100]		TRAY	-	GREEN	1-406507-2
		MATTE TIN	2.54	[.100]		TRAY	YELLOW	GREEN	1-406507-1
	OBSOLETE	TIN-LEAD	2.54	[.100]		TRAY	ORANGE/GREEN	ORANGE/GREEN	406507-7
	OBSOLETE	TIN-LEAD	2.54	[.100]		TRAY	YELLOW	YELLOW	406507-6
		TIN-LEAD	2.54	[.100]		TRAY	GREEN	GREEN	406507-5
		TIN-LEAD	2.54	[.100]		TRAY	GREEN	YELLOW	406507-4
	OBSOLETE	TIN-LEAD	2.54	[.100]		TRAY	YELLOW	-	406507-3
	OBSOLETE	TIN-LEAD	2.54	[.100]		TRAY	-	GREEN	406507-2
		TIN-LEAD	2.54	[.100]		TRAY	YELLOW	GREEN	406507-1
		TERMINAL LEAD PLATING	DIM B	SOLDERTAIL LENGTH		PACKAGING	POSITION 2	POSITION 1	
							INDICATOR COLOR		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG T. SPRINKLE 15SEP97 CHK T. SPRINKLE 15SEP97		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES (UNLESS OTHERWISE SPECIFIED) 0 PLC ± - 1 PLC ± - 2 PLC ± 0.25% [01] 3 PLC ± 0.13% [005] 4 PLC ± - 5 PLC ± - 6 PLC ANGLES ± -		NAME APVD M. DERSTINE 09C0CT97 PRODUCT SPEC 108-1163-4 APPLICATION SPEC 114-2154	
		MATERIAL 		INVERTED MODULAR JACK ASSEMBLY, 1X1, SHIELDED, PANEL GROUND, LED, INSULATOR	
FINISH 		WEIGHT -		SIZE CAGE CODE DRAWING NO A1 100779 C-406507	
		CUSTOMER DRAWING		SCALE 4:1 SHEET 1 OF 1 REV K4	