

Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242


The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 1299999

10.00mm (.393") Pitch Mini-Fit Sr.™ Header

42820

**Right Angle, Single Row
Metal Clip Mount**



Features and Benefits

- High current
- Fully polarized
- Positive locks
- Low engagement force
- Wire-to-board
- Metal board retention clip

Reference Information

Product Specification: PS-42815-0001
Packaging: Tray
UL File No.: E29179
CSA File No.: LR19980
TUV License No.: R9751144
Mates With: 42816 receptacle housing
Designed In: Millimeters

Electrical

Voltage: 600V
Current: 48.0A max.*
Contact Resistance: 1.5 milliohms max.
Dielectric Withstanding Voltage: 2200V
Insulation Resistance: 1000 Megohms min.

Mechanical

Insertion Force to PCB: 19.6N max.
Normal Force: 1.96N min.
Durability: 30 cycles

Physical

Housing: Glass-filled, 4/6 nylon, UL 94V-0
Contact: Copper Alloy
Plating: Tin or Select Gold
Operating Temperature: -40 to +105°C
PCB Thickness: 1.57, 2.36, 3.18, or 6.35mm
(.062, .093, .125, or .250")

* Depending on circuit size, wire gauge and PCB. Please refer to product specification.

Circuits	Order No.		PCB Thickness	Retention Clip Length	PC Tail Length	Lead-free
	Tin*	Select Gold				
2	42820-2212	42820-2213	1.57 (.062)	1.80 (.070)	3.50 (.137)	Yes
	42820-2222	42820-2223	2.36 (.093)	2.60 (.102)	5.10 (.200)	
	42820-2232	42820-2233	3.18 (.125)	3.40 (.133)	8.30 (.327)	
	42820-2242	42820-2243	6.35 (.250)	6.58 (.259)	8.30 (.327)	
3	42820-3212	42820-3213	1.57 (.062)	1.80 (.070)	3.50 (.137)	
	42820-3222	42820-3223	2.36 (.093)	2.60 (.102)	5.10 (.200)	
	42820-3232	42820-3233	3.18 (.125)	3.40 (.133)	8.30 (.327)	
	42820-3242	42820-3243	6.35 (.250)	6.58 (.259)	8.30 (.327)	
4	42820-4212	42820-4213	1.57 (.062)	1.80 (.070)	3.50 (.137)	
	42820-4222	42820-4223	2.36 (.093)	2.60 (.102)	5.10 (.200)	
	42820-4232	42820-4233	3.18 (.125)	3.40 (.133)	8.30 (.327)	
	42820-4242	42820-4243	6.35 (.250)	6.58 (.259)	8.30 (.327)	
5	42820-5212	42820-5213	1.57 (.062)	1.80 (.070)	3.50 (.137)	
	42820-5222	42820-5223	2.36 (.093)	2.60 (.102)	5.10 (.200)	
	42820-5232	42820-5233	3.18 (.125)	3.40 (.133)	8.30 (.327)	
	42820-5242	42820-5243	6.35 (.250)	6.58 (.259)	8.30 (.327)	
6	42820-6212	42820-6213	1.57 (.062)	1.80 (.070)	3.50 (.137)	
	42820-6222	42820-6223	2.36 (.093)	2.60 (.102)	5.10 (.200)	
	42820-6232	42820-6233	3.18 (.125)	3.40 (.133)	8.30 (.327)	
	42820-6242	42820-6243	6.35 (.250)	6.58 (.259)	8.30 (.327)	











* Select Gold headers recommended. See product specification for additional information.

molex® 10.00mm (.393") Pitch
Mini-Fit, Sr.™


- Wire-to-Wire (Free hanging and panel mount)
- Wire-to-Board
- Mandatory Terminal Position Assurance (TPA) Piece
- Voltage: 600V
- Current: 50.0A Max.*
- Temperature: -40 to +105°C



10.00mm (.393") Pitch
Mini-Fit, Sr.™

	Series	Description	Mates With/ Use With	Material	Circuits/ Wire Gauge	Features and Benefits
Terminals						
	42817	Male Terminal	Mates with 42815 Terminal Used in 42818 and 43938 Housings	Tin or Select Gold Plated Copper Alloy	8 to 16 AWG	■ Mating Cycles - Tin: 30 / Gold: 100 ■ Four points of electrical contact provide high reliability ■ Low insertion force design for greater ease in mating
	42815	Female Terminal	Mates with 42817 Terminal and PCB Header Terminal Used in 42816 and 43914 Housings			
Single Row Housings						
	42816	Receptacle Housing	42818, 42819, 42820	Black Polyester, UL 94V-0	2, 3, 4, 5, and 6 Circuits	■ TPA (Terminal Position Assurance) piece attached to housing to prevent terminal backouts ■ Positive latch guards against accidental disengagement of housings ■ Polarized housing assures proper mating ■ Used in wire-to-wire and wire-to-board applications ■ TPA (Terminal Position Assurance) clip attached to housing must be used at all times to prevent terminal backouts ■ Used in wire-to-wire applications (Panel Mount or Free Hanging) only
	42818	Plug Housing	42816			
Single Row PC Board Headers						
	42819	Vertical Header	42816	Housings: Black Glass-filled 4/6 Nylon, UL 94V-0 Terminals: Tin or Select Gold Plated Copper Alloy	2, 3, 4, 5 and 6 Circuits	■ SMC (Surface Mount Compatible) ■ Metal fork locks for secure retention to PC Board ■ Accommodates 1.57, 2.36, 3.18 and 6.35mm (.062, .093, .125 and .250") thick PC Boards
	42820	Right Angle Header	42816			
Dual Row Housings						
	43914	Receptacle Housing	43938, 43915	Black Polyester, UL 94V-0	6, 8, 10, 12 and 14 Circuits	■ Mandatory TPA (Terminal Position Assurance) piece (43980 Series) sold separately ■ Positive latch guards against accidental disengagement of housings ■ Polarized housing assures proper mating ■ Used in wire-to-wire or wire-to-board applications ■ Mandatory TPA (Terminal Position Assurance) piece (43980 Series) sold separately ■ Used in wire-to-wire applications (Panel Mount or Free Hanging)
	43938	Plug Housing	43914			
Dual Row TPA (Terminal Position Assurance Piece)						
	43980	TPA	Must Use With 43914, 43938	White Polyester, UL 94V-0	6, 8, 10, 12 and 14 Circuits	■ Virtually eliminates terminal back out. ■ White color for easy activation identification
Dual Row Vertical PC Board Header						
	43915	Vertical Header	43914	Housing: Black Glass-filled 4/6 Nylon, UL 94V-0 Terminals: Tin or Select Gold Plated Copper Alloy	6, 8, 10, 12 and 14 Circuits	■ SMC (Surface Mount Compatible) ■ Metal fork locks for secure retention to PC Board ■ Accommodates 1.57, 2.36, 3.18 and 6.35mm (.062, .093, .125 and .250") Thick PC Boards

*Maximum current is dependent on wire gauge and circuit size. See Mini-Fit, Sr. product specification PS-42815-001.



APPLICATION EXAMPLES

- Servers
- Telecommunications
- Generators
- HVAC
- Workstations
- Welders
- Networking Equipment
- Power Supplies
- UPS Systems
- High Current Applications
- Factory Automation Equipment
- Power Transmission

Americas Headquarters
Lisle, Illinois 60532 U.S.A.
Tel: 1-800-78MOLEX
Fax: 630-969-1352

Far East North Headquarters
Yamato, Kanagawa, Japan
Tel: 81-462-65-2324
Fax: 81-462-65-2366

Far East South Headquarters
Jurong, Singapore
Tel: 65-268-6868
Fax: 65-265-6044

European Headquarters
Munich, Germany
Tel: 49-89-413092-0
Fax: 49-89-401527

Corporate Headquarters
2222 Wellington Ct.
Lisle, IL 60532 U.S.A.
Tel: 630-969-4550
Fax: 630-969-1352

Visit our Web site at <http://www.molex.com>



PRODUCT SPECIFICATION

MINI-FIT SR. SERIES

1.0 SCOPE

This specification covers the 10.00 mm / (.394 in.) centerline tin and gold plated connector series, single and dual row versions in wire to wire and wire to printed circuit board applications. This product performance is optimized for stranded tinned wire termination.

2.0 PRODUCT DESCRIPTION

2.1 PRODUCT NAME AND PART NUMBER

<u>Product Name</u>	<u>Part Number</u>
Female Terminal	42815-****
Male Terminal	42817-****
Receptacle (single row)	42816-****
Plug (single row)	42818-****
Vertical Header (single row)	42819-****
Right Angle Header (single row)	42820-****
Receptacle (dual row)	43914-****
TPA (dual row)	43980-****
Vertical Header (dual row)	43915-****
Panel Mount Plug (dual row)	43938-****

2.2 DIMENSIONS, MATERIALS PLATINGS & MARKINGS.

See the appropriate sales drawings for the information on dimensions, materials, platings and markings.

3.0 APPLICABLE DOCUMENTS AND SPECIFICATIONS

See sales drawings and the other sections of this specification for the necessary referenced documents and specifications.

3.1 Agency Approvals

UL File #E29179

CSA Certificate #LR 19980-555

TUV Certificate #R 9751144, #R 9950481

4.0 RATINGS

4.1 VOLTAGE RATINGS

IEC 950	250 Volts AC (RMS) / DC
UL / CSA	600 Volts AC (RMS) / DC
TUV	250 Volts AC

<u>REVISION:</u> 16	<u>ECR/ECN INFORMATION:</u> <u>EC No:</u> UCP2007-0850 <u>DATE:</u> 2006 / 10 / 05	<u>TITLE:</u> PRODUCT SPECIFICATION FOR MINI-FIT SR. CONNECTOR SYSTEM	<u>SHEET No.</u> 1 of 8
<u>DOCUMENT NUMBER:</u> PS-42815-001	<u>CREATED / REVISED BY:</u> M. CARRANZA	<u>CHECKED BY:</u> J. COMERCI	<u>APPROVED BY:</u> J. COMERCI



PRODUCT SPECIFICATION

4.2 CURRENT RATINGS

Rating is established based on MIL-W-5088 max. current capacity guidelines for copper conductors and test data summary TS-42815-001 section 5.3.7. Test data is based on 30 deg. C temperature rise using tin-plated terminals and UL 1015 tin stranded wire.

Single Row Product (tested to 30degC max. rise)

	2ckt. W to W	2ckt. W to PCB**	6ckt W to W	6ckt. W to PCB**
16 AWG	13A	13A	13A	13A
14 AWG	17A	17A	17A	17A
12 AWG	23A	23A	23A	23A
10 AWG	33A	33A	33A	33A
8 AWG	50A	48A	45A	37A
12AWG Double Crimp	40A (20A per wire)	40A (20A per wire)		

Note: CSA ratings are as follows; 12AWG = 23A max., 10AWG = 30A max.

TUV ratings are as follows; 12AWG = 23A max., 10AWG = 33A max.

**PCB trace design may greatly effect temperature rise results.

Dual Row Product (tested to 30degC max. rise)

	6ckt. W to W	6ckt. W to PCB**	14ckt W to W	14ckt. W to PCB**
16 AWG	13A	13A	13A	12A
14 AWG	17A	17A	17A	16A
12 AWG	23A	23A	23A	22A
10 AWG	32A	31A	29A	28A
8 AWG	43A	37A	38A	36A

**PCB trace design may greatly affect temperature rise results.

4.3 TEMPERATURES

Operating: -40 Degrees C to +105 Degrees C

Non-operating: -40 Degrees C to +105 Degrees C

(Including 30 degrees C terminal temperature at full current)

REVISION:	ECR/ECN INFORMATION:	TITLE:	SHEET No.
16	EC No: UCP2007-0850 DATE: 2006 / 10 / 05	PRODUCT SPECIFICATION FOR MINI-FIT SR. CONNECTOR SYSTEM	2 of 8
DOCUMENT NUMBER:	CREATED / REVISED BY:	CHECKED BY:	APPROVED BY:
PS-42815-001	M. CARRANZA	J. COMERCI	J. COMERCI



PRODUCT SPECIFICATION

5.0 PERFORMANCE

5.1 ELECTRICAL PERFORMANCE

Section	Item	Test Condition	Requirement
5.1.1	Initial Contact Resistance (low level)	Mate connectors, measure by dry circuit, 20mV max., 100mA. Wire resistance shall be removed from the measured value.	1.5 mOhm max. (tin) 1.0 mOhm max. (gold)
5.1.2	Insulation Resistance	Mate connectors, apply 500V DC between adjacent terminal or ground.	1000 M Ohm min.
5.1.3	Dielectric Strength	Mate connectors, apply 2200V AC for 1 minute between adjacent terminal or ground.	No breakdown
5.1.4	Contact Resistance (rated)	Measure contact resistance at rated current.	1.5 mOhm max. (tin) 1.0 mOhm max. (gold)
5.1.5	Contact Resistance on Crimp	Crimp the wire to the terminal, measure crimp resistance by dry circuit, 20mV max., 100mA	1.0 mOhm max.

REVISION:

16

ECR/ECN INFORMATION:

EC No: **UCP2007-0850**

DATE: **2006 / 10 / 05**

TITLE:

PRODUCT SPECIFICATION FOR MINI-FIT SR. CONNECTOR SYSTEM

SHEET No.

3 of 8

DOCUMENT NUMBER:

PS-42815-001

CREATED / REVISED BY:

M. CARRANZA

CHECKED BY:

J. COMERCI

APPROVED BY:

J. COMERCI



PRODUCT SPECIFICATION

5.2 MECHANICAL PERFORMANCE

Section	Item	Test Condition	Requirement
5.2.1	Contact Insertion and Withdrawal	Insert and withdraw a contact at a speed rate of 25 +/- 6mm / minute	Max. Insertion = 3Kg Min. Withdrawal = 0.5Kg
5.2.2	Connector Insertion and Withdrawal	Insert and withdraw a connector at a rate of 25 +/- 6mm / minute	Max. Insertion = 3.0Kg/ckt. Min. Withdrawal = 0.5Kg/ckt.
5.2.3	Terminal Insertion Force	Insert the crimped terminal into the housing.	Max. Insertion = 7.0Kg
5.2.4	Crimp Terminal Retention Force	Apply axial pull out force at a speed rate of 25 +/- 6mm / minute on the terminal assembled in the housing and with the TPA cover installed.	Min. Retention = 10Kg
5.2.5	Header Terminal Retention Force	Apply axial pull out force at a speed rate of 25 +/- 6mm / minute on the terminal assembled in the housing.	Min. Retention = 2.0Kg
5.2.6	Wire Pull Out Force	Mount the crimped terminal, apply an axial pull out force on the wire at a speed rate of 25 +/- 6mm / minute.	16AWG = 14Kg 14AWG = 23Kg 12AWG = 31Kg 10AWG = 36Kg 8AWG = 40Kg
5.2.7	Normal Force	Apply a perpendicular force at a speed rate of 25 +/- 6mm / minute.	200 g min.
5.2.8	PCB Insertion and Withdrawal Force	Apply force perpendicular to the housing at a speed rate of 25 +/- 6mm minute as shown.	Insertion = 2Kg max. Withdrawal = 1Kg min.
5.2.9	Panel Insertion & Withdrawal	Insert and withdraw a connector at a speed rate of 25 +/- 6mm / minute	Insertion = 5Kg max. Withdrawal = 10Kg min.

REVISION:	ECR/ECN INFORMATION:	TITLE:	SHEET No.
16	EC No: UCP2007-0850 DATE: 2006 / 10 / 05	PRODUCT SPECIFICATION FOR MINI-FIT SR. CONNECTOR SYSTEM	4 of 8
DOCUMENT NUMBER:	CREATED / REVISED BY:	CHECKED BY:	APPROVED BY:
PS-42815-001	M. CARRANZA	J. COMERCI	J. COMERCI



PRODUCT SPECIFICATION

5.2 MECHANICAL PERFORMANCE (continued)

Section	Item	Test Condition	Requirement
5.2.10	Latch Yield Strength (only 43914 receptacle w/ 43938 plug)	Insert and withdraw connector housings (30 times) and pull apart at a speed rate of 25 +/- 6mm / minute	Yield = 7.0Kg min.
5.2.10A	Latch Yield Strength (all other)	Insert and withdraw connector housings (30 times) and pull apart at a speed rate of 25 +/- 6mm / minute	Yield = 10.0Kg min.
5.2.11	Durability (tin)	Insert and withdraw connectors (30 times) at a maximum rate of 10 cycles per minute prior to environmental tests.	Contact Res. change = 1.0mOhm max.
5.2.11A	Durability (gold)	Insert and withdraw connectors (100 times) at a maximum rate of 10 cycles per minute prior to environmental tests.	Contact Res. change = 1.0mOhm max.
5.2.12	Vibration without lubrication (tin) Not Recommended	(30 times) at a maximum rate of 10 cycles per minute prior to environmental tests.	Contact Res change =. 4.0mOhm max Discontinuity not greater than 1 microsecond
5.2.12A	Vibration with lubrication (tin) (Nyogel 760G)	Amplitude: 1.50 mm peak to peak Sweep: 10-50-10 Hz in one minute Duration: 2 hours in each X-Y-Z axis.	Contact Res change =. 1.0mOhm max Discontinuity not greater than 1 microsecond
5.2.12B	Vibration without lubrication (gold)	Amplitude: 1.50 mm peak to peak Sweep: 10-55-10 Hz in one minute Duration: 2 hours in each X-Y-Z axis.	Contact Res change =. 1.0mOhm max Discontinuity not greater than 1 microsecond
5.2.13	Mechanical Shock	Sweep: 10-50-10 Hz in one minute Duration: 2 hours in each X-Y-Z axis.	Contact Res. change = 1.0mOhm max. Discontinuity not greater than 1 microsecond

REVISION:	ECR/ECN INFORMATION:	TITLE:	SHEET No.
16	EC No: UCP2007-0850 DATE: 2006 / 10 / 05	PRODUCT SPECIFICATION FOR MINI-FIT SR. CONNECTOR SYSTEM	5 of 8
DOCUMENT NUMBER:	CREATED / REVISED BY:	CHECKED BY:	APPROVED BY:
PS-42815-001	M. CARRANZA	J. COMERCI	J. COMERCI



PRODUCT SPECIFICATION

5.3 ENVIRONMENTAL PERFORMANCE

Section	Item	Test Condition	Requirement
5.3.1	Cold Resistance	-40 +/- 3 degrees C for 96 hrs.	Appearance: No damage Contact Res. change = 1.0mOhm max.
5.3.2	Thermal Shock	Mate connectors, expose to 25 cycles of: -40 +0/-3 deg. C for 30 minutes +25 +/- 10 deg. C for 5 minutes max. +105 +3/-0 deg. C for 30 minutes +25 +/- 10 deg. C for 5 minutes max.	Appearance: No damage Contact Res. change = 1.0mOhm max.
5.3.3	Thermal Aging	Mate connectors, expose to 240 hours at 105 +/- 2 deg. C	Appearance: No damage Contact Res. change = 1.0mOhm max
5.3.4	Humidity (Steady State)	Mate connectors, expose to a temperature of 40 +/- 2 deg. C with a relative humidity of 90% to 95% for 96 hours.	Appearance: No damage Contact Res. change = 1.0mOhm max Dielectric withstanding voltage: No breakdown Insul. res: 1000M Ohm min.
5.3.5	Humidity (cyclic) without lubrication Not Recommended	Mate connectors, expose to 25 cycles at 90% to 95% relative humidity with a transition time of 2.5 hrs. between extremes. +25 +/- 10 deg. C for 5 minutes max. +65 +3/-0 deg. C for 30 minutes	Appearance: No damage Contact Res. change = 2.0mOhm max Dielectric withstanding voltage: No breakdown Insul. res: 1000M Ohm min.

REVISION:	ECR/ECN INFORMATION:	TITLE:	SHEET No.
16	EC No: UCP2007-0850 DATE: 2006 / 10 / 05	PRODUCT SPECIFICATION FOR MINI-FIT SR. CONNECTOR SYSTEM	6 of 8
DOCUMENT NUMBER:	CREATED / REVISED BY:	CHECKED BY:	APPROVED BY:
PS-42815-001	M. CARRANZA	J. COMERCI	J. COMERCI



PRODUCT SPECIFICATION

5.3 ENVIRONMENTAL PERFORMANCE (cont.)

Section	Item	Test Condition	Requirement
5.3.6	Immunity to Fretting Corrosion without lubrication. (tin) Not Recommended	Mate connectors, expose to 500 cycles with a max. transition time of 5 minutes between extremes. +25 +/- 10 deg. C for 30 minutes +70 +3/-0 deg. C for 30 minutes	Appearance: No damage Contact Res. change = 4.0mOhm max
5.3.6A	Immunity to Fretting Corrosion with lubrication. (tin) (Nyogel 760G)	Mate connectors, expose to 500 cycles with a max. transition time of 5 minutes between extremes. +25 +/- 10 deg. C for 30 minutes +70 +3/-0 deg. C for 30 minutes	Appearance: No damage Contact Res. change = 1.0mOhm max
5.3.7	Temp. Rise & Current Cycling	Mate the connectors and measure the temperature rise at the rated current for 96 hrs., 45 minutes ON and 15 minutes OFF for 240 hrs., and an additional 96 hrs. of steady-state current.	Max. Temp. Rise = 30deg. C Per EIA 364 and CSA requirement
5.3.8	Solderability**	Solder time: 3 +/- 5 seconds Solder temp.: 260 +/- 5 deg. C	95% of the immersed area must show no voids or pin holes.
5.3.9	IR Process Resistance	245 +/- 3 deg. C for 4 minutes, allow to cool to room temperature, repeat for 3 cycles. <i>(To deter blistering of housing, parts should be baked for a minimum of 24 hours at 125 +5/-0 deg. C)</i>	Appearance: No damage Dimensional: Conformance to sales drawing requirements.
5.3.10	Resistance to Solder**	Solder time: 3 +/- 0.5 seconds Solder temp.: 260 +/- deg. C	Appearance: No damage

****NOTE :** This product is compatible with lead-free hand soldering temperatures.

REVISION:	ECR/ECN INFORMATION:	TITLE:	SHEET No.
16	EC No: UCP2007-0850 DATE: 2006 / 10 / 05	PRODUCT SPECIFICATION FOR MINI-FIT SR. CONNECTOR SYSTEM	7 of 8
DOCUMENT NUMBER:	CREATED / REVISED BY:	CHECKED BY:	APPROVED BY:
PS-42815-001	M. CARRANZA	J. COMERCI	J. COMERCI



PRODUCT SPECIFICATION

5.3 ENVIRONMENTAL PERFORMANCE (cont.)

Section	Item	Test Condition	Requirement
5.3.11	Resistance to Solvents	Solvent: flourinert FC-70 (3M Corp.) Solvent temp: Boiling temp. Immersion time: 120 +/- 5 seconds Solvent: Alpha 1003 (Alpha Metal) Solvent: Isopropyl Alcohol Solvent Temp.: Boiling temp. Immersion time: 240 +/- 5 seconds Repeat in solvent 5 times. Rinse with deionized water between cycles.	Appearance: No damage

REVISION:

16

ECR/ECN INFORMATION:

EC No: **UCP2007-0850**

DATE: **2006 / 10 / 05**

TITLE:

PRODUCT SPECIFICATION FOR MINI-FIT SR. CONNECTOR SYSTEM

SHEET No.

8 of 8

DOCUMENT NUMBER:

PS-42815-001

CREATED / REVISED BY:

M. CARRANZA



CHECKED BY:

J. COMERCI

APPROVED BY:

J. COMERCI

	20	19	18	17	16
	ITEM NUMBER	CKT. SIZE	DIM. 'A'	DIM. 'B'	DIM. 'C'
M	42820-2212	2	.138/(3.50)	.823/(20.90)	.071/(1.80)
	42820-2219	2	.138/(3.50)	.823/(20.90)	.071/(1.80)
	42820-2222	2	.201/(5.10)	.823/(20.90)	.102/(2.60)
	42820-2232	2	.201/(5.10)	.823/(20.90)	.134/(3.40)
L	42820-2239	2	.201/(5.10)	.823/(20.90)	.134/(3.40)
	42820-2242	2	.327/(8.30)	.823/(20.90)	.259/(6.58)
	42820-3212	3	.138/(3.50)	1.217/(30.90)	.071/(1.80)
	42820-3222	3	.201/(5.10)	1.217/(30.90)	.102/(2.60)
K	42820-3229	3	.201/(5.10)	1.217/(30.90)	.102/(2.60)
	42820-3232	3	.201/(5.10)	1.217/(30.90)	.134/(3.40)
	42820-3242	3	.327/(8.30)	1.217/(30.90)	.259/(6.58)
	42820-4212	4	.138/(3.50)	1.610/(40.90)	.071/(1.80)
J	42820-4222	4	.201/(5.10)	1.610/(40.90)	.102/(2.60)
	42820-4232	4	.201/(5.10)	1.610/(40.90)	.134/(3.40)
	42820-4242	4	.327/(8.30)	1.610/(40.90)	.259/(6.58)
	42820-5212	5	.138/(3.50)	2.004/(50.90)	.071/(1.80)
I	42820-5222	5	.201/(5.10)	2.004/(50.90)	.102/(2.60)
	42820-5232	5	.201/(5.10)	2.004/(50.90)	.134/(3.40)
	42820-5242	5	.327/(8.30)	2.004/(50.90)	.259/(6.58)
	42820-6212	6	.138/(3.50)	2.389/(60.90)	.071/(1.80)
H	42820-6222	6	.201/(5.10)	2.389/(60.90)	.102/(2.60)
	42820-6229	6	.201/(5.10)	2.389/(60.90)	.102/(2.60)
	42820-6232	6	.201/(5.10)	2.389/(60.90)	.134/(3.40)
	42820-6242	6	.327/(8.30)	2.389/(60.90)	.259/(6.58)
G	42820-2332	2	.201/(5.10)	.823/(20.90)	N/A
	42820-2342	2	.327/(8.30)	.823/(20.90)	N/A
	42820-2213	2	.138/(3.50)	.823/(20.90)	.071/(1.80)
	42820-2223	2	.201/(5.10)	.823/(20.90)	.102/(2.60)
F	42820-2233	2	.201/(5.10)	.823/(20.90)	.134/(3.40)
	42820-2243	2	.327/(8.30)	.823/(20.90)	.259/(6.58)
	42820-3213	3	.138/(3.50)	1.217/(30.90)	.071/(1.80)
	42820-3223	3	.201/(5.10)	1.217/(30.90)	.102/(2.60)
E	42820-3233	3	.201/(5.10)	1.217/(30.90)	.134/(3.40)
	42820-3243	3	.327/(8.30)	1.217/(30.90)	.259/(6.58)
	42820-4213	4	.138/(3.50)	1.610/(40.90)	.071/(1.80)
	42820-4223	4	.201/(5.10)	1.610/(40.90)	.102/(2.60)
D	42820-4233	4	.201/(5.10)	1.610/(40.90)	.134/(3.40)
	42820-4243	4	.327/(8.30)	1.610/(40.90)	.259/(6.58)
	42820-5213	5	.138/(3.50)	2.004/(50.90)	.071/(1.80)
	42820-5223	5	.201/(5.10)	2.004/(50.90)	.102/(2.60)
C	42820-5233	5	.201/(5.10)	2.004/(50.90)	.134/(3.40)
	42820-5243	5	.327/(8.30)	2.004/(50.90)	.259/(6.58)
	42820-6213	6	.138/(3.50)	2.389/(60.90)	.071/(1.80)
	42820-6223	6	.201/(5.10)	2.389/(60.90)	.102/(2.60)
B	42820-6233	6	.201/(5.10)	2.389/(60.90)	.134/(3.40)
	42820-6243	6	.327/(8.30)	2.389/(60.90)	.259/(6.58)



LEGEND:

A-42820 - * * *

CIRCUIT SIZE (2-6)

MOUNTING OPTION

1 = FLANGES (SEE DWG. SDA-42820-1**)

2 = RETENTION CLIP

3 = NO RETENTION CLIP

P.C. BOARD THICKNESS

1 = .062/(1.57) NOMINAL

2 = .093/(2.36) NOMINAL


3 = .125/(3.18) NOMINAL

4 = .250/(6.35) NOMINAL

PLATING

2 OR 9 = OVERALL TIN OVER NICKEL

3 = SELECT GOLD IN CONTACT AREA
SELECT TIN ON SOLDER TAILS
OVER NICKEL



NOTES:

1) HOUSING MATERIAL: 30% GLASS-FILLED NYLON 4/6, U.L. 94V-0, COLOR: BLACK.

2) TERMINAL MATERIAL: ALLOY 15L

3) PART MATES WITH MOLEX RECEPTACLE #42816-***2 WITH TPA.

4) PART IS DESIGNED IN METRIC.

5) AN 'X' IN FRONT OF THE ITEM NUMBER INDICATES THE PART IS NOT TOOLED.

6) TERMINAL PLATING : 2= .000100/(.00254) MIN. *TIN OVER .000050/(.00127) MIN. NICKEL.
3= .000030/(.00076) MIN. SELECT GOLD IN CONTACT AREA.
.000100/(.00254) MIN. SELECT *TIN ON SOLDER TAILS
OVER .000050/(.00127) MIN. NICKEL.


* THE PRIMARY SHIPPING CARTON WILL BE LABELED
* COMPLIANT TO ROHS DIRECTIVE 2002/95/EC
AND ELY ANNEX II OF DIRECTIVE 2000/53/EC.
CARTONS WITHOUT THIS LABEL MAY CONTAIN
PRODUCT WITH TIN-LEAD.

7) PARTS ARE NOT TO BE MATED OR UNMATED WHILE CIRCUITS ARE LIVE.


8) WHEN USING OVERALL TIN PLATED TERMINALS:
FOR APPLICATIONS INVOLVING VIBRATION AND/OR THERMAL CYCLING, MOLEX STRONGLY
RECOMMENDS THE USE OF NYE LUBRICANT (NYGEL 760G) ON THE MATING
SURFACES OF THE TERMINAL.

9) FOR PACKAGING INFORMATION SEE MOLEX PACKAGING SPEC. PK-42820-910

RECOMMENDED P.C. BOARD PLATED-THRU HOLE LAYOUT (4 CKT. SHOWN FOR REF.)



HEADER WITH RT. ANGLE TERMINAL & CLIP
ISO VIEW



ADDED -3229 EC NO: UCP2007-0946 2004/10/18 DRAWN: JOMERU 2004/10/18 CHKD: APPR: JOMERU 2004/10/19	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± 0.25 ± --- 1 PLACE ± 0.40 ± --- ANGULAR ±1/2°	DIMENSION STYLE IN/MM DRAWN BY DATE KSM 1/4/196 CHECKED BY DATE SF 1/4/196 APPROVED BY DATE SF 1/4/196	SCALE 4:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	RIGHT ANGLE HEADER ASSEMBLY MINIFIT SR. SERIES MOLEX INCORPORATED	MATERIAL NO. SDA-42820-0002	DOCUMENT NO.	SHEET NO. 1 OF 1