

S5KP SERIES

V_{RM} : 5.0 - 180 Volts

P_{PK} : 5000 Watts

FEATURES :

- * 5000W Peak Pulse Power
- * Excellent clamping capability
- * Low incremental surge resistance
- * Fast response time : typically less than 1.0 ps from 0 volt to V_{BR(min.)}
- * Pb / RoHS Free

MECHANICAL DATA

- * Case : D²PAK(TO-263)
- * Epoxy : UL94V-O rate flame retardant
- * Lead : Surface Mount per J-STD-020C, Method 208 guaranteed
- * Polarity : Heatsink is Anode
- * Mounting position : Any
- * Weight : 1.7 grams (approximately)


DEVICES FOR BIPOLAR APPLICATIONS

For Bi-directional use C or CA Suffix

Electrical characteristics apply in both directions

SURFACE MOUNT TRANSIENT VOLTAGE SUPPRESSOR

**** Under Development ****



MAXIMUM RATINGS

Rating at 25 °C ambient temperature unless otherwise specified

Rating	Symbol	Value	Unit
Peak Pulse Power Dissipation at tp = 1ms (Note 1, Fig. 4)	P _{PK}	Minimum 5000	W
Steady State Power Dissipation	P _D	5.0	W
Peak Forward Surge Current, 8.3ms Single Half Sine-Wave Superimposed on Rated Load (JEDEC Method) (Note 2)	I _{FSM}	400	A
Operating and Storage Temperature Range	T _J , T _{STG}	- 55 to + 150	°C

Notes:

- (1) Non-repetitive Current pulse, per Fig. 5 and derated above Ta = 25 °C per Fig. 1
- (2) Measured on 8.3 ms single half sine-wave or equivalent square wave, duty cycle = 4 pulses per minutes maximum.

ELECTRICAL CHARACTERISTICS (Ta = 25°C)

TYPE	Breakdown Voltage @ I_T (Note 1)		Reverse Stand off Voltage	Maximum Reverse Leakage @ V_{RM}	Maximum Peak Pulse Current ⁽²⁾	Maximum Clamping Voltage @ I_{PPM}	Maximum Temperature Coefficient of V_{BR} (%/°C)
	V_{BR} (V)		I_T	V_{RM}	I_R	I_{PPM}	V_C
	Min.	Max.	(mA)	(V)	(μA)	(A)	(V)
S5KP5.0	6.40	7.30	50	5.0	5000	520	9.60
S5KP5.0A	6.40	7.00	50	5.0	5000	543	9.20
S5KP6.0	6.67	8.15	50	6.0	5000	439	11.4
S5KP6.0A	6.67	7.37	50	6.0	5000	485	10.3
S5KP6.5	7.22	8.82	50	6.5	2000	407	12.3
S5KP6.5A	7.22	7.98	50	6.5	2000	447	11.2
S5KP7.0	7.78	9.51	5.0	7.0	1000	378	13.3
S5KP7.0A	7.78	8.60	5.0	7.0	1000	417	12.0
S5KP7.5	8.33	10.2	5.0	7.5	250	350	14.3
S5KP7.5A	8.33	9.21	5.0	7.5	250	388	12.9
S5KP8.0	8.89	10.9	5.0	8.0	150	333	15.0
S5KP8.0A	8.89	9.83	5.0	8.0	150	367	13.6
S5KP8.5	9.44	11.5	5.0	8.5	50	314	15.9
S5KP8.5A	9.44	10.4	5.0	8.5	50	347	14.4
S5KP9.0	10.0	12.2	5.0	9.0	20	295	16.9
S5KP9.0A	10.0	11.1	5.0	9.0	20	325	15.4
S5KP10	11.1	13.6	5.0	10	15	266	18.8
S5KP10A	11.1	12.3	5.0	10	15	294	17.0
S5KP11	12.2	14.9	5.0	11	10	249	20.1
S5KP11A	12.2	13.5	5.0	11	10	274	18.2
S5KP12	13.3	16.3	5.0	12	10	227	22.0
S5KP12A	13.3	14.7	5.0	12	10	251	19.9
S5KP13	14.4	17.6	5.0	13	10	210	23.8
S5KP13A	14.4	15.9	5.0	13	10	232	21.5
S5KP14	15.6	19.1	5.0	14	10	194	25.8
S5KP14A	15.6	17.2	5.0	14	10	215	23.2
S5KP15	16.7	20.4	5.0	15	10	188	26.9
S5KP15A	16.7	18.5	5.0	15	10	206	24.4
S5KP16	17.8	21.8	5.0	16	10	176	28.8
S5KP16A	17.8	19.7	5.0	16	10	192	26.0
S5KP17	18.9	23.1	5.0	17	10	164	30.5
S5KP17A	18.9	20.9	5.0	17	10	181	27.6
S5KP18	20.0	24.4	5.0	18	10	155	32.2
S5KP18A	20.0	22.1	5.0	18	10	172	29.2
S5KP20	22.2	27.1	5.0	20	10	139	35.8
S5KP20A	22.2	24.5	5.0	20	10	154	32.4
S5KP22	24.4	29.8	5.0	22	10	127	39.4
S5KP22A	24.4	26.9	5.0	22	10	141	35.5
S5KP24	26.7	32.6	5.0	24	10	116	43.0
S5KP24A	26.7	29.5	5.0	24	10	128	38.9
S5KP26	28.9	35.3	5.0	26	10	107	46.6
S5KP26A	28.9	31.9	5.0	26	10	119	42.1
S5KP28	31.1	38.0	5.0	28	10	99	50.1
S5KP28A	31.1	34.4	5.0	28	10	110	45.4
S5KP30	33.3	40.7	5.0	30	10	93	53.5
S5KP30A	33.3	36.8	5.0	30	10	103	48.4
S5KP33	36.7	44.9	5.0	33	10	85	59.0
S5KP33A	36.7	40.6	5.0	33	10	94	53.3
S5KP36	40.0	48.9	5.0	36	10	78	64.3
S5KP36A	40.0	44.2	5.0	36	10	86	58.1

ELECTRICAL CHARACTERISTICS (Ta = 25°C)

TYPE	Breakdown Voltage @ I _T (Note 1)			Reverse Stand off Voltage V _{RM} (V)	Maximum Reverse Leakage @ V _{RM} I _R (μA)	Maximum Peak Pulse Current ⁽²⁾ I _{PPM} (A)	Maximum Clamping Voltage @ I _{PPM} V _C (V)	Maximum Temperature Coefficient of V _{BR} (%/°C)
	V _{BR} (V)		I _T					
	Min.	Max.	(mA)					
S5KP40	44.4	54.3	5.0	40	10	70	71.4	0.105
S5KP40A	44.4	49.1	5.0	40	10	78	64.5	0.105
S5KP43	47.8	58.4	5.0	43	10	65	76.7	0.105
S5KP43A	47.8	52.8	5.0	43	10	72	69.4	0.105
S5KP45	50.0	61.1	5.0	45	10	62	80.3	0.106
S5KP45A	50.0	55.3	5.0	45	10	69	72.7	0.106
S5KP48	53.3	65.2	5.0	48	10	58	85.5	0.106
S5KP48A	53.3	58.9	5.0	48	10	65	77.4	0.106
S5KP51	56.7	69.3	5.0	51	10	55	91.1	0.107
S5KP51A	56.7	62.7	5.0	51	10	61	82.4	0.107
S5KP54	60.0	73.3	5.0	54	10	52	96.3	0.107
S5KP54A	60.0	66.3	5.0	54	10	57	87.1	0.107
S5KP56	62.2	76.1	5.0	56	10	50	100	0.107
S5KP56A	62.2	68.8	5.0	56	10	55	91	0.107
S5KP58	64.4	78.7	5.0	58	10	49	103	0.107
S5KP58A	64.4	71.2	5.0	58	10	53	94	0.107
S5KP60	66.7	81.5	5.0	60	10	47	107	0.108
S5KP60A	66.7	73.7	5.0	60	10	52	97	0.108
S5KP64	71.1	96.9	5.0	64	10	44	114	0.108
S5KP64A	71.1	78.6	5.0	64	10	49	103	0.108
S5KP70	77.6	95.1	5.0	70	10	40	125	0.108
S5KP70A	77.6	86.0	5.0	70	10	44	113	0.108
S5KP75	83.3	102	5.0	75	10	37	134	0.108
S5KP75A	83.3	92.1	5.0	75	10	41	121	0.108
S5KP78	86.7	106	5.0	78	10	36	139	0.108
S5KP78A	86.7	95.8	5.0	78	10	40	126	0.108
S5KP85	94.4	115	5.0	85	10	33	151	0.108
S5KP85A	94.4	104	5.0	85	10	36	137	0.110
S5KP90	100	122	5.0	90	10	31	160	0.110
S5KP90A	100	111	5.0	90	10	34	146	0.110
S5KP100	111	136	5.0	100	10	28	179	0.110
S5KP100A	111	123	5.0	100	10	31	162	0.110
S5KP110	122	149	5.0	110	10	26	196	0.112
S5KP110A	122	135	5.0	110	10	28	177	0.112
S5KP120	133	163	5.0	120	10	24	211	0.112
S5KP120A	133	147	5.0	120	10	26	194	0.112
S5KP150	167	204	5.0	150	10	19	263	0.112
S5KP150A	167	184	5.0	150	10	21	242	0.112
S5KP160	178	217	5.0	160	10	18	281	0.114
S5KP160A	178	196	5.0	160	10	19	258	0.114
S5KP170	189	231	5.0	170	10	17	298	0.114
S5KP170A	189	209	5.0	170	10	18	274	0.114
S5KP180	200	244	5.0	180	10	16	316	0.114
S5KP180A	200	221	5.0	180	10	17	290	0.114

Notes:

- (1) V_{BR} measured after I_T applied for 300 $\mu s.$, I_T = square wave pulse or equivalent.
- (2) Surge Current waveform per Fig. 5.
- (3) V_F = 3.5 Volts max. for devices of V_R < 100 V, and V_F = 5 Volts max. for devices of V_R > 100 V.
- (4) For Bi-directional devices having V_R of 10 Volts and under the IR limit is doubled.
- (5) " S KP " will be omitted in marking on the diode.

RATING AND CHARACTERISTIC CURVES (S5KP SERIES)

FIG.1 - PULSE DERATING CURVE




FIG.2 - MAXIMUM NON-REPETITIVE
PEAK FORWARD SURGE CURRENT




FIG.3 - STEADY STATE POWER DERATING




FIG.4 - PEAK PULSE POWER RATING CURVE




FIG.5 - PULSE WAVEFORM

