






NOTES:

1. MATERIAL:

HSG: LCP, GLASS-FILLED, UL94V-0, COLOR:BLACK
PIN: 0.50mm SQ, COPPER ALLOY

2. PLATING:

- (1) 2.54μm TIN OVERALL PLATING
OVER NICKEL OVERALL
- (2) 5.08μm TIN OVERALL PLATING
OVER NICKEL OVERALL

3. PACKAGING TYPE: SEE TABLE

4. PACKAGING SPECIFICATION:

TRAY: PK-89990-487
TAPE & REEL: PK-89990-484

5. PRODUCT SPEC PS-87761-100 APPLIES

6. IRREGULAR CIRCUIT CUTOFF WITHIN BREAKAWAY SECTION IS PERMISSIBLE. MEASUREMENT AT BOTH ENDS, FROM CUT END TO THE CENTRELINE OF THE HOUSING CORE HOLE OF THE FIRST PIN REMAINS AT 0.95±0.20MM. CUTTING AND CHIPPING OF THE MAIN BODY IS NOT ACCEPTABLE.

7. THE ABOVE CKT 5 IS FOR ILLUSTRATION PURPOSE ONLY

8. COPLANARITY IS TO BE MEASURED BY RESTING THE SOLDER TAIL ON A GAUGE SURFACE

9. KAPTON TAPE LOCATION IS CENTRED AT THE PART AS POSSIBLE.


10. RECOMMENDED PCB BOARD THICKNESS: 1.60±0.10mm

EWR:HSG MODIFICATION EC NO: S2009-0295 DRWN:ATSEE CHKD:SKANG APPR:MLONG		2009/02/09 2009/02/10 2009/02/11	DESCRIPTION	QUALITY SYMBOLS ▽=0 ∇=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION 	
</												

10 9 8 7 6 5 4 3 2 1

CKT	DIMENSION					PACKABLE
	BoA	Ao	K2	F	W	QTY
5	11.20	8.50	4.40	11.50	24.00	1200
7	15.20	8.50	4.40	11.50	24.00	1200

TAPE AND REEL INFORMATION




SECTION X-X


PART IN
TAPE & REEL
ORIENTATION
(FOR REF. ONLY)

NOTES:

1. LEADER AND TRAILER TAPE



2. PEELING OFF FORCE OF THE TOP TAPE: 20-80gf. (PEELING DIRECTION AS SHOWN IN FOLLOWING FIGURE)



3. MATERIAL: BLACK P.S CONDUCTIVE

4. PACKAGING STANDARD IS AS PER EIA-481.

5. THE TAPE IS TREATED FOR ANTI-STATIC.

EWRHSG MODIFICATION EC NO: S2009-0295 DRWN:ATSEE 2009/02/09 CHKD:SKANG 2009/02/10 APPR:MLONG 2009/02/11	QUALITY SYMBOLS ▽=0 ⌒=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 1:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION		
				mm	INCH	DRAWN BY CWLAM	DATE 2007/12/04	TITLE 2MM SINGLE ROW HDR (ODD) SMT WITH PEG, BREAKAWAY		
						CHECKED BY KWLEE	DATE 2007/12/17			
				4 PLACES ± ---	± ---			MOLEX INCORPORATED		
				3 PLACES ± ---	± ---					
				2 PLACES ± 0.2	± ---			DOCUMENT NO. SD-87858-022		
				1 PLACE ± ---	± ---					
				ANGULAR ± 3 °		APPROVED BY KWLEE		DATE 2007/12/17	SHEET NO. 3 OF 3	
						MATERIAL NO.				
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE				
						SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		