

10 9 8 7 6 5 4 3 2 1

F

E

D

C

B

A

F

E

D



C

B


A

NOTES.


1. 適合ハウジング: 504051****
APPLICABLE HOUSING : 504051****
2. 材質: 銅合金
MATERIAL : COPPER ALLOY
3. メッキ仕様: 金メッキ、ニッケル下地
PLATING : GOLD PLATING
NICKEL UNDER PLATING
4. 圧着後、CS-504052-001の内容を満たす事
FULFILL THE CONTENTS OF
CS-504052-001 AFTER CRIMP



SECTION A-A



SECTION B-B



φ0.8 - 1.1mm	AWG #24 - 28	5040520098	CHAIN
INS. RANGE	WIRE RANGE	ORDER No.	FORM

RELEASED EC NO: J2014-1702 DRWN:YMAKE CHKD:KASAKAWA APPR:NUKITA	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 20:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
		10 UNDER	± 0.2	DRAWN BY THANYU	DATE 2012/03/29	TITLE 1.5 WIRE TO BOARD CONN. REC CRIMP TERMINAL (AWG #24 - 28)				
		10 OVER 30 UNDER	± 0.25	CHECKED BY KASAKAWA	DATE 2012/03/29					
		30 OVER	± 0.3	APPROVED BY YOITO	DATE 2012/09/04	DOCUMENT NO. SD-504052-001				
		ANGULAR ±3 °		MATERIAL NO. SEE CHART						
	REV	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						

9 8 7 6 5 4 3 2