


PHOTONIC DETECTORS INC.

Silicon Photodiode, Filter Combination Photovoltaic 600 nm (red color) Type PDV-V403



FEATURES

- 600 nm CWL
- 65 nm FWHM
- Low noise

DESCRIPTION: The **PDV-V403** is a silicon, PIN planardiffused, photodiode with a red color 600 nm +/- 2 nm CWL wide band interference filter and a 65 nm half band-width. Ideal for photometry and radiometry measurement applications.

APPLICATIONS


- Red color matching
- Color meters
- Film processing

ABSOLUTE MAXIMUM RATING (TA=25°C unless otherwise noted)

SYMBOL	PARAMETER	MIN	MAX	UNITS
V _{BR}	Reverse Voltage		100	V
T _{STG}	Storage Temperature	-20	+85	°C
T _O	Operating Temperature Range	-15	+70	°C
T _S	Soldering Temperature*		+240	°C
I _L	Light Current		0.5	mA

*1/16 inch from case for 3 secs max

SPECTRAL RESPONSE



ELECTRO-OPTICAL CHARACTERISTICS (TA=25°C unless otherwise noted)

SYMBOL	CHARACTERISTIC	TEST CONDITIONS	MIN	TYP	MAX	UNITS
I _{SC}	Short Circuit Current***	H = 100 fc, 2850 K	150	200		μA
I _D	Dark Current	H = 0, V _R = 10 mV		10	50	pA
R _{SH}	Shunt Resistance	H = 0, V _R = 10 mV	.20	2		GΩ
TC R _{SH}	R _{SH} Temp. Coefficient	H = 0, V _R = 10 mV		-8		% / °C
C _J	Junction Capacitance	H = 0, V _R = 10 V**		1700		pF
CWL	Center Wavelength	(CWL, λ ₀) +/- 2 nm		600		nm
HBW	Half Bandwidth	(FWHM)		65		nm
V _{BR}	Breakdown Voltage	I = 10 μA	50	75		V
N EP	Noise Equivalent Power	V _R = 10 mV @ Peak		9x10 ⁻¹⁵		W/√Hz
tr	Response Time	RL = 1 KΩ V _R = 10 V		1.0		μS

Information in this technical data sheet is believed to be correct and reliable. However, no responsibility is assumed for possible inaccuracies or omission. Specifications are subject to change without notice.**1 = 1 MHz, ***without filter

[FORM NO. 100-PDV-V403 REV A]