






5 x 20 mm		F = No. 120.900	(DIN 41661 / EN 60127-2-2)		
		M = No. 121.800	(DIN 41571/2)		
		T = No. 122.800	(DIN 41662 / EN 60127-2-3)		
Inhalt:	100 St./pcs.:	10 x 160 mA	10 x	1	A
contents:		10 x 250 mA	10 x	1,6	A
contenu:		10 x 500 mA	10 x	2,5	A
		10 x 630 mA	10 x	4	A
		10 x 800 mA	10 x	6,3	A



5 x 20 mm		F = No. 520 .800	(DIN 41661 / EN 60127-2-2)	
		M = No. 521 .800	(DIN 41571/2)	
		T = No. 522 .800	(DIN 41662 / EN 60127-2-3)	
Inhalt:	200 St./ pcs.:	10 x 100 mA	20 x	800 mA
contents:		10 x 200 mA	30 x	1 A
contenu:		10 x 315 mA	10 x	1,25 A
		10 x 400 mA	20 x	1,6 A
		30 x 500 mA	10 x	2,5 A
		20 x 630 mA	10 x	4 A
			10 x	6.3 A



5 x 20 mm		F = No. E3520 .800	(DIN 41661 / EN 60127-2-2)		
		M = No. E3521 .800	(DIN 41571/2)		
		T = No. E3522 .800	(DIN 41662 / EN 60127-2-3)		
Inhalt:	360 St./pcs.:	20 x 100 mA	20 x	800	mA
contents:		20 x 125 mA	20 x	1	A
contenu:		20 x 160 mA	20 x	1,25	A
		20 x 200 mA	20 x	1,6	A
		20 x 250 mA	20 x	2	A
		20 x 315 mA	20 x	2,5	A
		20 x 400 mA	20 x	3,15	A
		20 x 500 mA	20 x	4	A
		20 x 630 mA	20 x	6,3	A



6,3 x 32 mm		F = No. 632.800 M = No. 632.820 T = No. 632.830			
Inhalt:	120 St./pcs.:	10 x 315 mA	10 x	2	A
contents:		10 x 500 mA	10 x	2,5	A
contenu:		10 x 800 mA	10 x	4	A
		10 x 1 A	10 x	5	A
		10 x 1,25 A	10 x	6,3	A
		10 x 1.6 A	10 x	10	A