










NOTES

- 1 - NOTED ELECTRICAL RATING APPLY AS SPECIFIED IN MIL-PRF-8805/40-1 UP TO 185°F
- 2 - SWITCH SEALED PER MIL-PRF-8805, SYMBOL 4
- 3 - CORROSION RESISTANT STEEL SHAFT, BUSHING AND PINS
- 4 - DO NOT APPLY MORE THAN 20-25 INCH-POUNDS OF TORQUE WHEN TIGHTENING LOCKING NUT
- 5 - CIRCUIT DIAGRAM, CAT LISTING, AND FCSM NO. ARE MARKED ON SWITCH
- 6 - HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-PRF-8805
- 7 - REPLACEMENT MOUNTING HARDWARE - PACKET 19PA10
- 8 - .050 WIDE X .050 DEEP SLOT
- 9 - Ø.037 HOLE FOR WIRE LOCKING



CHARACTERISTICS		ELECTRICAL DATA		
OPERATING TORQUE ----- 12-25 IN LB		CONTACT ARRANGEMENT		
RELEASE TORQUE ----- 9 IN LB MIN		2X S P D T (SEE CIRCUIT DIAGRAM)		
PRETRAVEL _____		LOAD	28 VDC	
 SEE DETAIL			SEA LEVEL	
		RES	4	4
		IND	2	2
		MOTOR	4	

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH. A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

MICRO SWITCH
a Honeywell Division


FED MEG CODE 91939

SWITCH - ENCLOSED

CATALOG LISTING

131EN92-R

THIRD ANGLE PROJECTION



DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE

ONE PLACE	(.0)	± .030
TWO PLACES	(.00)	± .015
THREE PLACES	(.000)	± .005
ANGLES		±

WEIGHT 12.0 OZ MAX

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[131EN92-R](#)