

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	R1	REVISED PER ECN-25-315398	07APR2025	MM	LR





TABLE OF DIMENSIONS

PART NUMBER	H		J		K		P	R	W	X	Weight	This Boot Fits		
	Min	±5%	Min	±5%	Min	Max						Nom	Cannon/Cinch	Amphenol Series 17
	a	b	a	b	a	b								
214A011	<u>.85</u> [20,3]	<u>.80</u> [20,3]	<u>.47</u> [10,7]	<u>.42</u> [10,7]	<u>.31</u> [7,9]	<u>.16</u> [4,1]	<u>1.31</u> [33,3]	<u>.75</u> [19,1]	<u>.04</u> [1,0]	<u>.12</u> [3,0]	<u>.0044</u> [2,0]	DE-9	XX09X	
214A021	<u>1.16</u> [28,2]	<u>1.11</u> [28,2]	<u>.47</u> [10,7]	<u>.42</u> [10,7]	<u>.40</u> [10,2]	<u>.21</u> [5,3]	<u>1.53</u> [38,9]	<u>.87</u> [22,1]	<u>.04</u> [1,0]	<u>.12</u> [3,0]	<u>.0057</u> [2,6]	DA-15	XX15X	
214A032	<u>1.71</u> [42,2]	<u>1.66</u> [42,2]	<u>.47</u> [10,7]	<u>.42</u> [10,7]	<u>.55</u> [14,0]	<u>.32</u> [8,1]	<u>1.77</u> [45,0]	<u>1.00</u> [25,4]	<u>.04</u> [1,0]	<u>.12</u> [3,0]	<u>.0088</u> [4,0]	DB-25	XX25X	
214A042	<u>2.36</u> [58,7]	<u>2.31</u> [58,7]	<u>.47</u> [10,7]	<u>.42</u> [10,7]	<u>.68</u> [17,3]	<u>.34</u> [8,6]	<u>2.10</u> [53,3]	<u>1.12</u> [28,4]	<u>.04</u> [1,0]	<u>.12</u> [3,0]	<u>.0148</u> [6,7]	DC-37	XX37X	
214A052	<u>2.32</u> [57,9]	<u>2.28</u> [57,9]	<u>.58</u> [13,7]	<u>.54</u> [13,7]	<u>.75</u> [19,1]	<u>.42</u> [10,7]	<u>2.40</u> [61,0]	<u>1.25</u> [31,8]	<u>.04</u> [1,0]	<u>.12</u> [3,0]	<u>.0159</u> [7,2]	DD-50	XX50X	

TE Connectivity. All Rights Reserved.

I



DIMENSIONS:

INCHES

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -


1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -



DWN

07APR2025

CHK

01APR2025

APVD

01APR2025

L RODRIGUEZ

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

0.000000

MATERIAL

-

FINISH

-



TE Connectivity

NAME

BOOT, RECTANGULAR,
SUBMINIATURE, STRAIGHT

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A4

06090

C-214A011THRU052

-

CUSTOMER DRAWING

SCALE

DNS

SHEET

1 OF 2

REV R1

*VITON is a Registered Trademark of Dupont

214A0XX -XXX -XX /XXX -0

Base part number

Material dash number
(See Compatibility Chart)

Modification number

Adhesive slash number
(If necessary, see Compatibility Chart)


Color Designator

1. All dimensions are in $\frac{\text{inches}}{[\text{millimeters}]}$; $\frac{\text{lbs}}{[\text{gms}]}$

2. Dimensions appearing in table are as follows:
 - a - As Supplied
 - b - After Unrestricted Recovery
3. Coating is optional. As supplied dimensions appearing in table are for uncoated parts. When coating is added, entry diameters will be reduced by .06 max.
4. Molding ports are optional. When -00 modification number is specified molding ports will be located as shown.
5. Molding shown in table of dimensions is based on polyolefin part.

TE Connectivity. All Rights Reserved.



DIMENSIONS:		DWN	07APR2025		MATERIAL		FINISH	
INCHES		CHK	—		 TE Connectivity			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	—					
0 PLC	± —	PRODUCT SPEC			NAME			
1 PLC	± —	—			—			
2 PLC	± —	APPLICATION SPEC			—			
3 PLC	± —	—			SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
4 PLC	± —	—			A4	06090	C-214A011THRU052	—
ANGLES	± —	WEIGHT			0.000000			
		CUSTOMER DRAWING					SCALE	DNS
							SHEET	2 of 2
							REV	R1