



RECOMMENDED PCB LAYOUT



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: $X.X = \pm 0.4$
 $X.XX = \pm 0.25$
3. TERM. NOS. FOR REFERENCE ONLY.
4. RATING: 0.1A @30V DC
5. MATERIALS:

CONTACT/TERMINAL: SILVER PLATED COPPER ALLOY

HOUSING/PLUNGER: UL94HB

6. CONTACT RESISTANCE: 0.1 MAX.

7. TIMING: NON-SHORTING (BBW)


8. OPERATING FORCE: 300±100g

9. TRAVEL: 2mm (TRAVEL TO LOCK)

3mm (OVERALL)

10. ELECTRICAL LIFE: >10,000

11. DIELECTRIC STRENGTH: 250V RMS



TITLE				E-SWITCH®			
D	11999	REVISED AND REDRAWN	3/14/02	CJB	SCALE	DATE	DR
REV.	ECN No.	DESCRIPTION	DATE	CHKD	1.5:1	3/14/02	CJB
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED				MTH6U EE N AGX (LATCHING)			
				A960010			
				REV D			