

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

,19

© COPYRIGHT 19

BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

LOC

DIST

P

F

ZONE

LTR

REVISIONS

DESCRIPTION

DATE

APPD

AF

50


H

REV PER 0G3A-0677-02

12NOV02

JR/ND

- 1 SUPPLIED IN LOOSE PIECE
- 2 0.41 [.016] THK 1/4 HARD S.STEEL WITH 0.102 [.004] THK COPPER CLAD, THIS SIDE ONLY.
- 3 DIM APPLIES AT TANGENT OF RADIUS AT BASE.
- 4 CLEANING PROCESS NOT INCLUDED.
- 5 0.51 [.020] THK 1/4 HARD S.STEEL
- 6 PRELIMINARY - NOT FOR PRODUCTION.



DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN mm [INCHES]
TOLERANCES ON:
2 PLC DEC ± 0.25 [.010]
3 PLC DEC ± .1
ANGLES ± 1°

MATERIAL

SEE TABLE

FINISH

SEE TABLE

DR 11/14/87

JR RUTH

CHK 11/14/87

MS FEHER

APPD 11/14/87

P DESANTIS

APPD 11/14/87

D BRATINA

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

FINISH

MATERIAL

PART NO

AMP

AMP Incorporated
Harrisburg, PA 17105-3608

NAME

TAB, SPECIAL, 4.75 [.187] SERIES

SIZE

CAGE CODE

DRAWING NO

B

00779

C=63953

SCALE 3:1

SHEET

1 OF 1

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.