

**Model 6741
BNC (F) Bulkhead, Isolated Ground – 75 Ω**



Model 6741 BNC (F) Bulkhead, Isolated ground

**Employ 75 Ω bulkhead jacks
in your broadcast system
applications**

Features



- U-shaped solder cup eases solder installation. Precision machined.
- Mounting hardware is isolated from outer conductor of BNC.
- Precision machined.
- Gold-plated contacts.
- Dielectric is PTFE (**not delrin**).

Materials

- Machined brass with tarnish resistant nickel plating.
- Male center pin contacts are gold-plated (20 micro inches) brass. Female center contacts are gold-plated, heat-treated beryllium copper.
- Body made from precision machined high quality brass (not die cast).
- High quality machined PTFE dielectric.

Ordering Information

Model: 6741 75 Ω BNC (F), Isolated ground



PANEL CUTOUT

Specifications

Nominal impedance	75 Ω
Frequency	0-3 GHz
VSWR	1.10 max. 0-1 GHz 1.35 max. 1-3 GHz
Center contact resistance	1.5 mΩ
Insulation resistance	5000 MΩ
Number of insertions	500
Ratings: Voltage: 500 Vrms Operating temperature: -85 °F to +131 °F (-65 °C to +155 °C) Max.	

USA: Sales: 800-490-2361 Technical Support: 800-241-2060 Fax: 888-403-3360

Europe: 31-(0) 40 2675 150 **International:** 425-446-5500
e-mail: technicalsupport@pomonatest.com

Where to Buy: www.pomonaelectronics.com

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.