

NCP4421, NCP4422

9.0 A High-Speed MOSFET Drivers

The NCP4421/4422 are high current buffer/drivers capable of driving large MOSFETs and IGBTs.

They are essentially immune to any form of upset except direct overvoltage or over-dissipation – they cannot be latched under any conditions within their power and voltage ratings; they are not subject to damage or improper operation when up to 5.0 V of ground bounce is present on their ground terminals; they can accept, without either damage or logic upset, more than 1.0 A inductive current of either polarity being forced back into their outputs. In addition, all terminals are fully protected against up to 4.0 kV of electrostatic discharge.


The inputs may be driven directly from either TTL or CMOS (3.0 V to 18 V). In addition, 300 mV of hysteresis is built into the input, providing noise immunity and allowing the device to be driven from slowly rising or falling waveforms.

Features

- Tough CMOS™ Construction
- High Peak Output Current (9.0 A)
- High Continuous Output Current (2.0 A Max)
- Fast Rise and Fall Times:
 - 30 ns with 4,700 pF Load
 - 180 ns with 47,000 pF Load
- Short Internal Delays (30 nsec Typ)
- Low Output Impedance (1.4 Ω Typ)


Applications

- Line Drivers for Extra-Heavily-Loaded Lines
- Pulse Generators
- Driving the Largest MOSFETs and IGBTs
- Local Power ON/OFF Switch
- Motor and Solenoid Driver



ON Semiconductor®

<http://onsemi.com>




PDIP-8
P SUFFIX
CASE 626




TO-220
T SUFFIX
CASE 314D

PIN CONNECTIONS



5-Pin TO-220



NOTE: Duplicate pins must *both* be connected for proper operation.
NC = No connection

ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 8 of this data sheet.

DEVICE MARKING INFORMATION

See general marking information in the device marking section on page 8 of this data sheet.

NCP4421, NCP4422

ABSOLUTE MAXIMUM RATINGS*

Rating	Symbol	Value	Unit
Power Dissipation ($T_A \leq 70^\circ\text{C}$) PDIP 5-Pin TO-220	–	730 1.6	W
Power Dissipation ($T_C \leq 25^\circ\text{C}$) 5-Pin TO-220 (With Heat Sink)	–	12.5	W
Derating Factors (To Ambient) PDIP 5-Pin TO-220	–	8.0 12	mW/°C
Thermal Impedance (To Case) 5-Pin TO-220 $R_{\theta JC}$	–	10	°C/W
Storage Temperature	T_{stg}	–65 to +150	°C
Operating Temperature (Chip)	–	150	°C
Operating Temperature (Ambient) TO-220 Version PDIP Version	–	0 to +70 –40 to +85	°C
Lead Temperature (10 Seconds)	–	300	°C
Supply Voltage	V_{CC}	20	V
Input Voltage	–	$V_{DD} + 3.0$ to GND – 5.0	V
Input Current ($V_{IN} > V_{DD}$)	–	50	mA

*Static-sensitive device. Unused devices must be stored in conductive material. Protect devices from static discharge and static fields. Stresses above those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only and functional operation of the device at these or any other conditions above those indicated in the operational sections of the specifications is not implied. Exposure to Absolute Maximum Rating Conditions for extended periods may affect device reliability.

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ with $4.5\text{ V} \leq V_{DD} \leq 18\text{ V}$ unless otherwise specified.)

Characteristics	Test Conditions	Symbol	Min	Typ	Max	Unit
Input						
Logic 1 Input Voltage	–	V_{IH}	2.4	1.8	–	V
Logic 0 Input Voltage	–	V_{IL}	–	1.3	0.8	V
Input Current	$0\text{ V} \leq V_{IN} \leq V_{DD}$	I_{IN}	–10	–	10	μA
Output						
High Output Voltage	See Figure 1	V_{OH}	$V_{DD} - 0.025$	–	–	V
Low Output Voltage	See Figure 1	V_{OL}	–	–	0.025	V
Output Resistance, High	$V_{DD} = 18\text{ V}$, $I_O = 10\text{ mA}$	R_O	–	1.4	–	Ω
Output Resistance, Low	$V_{DD} = 18\text{ V}$, $I_O = 10\text{ mA}$	R_O	–	0.9	1.7	Ω
Peak Output Current	$V_{DD} = 18\text{ V}$	I_{PK}	–	9.0	–	A
Continuous Output Current	$10\text{ V} \leq V_{DD} \leq 18\text{ V}$, $T_C = 25^\circ$ (TC4421/22 CAT only)	I_{DC}	2.0	–	–	A
Latch-Up Protection	Duty Cycle $\leq 2\%$ Withstand Reverse Current	I_{REV}	> 1500 $t \leq 300\text{ }\mu\text{s}$	–	–	mA
Switching Time (Note 1)						
Rise Time	Figure 1, $C_L = 10,000\text{ pF}$	t_R	–	60	75	nsec
Fall Time	Figure 1, $C_L = 10,000\text{ pF}$	t_F	–	60	75	nsec
Delay Time	Figure 1	t_{D1}	–	30	60	nsec
Delay Time	Figure 1	t_{D2}	–	33	60	nsec

1. Switching times guaranteed by design.

NCP4421, NCP4422

ELECTRICAL CHARACTERISTICS (continued) ($T_A = 25^\circ\text{C}$ with $4.5\text{ V} \leq V_{DD} \leq 18\text{ V}$ unless otherwise specified.)

Characteristics	Test Conditions	Symbol	Min	Typ	Max	Unit
-----------------	-----------------	--------	-----	-----	-----	------

Power Supply

Power Supply Current	$V_{IN} = 3.0\text{ V}$ $V_{IN} = 0\text{ V}$	I_S	– –	0.2 55	1.5 150	mA μA
Operating Input Voltage	–	V_{DD}	4.5	–	18	V

Input

Logic 1 Input Voltage	–	V_{IH}	2.4	–	–	V
Logic 0 Input Voltage	–	V_{IL}	–	–	0.8	V
Input Current	$0\text{ V} \leq V_{IN} \leq V_{DD}$	I_{IN}	–10	–	10	μA

ELECTRICAL CHARACTERISTICS (Measured over operating temperature range with $4.5\text{ V} \leq V_S \leq 18\text{ V}$ unless otherwise specified.)

Characteristics	Test Conditions	Symbol	Min	Typ	Max	Unit
-----------------	-----------------	--------	-----	-----	-----	------

Input

Logic 1 Input Voltage	–	V_{IH}	2.4	–	–	V
Logic 0 Input Voltage	–	V_{IL}	–	–	0.8	V
Input Current	$0\text{ V} \leq V_{IN} \leq V_{DD}$	I_{IN}	–10	–	10	μA

Output

High Output Voltage	See Figure 1	V_{OH}	$V_{DD} - 0.025$	–	–	V
Low Output Voltage	See Figure 1	V_{OL}	–	–	0.025	V
Output Resistance, High	$V_{DD} = 18\text{ V}$, $I_O = 10\text{ mA}$	R_O	–	2.4	3.6	Ω
Output Resistance, Low	$V_{DD} = 18\text{ V}$, $I_O = 10\text{ mA}$	R_O	–	1.8	2.7	Ω

Switching Time (Note 1)

Rise Time	Figure 1, $C_L = 10,000\text{ pF}$	t_R	–	60	120	nsec
Fall Time	Figure 1, $C_L = 10,000\text{ pF}$	t_F	–	60	120	nsec
Delay Time	Figure 1	t_{D1}	–	50	80	nsec
Delay Time	Figure 1	t_{D2}	–	65	80	nsec

Power Supply

Power Supply Current	$V_{IN} = 3.0\text{ V}$ $V_{IN} = 0\text{ V}$	I_S	– –	0.45 0.06	3.0 0.2	mA
Operating Input Voltage	–	V_{DD}	4.5	–	18	V

1. Switching times guaranteed by design.

NCP4421, NCP4422





Figure 1. Switching Time Test Circuit

ARCHIVE
 DEVICE NOT RECOMMENDED FOR NEW DESIGN

TYPICAL ELECTRICAL CHARACTERISTICS




Figure 2. Rise Time vs. Supply Voltage




Figure 3. Fall Time vs. Supply Voltage




Figure 4. Rise Time vs. Capacitive Load




Figure 5. Fall Time vs. Capacitive Load




Figure 6. Rise and Fall Times vs. Temperature




Figure 7. Propagation Delay vs. Supply Voltage

TYPICAL ELECTRICAL CHARACTERISTICS




Figure 8. Supply Current vs. Capacitive Load ($V_{DD} = 18\text{ V}$)




Figure 9. Supply Current vs. Frequency ($V_{DD} = 18\text{ V}$)




Figure 10. Supply Current vs. Capacitive Load ($V_{DD} = 12\text{ V}$)




Figure 11. Supply Current vs. Frequency ($V_{DD} = 12\text{ V}$)




Figure 12. Supply Current vs. Capacitive Load ($V_{DD} = 6\text{ V}$)




Figure 13. Supply Current vs. Frequency ($V_{DD} = 6\text{ V}$)

TYPICAL ELECTRICAL CHARACTERISTICS




Figure 14. Propagation Delay vs. Input Amplitude




Figure 15. Propagation Delay vs. Temperature




Figure 16. Crossover Energy vs. Supply Voltage




Figure 17. Quiescent Supply Current vs. Temperature




Figure 18. High-State Output Resistance vs. Supply Voltage





Figure 19. Low-State Output Resistance vs. Supply Voltage

NCP4421, NCP4422

MARKING DIAGRAMS



x = 1 or 2
X = Assembly ID Code
Y = Year
CO = Country of Origin

ORDERING INFORMATION

Device	Package	Temperature Range	Shipping
NCP4421T	5-Pin TO-220	0°C to + 70°C	50 Units/Rail
NCP4421P	8-Pin PDIP	-40°C to + 85°C	50 Units/Rail
NCP4422T	5-Pin TO-220	0°C to + 70°C	50 Units/Rail
NCP4422P	8-Pin PDIP	-40°C to + 85°C	50 Units/Rail

Notes

ARCHIVE
DEVICE NOT RECOMMENDED FOR NEW DESIGN


Notes

ARCHIVE
DEVICE NOT RECOMMENDED FOR NEW DESIGN

NCP4421, NCP4422

PACKAGE DIMENSIONS

PDIP
P SUFFIX
CASE 626-05
ISSUE K




NOTES:

1. DIMENSION L TO CENTER OF LEAD WHEN FORMED PARALLEL.
2. PACKAGE CONTOUR OPTIONAL (ROUND OR SQUARE CORNERS).
3. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.

DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	9.40	10.16	0.370	0.400
B	6.10	6.60	0.240	0.260
C	3.94	4.45	0.155	0.175
D	0.38	0.51	0.015	0.020
F	1.02	1.78	0.040	0.070
G	2.54 BSC		0.100 BSC	
H	0.76	1.27	0.030	0.050
J	0.20	0.30	0.008	0.012
K	2.92	3.43	0.115	0.135
L	7.62 BSC		0.300 BSC	
M	---	10°	---	10°
N	0.76	1.01	0.030	0.040

TO-220
T SUFFIX
CASE 314D-04
ISSUE E



NOTES:

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: INCH.
3. DIMENSION D DOES NOT INCLUDE INTERCONNECT BAR (DAMBAR) PROTRUSION. DIMENSION D INCLUDING PROTRUSION SHALL NOT EXCEED 10.92 (0.043) MAXIMUM.

DIM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	0.572	0.613	14.529	15.570
B	0.390	0.415	9.906	10.541
C	0.170	0.180	4.318	4.572
D	0.025	0.038	0.635	0.965
E	0.048	0.055	1.219	1.397
G	0.067 BSC		1.702 BSC	
H	0.087	0.112	2.210	2.845
J	0.015	0.025	0.381	0.635
K	0.990	1.045	25.146	26.543
L	0.320	0.365	8.128	9.271
Q	0.140	0.153	3.556	3.886
U	0.105	0.117	2.667	2.972

ARCHIVE
RECOMMENDED FOR NEW DESIGN

ON Semiconductor and  are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer.

PUBLICATION ORDERING INFORMATION

Literature Fulfillment:

Literature Distribution Center for ON Semiconductor
P.O. Box 5163, Denver, Colorado 80217 USA
Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada
Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada
Email: ONlit@hibbertco.com

N. American Technical Support: 800-282-9855 Toll Free USA/Canada

JAPAN: ON Semiconductor, Japan Customer Focus Center
2-9-1 Kamimeguro, Meguro-ku, Tokyo, Japan 153-0051
Phone: 81-3-5773-3850
Email: r14525@onsemi.com

ON Semiconductor Website: <http://onsemi.com>

For additional information, please contact your local Sales Representative.