




| LOC |   | DIST |     | REVISIONS   |               |           |      |    |
|-----|---|------|-----|-------------|---------------|-----------|------|----|
| A   | I | P    | LTR | DESCRIPTION | DATE          | DWN       | APVD |    |
|     |   |      |     | B1          | ECR-09-026756 | 09FEB2010 | SR   | ME |
|     |   |      |     |             |               |           |      |    |
|     |   |      |     |             |               |           |      |    |
|     |   |      |     |             |               |           |      |    |

PANEL CUT-OUT FOR CONTACT INSERT  
WHEN USED WITHOUT HOUSING




CONTACT ARRANGEMENT VIEW FROM  
TERMINATION SIDE



NOTES

- 1
- POVER CONTACT : 1 TO 12  
OUTER DIMENSIONS OF INSULATION: MAX. Ø6.5mm  
SIGNAL CONTACT: A AND B  
OUTER DIMENSIONS OF INSULATION: MAX. Ø3.2mm
- 2
- SUITABLE HOOD SIZE 6  
SERIES HB, HD, EMV, AND HIP
- △
- GROUNDING CONTACT
- 4
- STANDARDS:  
DIN EN 61984; DIN EN 60664-1
- 5
- PACKAGING:  
5 PIECES IN A CARTON BOX



\*DISTANCE ARRANGEMENT  
VIEW FROM TERMINATION SIDE

|     |                         |             |               |      |
|-----|-------------------------|-------------|---------------|------|
| 1   | CYLINDER SCREW , M5     | STEEL       | NICKEL PLATED | 5    |
| 1   | CLIP TAB                | STEEL       | NICKEL PLATED | 4    |
| 4   | FIXING SCREW ASSY       | STEEL       | NICKEL PLATED | 3    |
| 2   | GRUNDING CONTACT-SOCKET | Cu Zn37 F38 | NICKEL PLATED | 2    |
| 1   | SOCKET INSERT           | VALOX       |               | 1    |
| QTY | DESCRIPTION             | MATERIAL    | SURFACE       | ITEM |
| 0-1 | HSK.6/36.Sti.C          |             |               |      |

|                                                                                       |  |                                        |  |                     |           |                                                                                                       |  |  |  |
|---------------------------------------------------------------------------------------|--|----------------------------------------|--|---------------------|-----------|-------------------------------------------------------------------------------------------------------|--|--|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                |  |                                        |  | DWN<br>R.SCHNEIDER  | 09FEB2010 |  TE Connectivity |  |  |  |
|                                                                                       |  |                                        |  | CHK<br>T.SCHNURPFEL | 09FEB2010 |                                                                                                       |  |  |  |
|                                                                                       |  |                                        |  | APVD                | -         |                                                                                                       |  |  |  |
| DIMENSIONS:                                                                           |  | TOLERANCES UNLESS OTHERWISE SPECIFIED: |  | NAME                |           | MALE INSERT<br>MALE INSERT HSK6/36<br>-                                                               |  |  |  |
| mm                                                                                    |  | 0 PLC ±                                |  | PRODUCT SPEC        |           |                                                                                                       |  |  |  |
|  |  | 1 PLC ±                                |  | APPLICATION SPEC    |           |                                                                                                       |  |  |  |
|                                                                                       |  | 2 PLC ±                                |  | WEIGHT              |           | A 1 00779 C-1108761                                                                                   |  |  |  |
|                                                                                       |  | 3 PLC ±                                |  | CUSTOMER DRAWING    |           |                                                                                                       |  |  |  |
|                                                                                       |  | 4 PLC ±                                |  |                     |           |                                                                                                       |  |  |  |
|                                                                                       |  | ANGLES ±°                              |  |                     |           | SCALE 5:1 SHEET 1 of 1 REV B1                                                                         |  |  |  |
| MATERIAL                                                                              |  | FINISH                                 |  |                     |           |                                                                                                       |  |  |  |
| -                                                                                     |  | -                                      |  |                     |           |                                                                                                       |  |  |  |