


 8.0 ± 0.26
 $(.31 \pm .01)$ TYP.


 $14.0 \pm .50$
 $(.55 \pm .02)$ TYP.

2000 ± 3.3
(78.74 ± 0.13)

1950 REF
(76.77)

50.0 ± 0.76
(1.97 ± 0.03) TYP.

1000 ± 0.76
(39.37 ± 0.03) TYP.

FRONT VIEW

50.0 ± 0.76 TYP.
(1.97 ± .03)

$$-4.5 \pm 0.26$$

 (-18 ± 01) TYP.
$$-25.0 \pm 0.50$$

$$(-98 \pm 02)$$
$$-12.5 \pm 0.76$$

$$(-49 \pm 03)$$
$$-6.5 \pm 0.26_{\text{TYP.}}$$
 $\pm 0.5 \quad (\pm .020)$ $\pm 0.5 \quad (\pm .020)$

MOUNTING HOLE DIMENSIONS

B

1. "B" MEASURED AT BASE.
2. STANDARD LENGTH: 2 METER.
3. SEE CURRENT CATALOG FOR PART NUMBER DESIGNATIONS FOR TYPE, COLOR, AND LENGTH.
4. DUCT TYPE "NNC" PACKAGED WITH TYPE "NC" COVER.
5. DIMENSIONS ARE METRIC (INCHES).


Technical drawing of a U-shaped profile. The drawing shows a cross-section of the profile with the following dimensions and tolerances:

- Height:** H REF.
- Width:** B REF.
- Top Flange Thickness:** T
- Bottom Flange Thickness:** T
- Bottom Flange Width:** ± 0.50

FOR 75mm WALL HGT.

FOR 37.5mm AND 50mm
76 WALL HGT.

CHANNEL EXAMPLE:
NNC 37 X 50 LG 2
 TYPE 37mm WIDE 50mm HIGH
 COLOR (LIGHT GRAY) LENGTH (m)

D38539AA_DC_NNC_01B.PRT

PANDUIT

CORP. TINLEY PARK, ILLINOIS

WIRING DUCT AND COVER
TYPE "NNC" METRIC
CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:

(.X)	±	(.XXX)	±
(.XX)	± 3.1	ANGLES	±

DRAWN BY JHNU	MAT'L: HALOG
------------------	--------------

DATE	MOD
8 3 83	POL YPL

8-2-02	FOLETTI
HK'D	0)
110	1)

JKG	(H
-----	----

UNLESS OTHERWISE SPECIFIED,

ALL DIMENSIONS ARE GIVEN

IN INCHES, THIRD ANGLE PROJECTION.

SCALE	NONF
-------	------

DRAWING NO.

38539-04

Sht 1 of 3

DWC

A

SIZE	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36	37	38	39	40	41	42	43	44	45	46	47	48	49	50	51	52	53	54	55	56	57	58	59	60	61	62	63	64	65	66	67	68	69	70	71	72	73	74	75	76	77	78	79	80	81	82	83	84	85	86	87	88	89	90	91	92	93	94	95	96	97	98	99	100
1	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36	37	38	39	40	41	42	43	44	45	46	47	48	49	50	51	52	53	54	55	56	57	58	59	60	61	62	63	64	65	66	67	68	69	70	71	72	73	74	75	76	77	78	79	80	81	82	83	84	85	86	87	88	89	90	91	92	93	94	95	96	97	98	99	100



ALL DIMENSIONS ARE METRIC (INCHES)

										CAD FILENAME/LAYERS		D38539AA_DC_NNC_01B.PRT	
										PANDUIT CORP. TINLEY PARK, ILLINOIS			
										WIRING DUCT AND COVER			
										TYPE "NNC" METRIC			
										CUSTOMER DRAWING			
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) (.XX) ± 3.1 (.12) ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
1	9-18-06	JCST	JKG	SEE SHEET 1 OF 3 FOR REVISIONS	38539-04	JKG	JKG			DRAWN BY JHNU	MAT'L: HALOGEN FREE MODIFIED POLYPHENYLENE OXIDE (PPQ)	SCALE NONE	
R	11-2-02	JHNU JCST	JKG	SEE SHEET 1 OF 3 FOR REVISIONS	38539-04	HIW	HIW			DATE 8-2-02		DRAWING NO. 38539-04	DWG A
REV	DATE	BY	CHK	DESCRIPTION	ECN	CHK	CUST	SUP		CHK'D JKG		SHT 2 OF 3	SIZE



CAD FILENAME/LAYERS

PANDUIT CORP. TINLEY PARK, ILLINOIS
WIRING DUCT AND COVER
TYPE "NNC" METRIC
CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN IN
INCHES, THIRD ANGLE PROJECTION.

SCALE NONE

DRAWING NO. 38539-04
SHT 3 OF 3

DWG
A
SIZE