

9619 Multi-Conductor - Computer Cable for EIA RS-232 Applications



Description:

24 AWG stranded (7x32) tinned copper conductors, S-R PVC insulation, overall Beldfoil® (100% coverage), TC braid shield (65% coverage), PVC jacket

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
50	24	7x32	TC - Tinned Copper

Insulation

Insulation Material:

Insulation Material
S-R PVC - Semi-Rigid Polyvinyl Chloride

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100
2		Braid	TC - Tinned Copper	65

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cabling

Overall Cabling Color Code Chart:

Number	Color
1	Black
2	White
3	Red
4	Green
5	Orange
6	Blue
7	White/Black
8	Red/Black
9	Green/Black
10	Orange/Black
11	Blue/Black
12	Black/White
13	Red/White
14	Green/White
15	Blue/White
16	Black/Red
17	White/Red
18	Orange/Red
19	Blue/Red
20	Red/Green
21	Orange/Green
22	Black/White/Red

9619 Multi-Conductor - Computer Cable for EIA RS-232 Applications

23	White/Black/Red
24	Red/Black/White
25	Green/Black/White
26	Orange/Black/White
27	Blue/Black/White
28	Black/Red/Green
29	White/Red/Green
30	Red/Black/Green
31	Green/Black/Orange
32	Orange/Black/Green
33	Blue/White/Orange
34	Black/White/Orange
35	White/Red/Orange
36	Orange/White/Blue
37	White/Red/Blue
38	Black/White/Green
39	White/Black/Green
40	Red/White/Green
41	Green/White/Blue
42	Orange/Red/Green
43	Blue/Red/Green
44	Black/White/Blue
45	White/Black/Blue
46	Red/White/Blue
47	Green/Orange/Red
48	Orange/Red/Blue
49	Blue/Orange/Red
50	Black/Orange/Red

Overall Nominal Diameter: 0.485 in.

Mechanical Characteristics (Overall)

Operating Temperature Range:	-30°C To +80°C
UL Temperature Rating:	80°C (UL AWM Style 2464)
Bulk Cable Weight:	180 lbs/1000 ft.
Min. Bend Radius (Install)/Minor Axis:	4.900 in.

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/UL) Specification:	CMG
CEC/C(UL) Specification:	CMG
AWM Specification:	UL Style 2464 (300 V 80°C)
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	10/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	UL1685 FT4 Loading
C(UL) Flame Test:	FT4

9619 Multi-Conductor - Computer Cable for EIA RS-232 Applications

Plenum/Non-Plenum

Plenum (Y/N): No

Electrical Characteristics (Overall)

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)

30

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft)

55

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

25

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

4.3

Max. Operating Voltage - UL:

Voltage

300 V RMS (UL AWM Style 2464)

Max. Recommended Current:

Current

.9 Amps per conductor @ 25°C

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9619 060100	100 FT	17.200 LB	CHROME	C	50 #24 PVC SHLD PVC
9619 0601000	1,000 FT	182.000 LB	CHROME	C	50 #24 PVC SHLD PVC
9619 060500	500 FT	93.000 LB	CHROME	C	50 #24 PVC SHLD PVC

Notes:

C = CRATE REEL PUT-UP.

Introduction

Belden® multi-conductor cables are manufactured in a wide variety of gage sizes, dimensions, insulation materials, shielding configurations, and jacketing materials including Plenum and High-Temperature versions. These cables meet the technical requirements of many different types of systems. In fact, Belden offers one of the broadest lines of UL Listed, NEC and CEC multi-conductor cables available from any single source.

Applications for multi-conductor cables include computers, communications, instrumentation, sound, control, audio, and data transmission. Each of these cables is designed to protect signal integrity under critical conditions by reducing hum, noise, and crosstalk.

To assist you in selecting the proper cable for your application, both the suggested working voltages and the maximum temperature ratings are indicated for each applicable product in this section.

Most of our multi-conductor cables are available from stock. Many of these are available off the shelf from distributors. If you have a new or unusual application or you cannot find a multi-conductor cable in this catalog section that meets your technical requirements, contact Technical Support at 1-800-BELDEN-1.

Multi-Conductor Cables Packaging

Belden's unique UnReel® cable dispenser is available for many of the multi-conductor products listed in this section. The letter "U" before the specified put-up length denotes UnReel packaging.

Selection Guide

Shielded Multi-Conductor Computer Cables for RS-232 Applications

Specifications		Cable Series*			
		9925	9608	9533	9939
Conductor Size: (AWG)	28				
	24	✓	✓	✓	
	22				✓
	20				
	18				
Page No.		4.18	4.17	4.11	4.19
Insulation:	S-R PVC		✓	✓	✓
	Polyethylene				
	Polypropylene				
	Datalene®†	✓			
Shield:	Overall Foil			✓	
	Drain Wire	✓		✓	
	Overall Foil/Braid	✓	✓		✓
	Braid Coverage	65%	65%		65%
Drain Wire Overall:		Yes	No	Yes	No
No. of Cond. Available:	1				
	2				
	3	✓	✓	✓	✓
	4	✓	✓	✓	✓
	5	✓	✓	✓	✓
	6	✓	✓	✓	✓
	7	✓	✓	✓	✓
	8	✓	✓	✓	✓
	9	✓	✓	✓	✓
	10	✓	✓	✓	✓
	11				
	12				
	13				
	15	✓	✓	✓	✓
	17				
	18				
	19				
	20			✓	
	25	✓	✓	✓	✓
	27				
	30			✓	
	31				
	37	✓	✓		✓
	40			✓	
	50		✓	✓	✓
Capacitance ** (pF/ft.)		12.0	30.0	30.0	35.0


*All cables are UL-listed.

**Capacitance may vary on some cables.

† Foam high density polyethylene.

Overall Foil/Braid Shield

Computer Cables for EIA RS-232 Applications

Description	Part No.	UL NEC/ C(UL) CEC Type	No. of Cond.	Color Code	Standard Lengths		Standard Unit Weight		Nominal OD		Nominal DCR		Nominal Capacitance																	
					Ft.	m	Lbs.	kg	Inch	mm	Cond.	Shield	* pF/ Ft.	* pF/ m	** pF/ Ft.	** pF/ m														
24 AWG Stranded (7x32) TC Conductors • Overall Beldfoil® (100% Coverage) + TC Braid Shield (65% Coverage)																														
Semi-rigid PVC Insulation • Chrome PVC Jacket																														
	9608	NEC:	3	See	100	30.5	3.1	1.4	.190	4.83	25.0Ω/M'	9.8Ω/M'	35	115	65	213														
		CMG:		Chart 1	500	152.4	12.0	5.4			82.0Ω/km	32.2Ω/km																		
		CEC:		(Tech Info	1000	304.8	23.0	10.4																						
		CMG FT4		Section)																										
		NEC:		4	See	100	30.5	3.5			1.6	.200					5.08	25.0Ω/M'	9.8Ω/M'	35	115	65	213							
		CMG:			Chart 1	500	152.4	13.5			6.1							82.0Ω/km	32.2Ω/km											
		CEC:			(Tech Info	1000	304.8	26.0			11.8																			
		CMG FT4			Section)																									
		NEC:			5	See	100	30.5			4.0							1.8	.215					5.46	25.0Ω/M'	6.5Ω/M'	35	115	65	213
		CMG:				Chart 1	500	152.4			16.0							7.3							82.0Ω/km	21.3Ω/km				
CEC:	(Tech Info	1000	304.8			32.0	14.5																							
CMG FT4	Section)																													
NEC:	6	See	100			30.5	4.2	1.9	.225	5.72	25.0Ω/M'		7.0Ω/M'	30	98.4	55		180												
CMG:		Chart 1	500			152.4	17.0	7.7			82.0Ω/km		23.0Ω/km																	
CEC:		(Tech Info	1000	304.8		34.0	15.4																							
CMG FT4		Section)																												
NEC:		7	See	100		30.5	4.2	1.9			.225	5.72	25.0Ω/M'				6.9Ω/M'			30	98.4	55	180							
CMG:			Chart 1	500		152.4	18.5	8.4					82.0Ω/km				22.6Ω/km													
CEC:			(Tech Info	1000	304.8	38.0	17.3																							
CMG FT4			Section)																											
NEC:			8	See	100	30.5	4.5	2.0					.240				6.10		25.0Ω/M'					7.3Ω/M'	30	98.4	55	180		
CMG:				Chart 1	500	152.4	21.0	9.5											82.0Ω/km					23.9Ω/km						
CEC:	(Tech Info			1000	304.8	41.0	18.6																							
CMG FT4	Section)																													
NEC:	9			See	100	30.5	4.8	2.2	.253	6.43				25.0Ω/M'	7.5Ω/M'	30		98.4	55					180						
CMG:				Chart 1	500	152.4	22.0	10.0						82.0Ω/km	24.6Ω/km															
CEC:		(Tech Info		1000	304.8	44.0	20.0																							
CMG FT4		Section)																												
NEC:		10		See	100	30.5	5.4	2.5			.270	6.86		25.0Ω/M'	6.9Ω/M'					30	98.4	55	180							
CMG:				Chart 1	500	152.4	25.0	11.4						82.0Ω/km	22.6Ω/km															
CEC:			(Tech Info	1000	304.8	50.0	22.7																							
CMG FT4			Section)																											
NEC:			15	See	100	30.5	6.6	3.0					.300	7.62	25.0Ω/M'		6.9Ω/M'								30	98.4	55	180		
CMG:				Chart 2R	500	152.4	31.5	14.3							82.0Ω/km		22.6Ω/km													
CEC:	(Tech Info			1000	304.8	63.0	28.6																							
CMG FT4	Section)																													
NEC:	25			See	100	30.5	10.1	4.6	.370	9.40					25.0Ω/M'	5.1Ω/M'	30	98.4	55					180						
CMG:				Chart 2R	500	152.4	49.5	22.5							82.0Ω/km	16.7Ω/km														
CEC:		(Tech Info		1000	304.8	100.0	45.4																							
CMG FT4		Section)																												
NEC:		37		See	100	30.5	13.7	6.2			.411	10.43			25.0Ω/M'	4.4Ω/M'				30	98.4	55	180							
CMG:				Chart 2R	500	152.4	66.5	30.2							82.0Ω/km	14.4Ω/km														
CEC:			(Tech Info	1000	304.8	135.0	61.3																							
CMG FT4			Section)																											
NEC:			50	See	100	30.5	17.2	7.8					.485	12.32	25.0Ω/M'	4.3Ω/M'									30	98.4	55	180		
CMG:				Chart 2R	500	152.4	93.0	42.2							82.0Ω/km	14.1Ω/km														
CEC:	(Tech Info			1000	304.8	182.0	82.6																							
CMG FT4	Section)																													

DCR = DC Resistance • TC = Tinned Copper

* Capacitance between conductors.

** Nominal capacitance conductor to conductor and shield.