





CONFIGURAZIONE POLARIZZAZIONI
POLARIZATION CONFIGURATION



NOTE:




- USATO CON TERMINALE 94518-0XXX E 94549-0XXX
- SPECIFICA DI RIFERIMENTO PER IL CONNETTORE PS-94550-001
- PER CARATTERISTICHE DI CRIMPATURA RIF. SD-94518-005 E SD-94549-001
- FORZA DI DISACCOPIAMENTO CONNETTORE (TRAZIONANDO DAI CAVI SENZA AZIONARE L'AGGANCI): 60 N MIN.
- SPESSORE MIN. PARETI CONNETTORE 0.40 mm.

NOTE:

- USED WITH TERMINALS 94518-0XXX AND 94549-0XXX
- REFER TO PS-94550-001 FOR CONNECTOR SPECIFICATION
- REFER TO SD-94518-005 AND SD-94549-001 FOR CRIMPING CHARACTERISTICS
- CONNECTOR DISENGAGEMENT FORCE (PULLING BY THE WIRES, WITHOUT ACTUATING THE LATCH): 60 N MIN.
- MINIMUM CONNECTOR WALL THICKNESS 0.40 mm.

CONFEZIONE: Box da 1300 Pz.

PACKAGING: 1300 pcs in carton box



* AGENCY
RECOGNIZATIONS
CSA (file LR19980)
UL (file E-29179)

P/N	MATERIAL/COLOR
*94550-9005	NYLON 6.6 V0 NATURAL
94550-4005	NYLON 6.6 GWT 750 °C sec.IEC 60335-1 TEST METHOD IEC 60695-2-11 NATURAL

SEZ: B-B

SPQ =1300

Std. Descr: "HSG W/SEC LOCK AND EXT LATCHES 5 CKT _____ COLOR"

EC NO: Z2006-0056 DRWN:FGOTTARD 2005/10/14 CHKD:RSANDANO 2005/10/14 APPR: GZUIN 2005/10/17 A2	QUALITY SYMBOLS ▽ = 0 ◻ = 0	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		SCALE 2:1	DESIGN UNITS METRIC	FIRST ANGLE PROJECTION		REVISE ON CAD ONLY	
					DIMENSION STYLE MM ONLY		TITLE		HSG 5 CKT WITH SEC.LOCK AND EXTERNAL LATCH	
			4 PLACES ± --- ± ---		DRAWN BY DATE		FGOTTARD 2002/06/27			
			3 PLACES ± --- ± ---		CHECKED BY DATE		MTESTAGU 2002/06/27		MOLEX MOLEX INCORPORATED	
			2 PLACES ± 0.10 ± ---		APPROVED BY DATE		GZUIN 2002/06/27		MATERIAL NO. 94550-9005	
			1 PLACE ± 0.2 ± ---		DRAFT WHERE APPLICABLE		SD-94550-004		DOCUMENT NO. 1 OF 1	
			ANGULAR ± 2 °		MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		A3	