


LOC		DIST		P		F		ZONE		LTR		REVISIONS		DATE		APPD	
G		14		P		F				D		REV,RDRW,& SM PKG PER 0720-0040-93		3-29-93		1AP DAP	

METRIC

DIMENSIONS LISTED IN mm [INCHES]

AMP WIRE RANGE	 E13288 Listed
12-10 AWG SOLID OR STRANDED	12-10 AWG STRANDED
 LR7189 Certified	MILITARY P/N AND CLASS
12-10 AWG SOLID OR STRANDED	NOT APPLICABLE

1 STAMP 6S AMP 12-10* APPROX AS SHOWN
6S INDICATES STUD SIZE



					50	LOOSE PIECE, BOX		8-53126-2					
					2500	ON TAPE		53126-2					
					---	LOOSE PIECE		53126-1					
					QUANTITY	PACKAGING TYPE		PART NO					
AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX		DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± - 3 PLC DEC ± - ANGLES ± -		DR 3-29-93 TA BRINKMAN CHK 3-29-93 DA PATTERSON APPD 3-29-93 DE MILLER APPD 3-29-93 JL MECKLEY PRODUCT SPEC -		 AMP Incorporated Harrisburg, PA 17105-3608				
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: NOT APPLICABLE		NAME							
FOR APPLICATION TOOLING INFORMATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		WIRE CROSS SECTIONAL AREA RANGE: 2.62-6.64mm² [5,180-13,100] CIR MILS SOLID OR STRANDED		MATERIAL PHOSPHOR BRONZE PER ASTM B-103 ANNEALED		TERMINAL, SHORT SPRING SPADE, SOLISTRAND™					
FOR ORDER ENTRY		1-800-526-5142		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		FINISH TIN PLATE 0.00254[.000100] MIN THK PER MIL-T-10727		APPLICATION SPEC -		SIZE 	CAGE CODE 00779	DRAWING NO C=53126	
						WEIGHT -		SCALE 10:1				SHEET 1 OF 1	