




D-SUBMINIATURE CONNECTORS:

K88X Series

Vertical PCB Mount High Profile

K88X Series Dimensions

Dimensions in mm



Number of Contacts (Shell Size)	Dimensions (mm)				
	A	A1	B	C	D
9 (E)	16.33	16.92	24.99	30.81	19.18
15 (A)	24.66	25.25	33.32	39.14	27.51
25 (B)	38.38	38.96	47.04	53.04	41.00
37 (C)	54.84	55.42	63.50	69.32	57.71

A = Exterior of Female Shell (S)

A1 = Interior of Male Shell (P)



Generated Part Number

K88X-ED-9P

Part Number Builder

K88X	-	E	D	9	P	
Series		Shell Type	Pin Type	Contact Option	Contact Type	Mounting Option

Series

K88X - D-Subminiature Vertical Connector

Contact Shell Size

E - 9 Contacts

A - 15 Contacts

B - 25 Contacts

C - 37 Contacts

Pin Type (L1)

D - 3.80mm

Contact Type

P - Pin Contact (Plug)

S - Socket Contact (Receptacle)

Mounting Option

Blank - Through Hole

BR - #4-40 Tin Plated 11.00mm Long Boardlocks

BRJ - #4-40 Boardlocks and #4-40 Jackscrews

K - #4-40 Bushings

KJ - #4-40 Bushings and #4-40 Jackscrews