


SMD Power Inductor

CDRH3D28



Description

- Ferrite drum core construction.
- Magnetically shielded.
- L × W × H: 4.0 × 4.0 × 3.0 mm Max.
- Product weight: 130m g (Ref.)
- Moisture Sensitivity Level: 1
- RoHS compliance.

Environmental Data

- Operating temperature range: -40℃~+105℃ (including coil's self temperature rise)
- Storage temperature range: -40℃~+105℃
- Solder reflow temperature: 260℃ peak.


Packaging

- Carrier tape and reel packaging
- 7.0" diameter reel
- 500pcs per reel


Applications

- Ideally used in Mobilephone, PDA, MP3, DSC/DVC, Portable DVD, etc as DC-DC converter inductors.

Dimension - [mm]



Land pattern and Schematics - [mm]



Electrical Characteristics

Part Name	Stamp	Inductance (μH) [within]※1	D.C.R. (mΩ) Max. (Typ.) (at 20℃)	Saturation Current (A) ※2		Temperature Rise Current (A) ※3
				at 20℃	at 100℃	
CDRH3D28NP-1R0NC	L	1.0μH±30%	37.5(30.0)	3.00	2.40	2.60
CDRH3D28NP-3R3NC	A	3.3±30%	72.1(57.7)	2.00	1.48	1.85
CDRH3D28NP-4R7NC	B	4.7±30%	88.3(70.6)	1.65	1.28	1.62
CDRH3D28NP-6R8NC	C	6.8±30%	119(95.0)	1.24	0.94	1.32
CDRH3D28NP-100NC	D	10±30%	145(116)	1.05	0.80	1.18
CDRH3D28NP-150NC	E	15±30%	213(170)	0.90	0.64	1.02
CDRH3D28NP-220NC	F	22±30%	335(268)	0.76	0.55	0.74
CDRH3D28NP-330NC	G	33±30%	481(385)	0.58	0.44	0.63
CDRH3D28NP-470NC	H	47±30%	599(479)	0.48	0.36	0.56

※1. Inductance measuring condition: at 100kHz.

※2. Saturation current: The value of D.C. current when the inductance decreases to 65% of it's nominal value.

※3. Temperature rise current: The value of D.C. current when the temperature rise is Δt=40℃(Ta=20℃).


SMD Power Inductor CDRH3D28




Saturation Current & Temperature Rise Graph

— L (20°C) — L (100°C) — ΔT


1. CDRH3D28NP-1R0NC




2. CDRH3D28NP-3R3NC




3. CDRH3D28NP-4R7NC




4. CDRH3D28NP-6R8NC




5. CDRH3D28NP-100NC




6. CDRH3D28NP-150NC




7. CDRH3D28NP-220NC



8. CDRH3D28NP-330NC



9. CDRH3D28NP-470NC




SMD Power Inductor CDRH3D28




Solder Reflow Condition

Heat Endurance



Temperature Chart



Please refer to the sales offices on our website - <http://www.sumida.com>

Hong Kong

Tel.+852-2880-6781
FAX.+852-2565-9600
sales@hk.sumida.com

Saitama(Japan)

Tel.+81-48-691-7300
FAX.+81-48-691-7340
sales@jp.sumida.com

Chicago

Tel.+1-847-545-6700
FAX. +1-847-545-6720
sales@us.sumida.com

Shanghai

Tel.+86-21-5836-3299
FAX.+86-21-5836-3266
shanghai.sales@cn.sumida.com

Seoul

Tel.+82-2-6237-0777
FAX.+82-2-6237-0778
sales@kr.sumida.com

Obernzell

Tel.+49-8591-937-0
FAX. +49-8591-937-103
contact@eu.sumida.com

Shenzhen

Tel.+86-755-8291-0228
FAX.+86-755-8291-0338
shenzhen.sales@cn.sumida.com

Singapore

Tel.+65-6296-3388
FAX.+65-6841-4426
sales@sg.sumida.com

Neumarkt

Tel.+49-9181-4509-110
FAX. +49-9181-4509-310
infocomp@eu.sumida.com

Taipei

Tel.+886-2-8751-2737
FAX.+886-2-8751-2738
sales@tw.sumida.com

San Jose

Tel.+1-408-321-9660
FAX.+1-408-321-9308
sales@us.sumida.com