





SPECIFICATIONS:

MATERIAL:-

BASE: LCP, BLACK COLOR

COVER: C5210-H, T=0.2mm

TERMINAL A: C5210-H, T=0.30mm

TERMINAL B: C5210-H, T=0.30mm

FINISH:-

COVER: Sn

TERMINAL A: CONTACT AREA: Au

NON CONTACT AREA: Au FLASH

TERMINAL A: CONTACT AREA: Au

NON CONTACT AREA: Au FLASH

ELECTRICAL:-

CONTACT RESISTANCE: 40 mΩ MAX

INSULATION RESISTANCE: 100 MΩ MIN

LEAD CO-PLANARITY: 0.1mm MAX.

CONTACT PIN PLANARITY: 0.1mm MAX.

NOTES: ALL DIMENSIONS AND NOTES
MARKED ✖ ARE CRITICAL AND
MUST BE CHECKED IN ACCORDANCE
WITH QUALITY DOC. Q1-02A

OBSOLETE

TOLERANCES

X. = ±25mm
X.X = ±0.20mm
X.XX = ±0.10mm

HARWIN

HARWIN USA
TEL: 603 893 5376
FAX: 603 893 5396
mis@harwin.com

HARWIN Europe (UK)
TEL: 023 9231 4545
FAX: 023 9231 4590
mis@harwin.co.uk

HARWIN Asia
TEL: +65 6 779 4909
FAX: +65 6 779 3868
mis@harwin.com.sg

THIS DRAWING AND ANY
INFORMATION OR DESCRIPTIVE
MATTER SET OUT HEREON ARE
CONFIDENTIAL AND COPYRIGHT
PROPERTY OF THE HARWIN
GROUP AND MUST NOT BE
DISCLOSED, LOANED, COPIED
OR USED FOR MANUFACTURING,
TENDERING OR FOR ANY
OTHER PURPOSE WITHOUT
THEIR WRITTEN PERMISSION.

TOLERANCES

X. = ±1mm
X.X = ±0.25mm
X.XX = ±0.10mm
X.XXX = ±0.01mm

ANGLES = ±5°
UNLESS STATED

MATERIAL:

SEE NOTES

FINISH:

SEE NOTES

S/AREA:

mm²

TITLE:

LCD 31P HEADER R/A

DRAWING NUMBER:

M711-2123145R

SHT
1
OF
1

Allan	1	01.08.06	-
NAME	ISS.	DATE	C/NOTE
APPROVED: <i>Alan</i>			
CHECKED: <i>Alan</i>			
DRAWN: Allan			
CUSTOMER REF.:			
ASSEMBLY DRG:			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Harwin:

LVDS-31PRMA