


**Glass Passivated Junction
Fast Switching Rectifier****Reverse Voltage** 400 to 1000 V
Forward Current 1.0 A

NOTE: Lead diameter is $\frac{0.026}{0.023}$ ($\frac{0.66}{0.58}$) for suffix "E" part numbers

Dimensions in inches and (millimeters)

*Glass-plastic encapsulation technique is covered by
Patent No. 3,996,602, and brazed-lead assembly by Patent No. 3,930,306

Features

- Plastic package has Underwriters Laboratories Flammability Classification 94V-0
- High temperature metallurgically bonded construction
- For use in high frequency rectifier circuits
- Fast switching for high efficiency
- Cavity-free glass passivated junction
- Capable of meeting environmental standards of MIL-S-19500
- 1.0 Ampere operation at $T_A=55^\circ\text{C}$ with no thermal runaway
- Typical I_R less than 0.1 μA
- High temperature soldering guaranteed:
350°C/10 seconds, 0.375" (9.5mm) lead length,
5 lbs. (2.3kg) tension

Mechanical Data**Case:** JEDEC DO-204AL, molded plastic over glass body**Terminals:** Plated axial leads, solderable per
MIL-STD-750, Method 2026**Polarity:** Color band denotes cathode end**Mounting Position:** Any**Weight:** 0.012 ounce, 0.3 gram**Maximum Ratings & Thermal Characteristics** Ratings at 25°C ambient temperature unless otherwise specified.

Parameter	Symbols	BA157GP	BA158GP	BA159DGP	BA159GP	Units
Maximum repetitive peak reverse voltage	V_{RRM}	400	600	800	1000	V
Maximum RMS voltage	V_{RMS}	280	420	560	700	V
Maximum DC blocking voltage	V_{DC}	400	600	800	1000	V
Maximum average forward rectified current 0.375" (9.5mm) lead length at $T_A=55^\circ\text{C}$	$I_{F(AV)}$	1.0				A
Peak forward surge current 10ms single half sine-wave superimposed on rated load at $T_A=25^\circ\text{C}$	I_{FSM}	20				A
Typical thermal resistance (NOTE 1)	$R_{\theta JA}$	55				°C/W
Operating junction and storage temperature range	T_J, T_{STG}	- 65 to +175				°C

Electrical Characteristics Ratings at 25°C ambient temperature unless otherwise specified.

Parameter	Symbols	BA157GP	BA158GP	BA159DGP	BA159GP	Units
Maximum instantaneous forward voltage at 1.0A	V_F	1.3				V
Maximum DC reverse current at rated DC blocking voltage $T_A=25^\circ\text{C}$	I_R	5.0				μA
Maximum reverse recovery time at $I_F=0.5\text{A}$, $I_R=1.0\text{A}$, $I_{rr}=0.25\text{A}$	t_{rr}	150	250	500	500	ns
Typical junction capacitance at 4.0V, 1MHz	C_J	15				pF

Notes:

(1) Thermal resistance from junction to ambient at 0.375" (9.5mm) lead length, P.C.B. mounted

Ratings and Characteristic Curves ($T_A = 25^\circ\text{C}$ unless otherwise noted)

Fig. 1 – Forward Current Derating Curve




Fig. 2 – Maximum Non-Repetitive Peak Forward Surge Current




Fig. 3 – Typical Instantaneous Forward Characteristics




Fig. 4 – Typical Reverse Characteristics




Fig. 5 – Typical Junction Capacitance




Fig. 6 – Typical Transient Thermal Impedance

