


QTY REQD PER ASSY		PARTS LIST			
DIMENSIONS IN INCHES. DO NOT SCALE PRINT.		MATL	HT TR	FIN	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		DR 19APR00 B.HIGMAN	APP 19APR00 T.ELBIN	 AMP Incorporated Harrisburg, PA 17105-3608	
2 PLC DEC +/-		CHK 19APR00 B.HIGMAN	REL -		
3 PLC DEC +/-					
4 PLC DEC +/-					
ANGLES +/-		NAME SIDE FEED HDM APPLICATOR			MACHINE REF
SURF TEXTURE: ☒		SCALE -			MINI APPL ☒
REMOVE BURRS, BREAK SHARP EDGES R.015 MAX		☒ DWG NO	1385044		SHEET 1 OF 1 REV 01
CAGE CODE 00779	CUSTOMER AND ASSEMBLY DRAWING				RESTRICTED TO -



- ① RECOMMENDED SPARE PARTS.
- ② GREASE LIGHTLY.
- ③ GUARD MUST BE IN PLACE WHEN OPERATING APPLICATOR IN A BENCH MACHINE.
- ④ LUBRICATE DAILY USING NO. 20 MACHINE OIL.
5. ITEMS WITH QTY OF REF SPECIFIED (EXCEPT ITEMS 78 AND 79) ARE USED ON ITEM 46.
- ⑥ CUT TO LENGTH AT ASSEMBLY.
- ⑦ ANVIL TO BE ASSEMBLED IN FAR RIGHT SLOT IN CURRENT VIEW.
- ⑧ THIS IS A TWO STAGE APPLICATOR. FIRST STAGE SHEARS REAR CARRIER; SECOND STAGE CRIMPS, BENDS TERMINAL TO 90° AND SHEARS FRONT CARRIER STRIP.

[illegible]

THIS DRAWING IS A CONTROLLED DOCUMENT.

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION
© COPYRIGHT 19 BY AMP INCORPORATED. ALL RIGHTS RESERVED.	