




# WATERPROOF

Registered



ISO 9001

# EDACON

*an EDACOM company*



an EDACOM company

40 Tiffield Road., Scarborough, Ontario, M1V 5B6, Canada

Telephone: (416) 754-3322 Facsimile: (416) 754-3299

e-mail: edac@edac.net Web Page: <http://www.edac.net>

**Your Connection to Quality and Service**

## NUMERICAL INDEX

| Series    | Page |
|-----------|------|
| 556       | 8    |
| 566       | 2    |
| 566 Tools | 7    |
| 568       | 6    |
| 568 Tools | 7    |
| 570       | 4    |
| 570 Tools | 7    |

## TABLE OF CONTENTS

| Products                 | Page |
|--------------------------|------|
| Application Notes        | 1    |
| Water Proof Connectors   | 5    |
| Discrete wire Connectors | 8    |

## ENGINEERING NOTES:

The Waterproof series of connectors are made using the following materials and processes.

The insulator housing is made of high impact flame retardant (UL 94-V0) Polyester (PBT). The water seals are moulded out of silicone rubber. The housings use latching mechanisms to hold and lock the mating halves together.

The mated connectors have been tested for various levels of resistance to water ingress. These test vary from a level of "0" which means "without protection" to "8" which is a fully submersible connector.

The contacts are made of brass or phosphor bronze and are plated with nickel (to improve wear resistance and reduce galvanic corrosion), then they are plated with a tin-lead alloy for conductivity.

Crimp contacts are available for wire sizes of 28 to 22 AWG for the 566 series, and for 22 to 16 AWG for the 568 and 570 series.

## APPLICATION NOTES:

The typical application of these connectors includes any place where there is the chance of water contaminating the circuit. These applications have included: bathrooms, hot water heaters, washing machines, water purifiers, outdoor motors, frozen food show cases, dishwashers and most outdoor applications.

The Waterproof connectors have been approved for use in environments which require a protection grade of "4" (Splash-Proof). The connectors have successfully passed testing to a protection grade of "7".

The following chart describes the protection grades, class descriptions, and meanings of the various moisture/water protection grades.


| Protection Grade | Class Description  | Meaning                                                                                          |
|------------------|--------------------|--------------------------------------------------------------------------------------------------|
| 0                | -                  | No Moisture Protection                                                                           |
| 1                | Drip-Proof Type I  | No harmful influence by a drip of water falling perpendicularly.                                 |
| 2                | Drip-Proof Type II | No harmful influence by a drip of water falling from a range covering 15 from perpendicular.     |
| 3                | Spray-Proof        | No harmful influence by a rainfall of water falling from a range covering 60 from perpendicular. |
| 4                | Splash-Proof       | No harmful influence by a splash of water from any direction.                                    |
| 5                | Jet-Proof          | No harmful influence by a jet of water from any direction.                                       |
| 6                | Watertight         | No ingress of water inside by a jet of water from any direction.                                 |
| 7                | Immersion-Proof    | No ingress of water inside when immersed in water under specified conditions.                    |
| 8                | Submersible        | Always useable when submerged in water of specified pressure.                                    |

Waterproof Standard descriptions Based on JIS C 0920-1993

The waterproof connectors are available in a wire-to-wire or a wire-to-board configuration. When used in a wire-to-board application, a silastic conformal coating may be used to seal the board mounted connector.

# 566 SERIES WATERPROOF CONNECTOR

Plug, Receptacle & Board Mount



## FEATURES

- Fully waterproof connector
- Plastic latch provides locking mechanism
- Plug and Receptacle in 1, 3, and 5 Contact positions
- Board mount style available in 2, 3, 5 and 9 contact positions
- Tools Available for Contact Installation, Removal and Crimping
- Able to carry current up to 2 A

## SPECIFICATIONS

- Insulator Material: PBT (UL94V-0)
- Contact Material: PB / Tin plating
- Wire Housing Seal: Silicone Rubber
- Current Rating: 2 Amperes maximum
- Contact Resistance: 10m  $\Omega$  Maximum
- Insulator Withstanding Voltage: 1000 V AC rms at Sea Level
- Insulation Resistance: 1000M  $\Omega$  Minimum at 500 VDC
- Operating Temperature: -40 to +105 Degrees C
- Rated Voltage: 250 V
- Waterproof Grade 4
- Insulation diameter from .039" (1.0mm) to .059" (1.5mm) can be accommodated using different wire seals.

## 566 SERIES ORDERING CODE

Example Part Number **566 - 003 - 000 - 1 1 0**

Series \_\_\_\_\_  
 Total Number of Contacts \_\_\_\_\_  
 Contact Code \_\_\_\_\_  
 Style \_\_\_\_\_  
 Wire Diameter \_\_\_\_\_  
 Termination \_\_\_\_\_

|                             |                                                                   |
|-----------------------------|-------------------------------------------------------------------|
| Series                      | 566                                                               |
| Total Number of Contacts    | 002, 003, 005 or 009                                              |
| Contact Code <sup>1,2</sup> |                                                                   |
| 000                         | No Contacts Assembled                                             |
| 420                         | Board Mount Contacts Installed                                    |
| Style <sup>3</sup>          |                                                                   |
| 1                           | Plug                                                              |
| 2                           | Receptacle                                                        |
| Wire Diameter <sup>4</sup>  |                                                                   |
| 1                           | AWG 28 to 26<br>Insulation Dia. .039" (1.0 mm) to .049" (1.25 mm) |
| 2                           | AWG 24 to 22<br>Insulation Dia. .049" (1.25 mm) to .059" (1.5 mm) |
| Termination                 |                                                                   |
| 0                           | Wire crimp terminals required                                     |
| 1                           | PC Board Mount                                                    |

## Ordering Code Notes

1) Crimp contacts are available for the 566 series connectors. Contacts may be ordered separately for pre-wired or select position assembly.


| Part Number | Description    |
|-------------|----------------|
| 566-290-711 | Male contact   |
| 566-290-721 | Female contact |

2) For contact installation, removal and crimping tools, refer to page 7.


3) Insulator design prevents improper mating of individual plug and receptacle.

# 566 SERIES WATERPROOF CONNECTOR


Plug, Receptacle & Board Mount




566-002-000-210 (SML GA)  
566-002-000-220 (LRG GA)




566-002-000-110 (SML GA)  
566-002-000-120 (LRG GA)




566-002-420-101




566-003-000-210 (SML GA)  
566-003-000-220 (LRG GA)




566-003-000-110 (SML GA)  
566-003-000-120 (LRG GA)




566-003-420-101




566-005-000-210 (SML GA)  
566-005-000-220 (LRG GA)




566-005-000-110 (SML GA)  
566-005-000-120 (LRG GA)



566-005-420-101




566-009-000-210 (SML GA)  
566-009-000-220 (LRG GA)





## ASSEMBLY LAYOUT

- ① RETAINER
- ② WIRE SEAL
- ③ F TERMINAL
- ④ 566-NNN-000-210/220
- ⑤ HOUSING SEAL
- ⑥ M TERMINAL
- ⑦ 566-NNN-000-110/120
- ⑧ 566-NNN-000-101

566-009-420-101




| F TERMINAL | M TERMINAL |
|------------|------------|
|            |            |



# 570 SERIES WATERPROOF CONNECTOR

Plug, Receptacle & Board Mount



## FEATURES

- Fully waterproof connector
- Plastic latch provides both locking mechanism and polarity
- 5.8 mm Contact Spacing
- Plug and Receptacle in 2 or 3 Contact positions
- Board Mount Style available in 1, 2 or 3 contact positions
- Contact Termination Options include Crimp and P.C. Tail
- Tools Available for Contact Installation, Removal and Crimping
- Able to carry large current up to 10 A

## SPECIFICATIONS

- Insulator Material: PBT (UL94V-0)
- Contact Material: Brass / Tin plating
- Wire Housing Seal: Silicone Rubber
- Current Rating: 10 Amperes maximum
- Contact Resistance: 10m  $\Omega$  Maximum
- Insulator Withstanding Voltage: 1700 V AC rms at Sea Level
- Insulation Resistance: 1000M  $\Omega$  Minimum at 500 VDC
- Operating Temperature: -40 to +105 Degrees C
- Rated Voltage: 300 V
- Waterproof Grade 4
- For use with PC boards up to (.063") 1.6mm

## 570 SERIES ORDERING CODE

Example Part Number 570 - 003 - 000 - 1 0 0

Series \_\_\_\_\_  
Total Number of Contacts \_\_\_\_\_  
Contact Code \_\_\_\_\_  
Style \_\_\_\_\_  
Wire Diameter \_\_\_\_\_  
Termination \_\_\_\_\_

Series 570

Total Number of Contacts 001, 002 or 003

Contact Code <sup>1,2</sup>  
000 No Contacts Assembled  
420 Board Mount Contacts Installed

Style <sup>3</sup>  
1 Plug  
2 Receptacle

Wire Diameter <sup>4</sup>  
0 None installed; both contacts and water seals sold separately

Termination  
0 Wire crimp terminals required  
1 PC Board Mount

### Ordering Code Notes

1) Crimp contacts are available for the 570 series connectors. Contacts may be ordered separately for pre-wired or select position assembly.

| Part Number | Description                           |
|-------------|---------------------------------------|
| 570-290-711 | Male contact for smaller gauge wire   |
| 570-290-721 | Female contact for smaller gauge wire |
| 570-290-731 | Male contact for larger gauge wire    |
| 570-290-741 | Female contact for larger gauge wire  |

2) For contact installation, removal and crimping tools, refer to page 7.











3) Insulator design prevents improper mating of individual plug and receptacle.

4) Wire Seals are available as follows:

| Part Number | Colour | Insulation Dia             | Flange |
|-------------|--------|----------------------------|--------|
| 570-260-001 | Black  | .067" (1.7) to .075" (1.9) | No     |
| 570-260-002 | Blue   | .079" (2.0) to .102" (2.6) | No     |
| 570-260-003 | Blue   | .083" (2.1) to .106" (2.7) | Yes    |
| 570-260-004 | Brown  | .106" (2.7) to .122" (3.1) | Yes    |



# 570 SERIES WATERPROOF CONNECTOR

Plug, Receptacle & Board Mount




## ASSEMBLY LAYOUT

- ① WIRE SEAL
- ② F TERMINAL
- ③ 570-NNN-000-200
- ④ HOUSING SEAL
- ⑤ M TERMINAL
- ⑥ 570-NNN-000-100
- ⑦ 570-NNN-000-101



# 568 SERIES WATERPROOF CONNECTOR

## Plug and Receptacle



### FEATURES

- Fully waterproof connector
- Plastic latch provides locking mechanism
- Plug and Receptacle in 1 Contact position
- Tools Available for Contact Installation, Removal and Crimping
- Able to carry current up to 15 A

### SPECIFICATIONS

- Insulator Material: PBT (UL94V-0)
- Contact Material: Brass / Tin plating
- Wire Housing Seal: Silicone Rubber
- Current Rating: 15 Amperes maximum
- Contact Resistance: 10m  $\Omega$  Maximum
- Insulator Withstanding Voltage: 1700 V AC rms at Sea Level
- Insulation Resistance: 1000M  $\Omega$  Minimum at 500 VDC
- Operating Temperature: -40 to +105 Degrees C
- Rated Voltage: 300 V
- Waterproof Grade 4

### 568 SERIES ORDERING CODE

Example Part Number **568 - 001 - 000 - 100**

Series \_\_\_\_\_  
 Total Number of Contacts \_\_\_\_\_  
 Contact Code \_\_\_\_\_  
 Style \_\_\_\_\_

Series 568

Total Number of Contacts 001

Contact Code <sup>1,2</sup>  
 000 No Contacts Assembled

Style <sup>3</sup>  
 1 Plug  
 2 Receptacle

Wire Diameter <sup>4</sup>  
 0 None installed; both contacts and water seals sold separately

Termination  
 0 Wire crimp terminals required

### Ordering Code Notes

- 1) Crimp contacts are available for the 568 series connectors. Contacts may be ordered separately for pre-wired or select position assembly.


| Part Number | Description    |
|-------------|----------------|
| 570-290-711 | Male contact   |
| 570-290-721 | Female contact |
| 570-290-731 | Male contact   |
| 570-290-741 | Female contact |

- 2) For contact installation, removal and crimping tools, refer to page 7.

- 3) Insulator design prevents improper mating of individual plug and receptacle.

- 4) Wire Seals are available as follows:

| Part Number | Colour | Insulation Dia             | Flange |
|-------------|--------|----------------------------|--------|
| 570-260-001 | Black  | .067" (1.7) to .075" (1.9) | No     |
| 570-260-002 | Blue   | .079" (2.0) to .102" (2.6) | No     |
| 570-260-003 | Blue   | .083" (2.1) to .106" (2.7) | Yes    |
| 570-260-004 | Brown  | .106" (2.7) to .122" (3.1) | Yes    |



# Tools for 566, 568, 570 Series Waterproof Connectors

Crimp Tools, Withdrawal Tool, Automated Crimping Tool

## AUTOMATIC CONTACT CRIMP MACHINE

- Part Number 516-280-700 for base machine
- Applicators available to crimp all 566, 568 and 570 series contacts
- All required guards for operator safety
- Easy access for all setting changes
- Foot switch to initiate crimp cycle
- Mounts to any bench surface
- Quick change applicators allow for fast conversions from one contact type to another
- Requires 110V 50 / 60 Hz electrical supply



## CONTACT HAND CRIMP TOOL

- Manual hand crimp tool
- Uses contacts on carrier strip, crimps them and cuts the contacts from the carrier
- For 566 series, use crimper number 566-280-200
- For 568 and 570 series, use either 570-280-200 for smaller diameter wire and part



## RETAINER INSERTION TOOL

- Tool to insert retainer into connector housing to ensure water tight seal
- Required for all 566 series connectors
- Part number 566-280-250




## CONTACT EJECTION TOOL

- Tool to remove previously inserted contact from connector housing
- For use with 566 series, use tool part number 566-280-300
- For use with 568 and 570 series, use tool part number 570-280-300




## Plug and Receptacle



- UL Recognized
- .156 (3.96) Contact Spacing
- Plug and Receptacle in 3, 4, or 6 Contact Sizes
- Edacon Hermaphroditic Contact Mating Design
- Contact Termination Options include Crimp, P.C. Tail, Wire Hole, Wire Wrap and Taper Tail
- Tools Available for Contact Installation, Removal and Crimping
- These connectors are not waterproof.

- Insulator Material: White Nylon
- Contact Material: Phosphor Bronze Alloy CA-510
- Contact Plating: Gold over Nickel for Entire Contact
- Current Rating: 8.5 Amperes
- Contact Resistance: 10 Milliohms Maximum
- Dielectric Withstanding Voltage: 2000 V AC rms at Sea Level
- Insulation Resistance: 5000 Megohms Minimum
- Operating Temperature: -65 to +125 Degrees C
- Insertion and Withdrawal Force: 2 to 16 oz (0.56 to 4.45 N) per Contact Position



Series \_\_\_\_\_  
Total Number of Contacts \_\_\_\_\_  
Contact Code \_\_\_\_\_  
Style \_\_\_\_\_

|                          |                 |
|--------------------------|-----------------|
| Series                   | 556             |
| Total Number of Contacts | 003, 004 or 006 |


| Contact Code <sup>1,2</sup> | Description & Tail Size             | Tail Length "G" |
|-----------------------------|-------------------------------------|-----------------|
| 000                         | No Contacts Assembled               | -- --           |
| 500                         | Wire Hole .110 x .024 (2.79 x 0.61) | .245 (6.22)     |
| 501                         | Taper Tail                          | .245 (6.22)     |
| 520                         | P.C. Tail .025 x .024 (0.64 x 0.61) | .215 (5.46)     |
| 540                         | Wire Wrap .050 x .024 (1.27 x 0.61) | .600 (15.24)    |
| 541                         | Wire Wrap .026 x .024 (0.66 x 0.61) | .620 (15.75)    |
| 542                         | Wire Wrap .050 x .024 (1.27 x 0.61) | .790 (20.07)    |


| Style and Material <sup>3</sup> | Style                           |
|---------------------------------|---------------------------------|
| 101                             | Plug                            |
| 201                             | Receptacle with Panel Retention |

1) Crimp contacts are available for the 556 series connectors. Contacts may be ordered separately for pre-wired or select position assembly.

| Part Number | Description       |                                                                                       |
|-------------|-------------------|---------------------------------------------------------------------------------------|
| 516-290-500 | Wire Hole         |  |
| 516-290-501 | Taper Tail        |  |
| 516-290-520 | P.C. Tail         |  |
| 516-290-540 | Wire Wrap         |  |
| 516-290-541 | Wire Wrap         |  |
| 516-290-542 | Wire Wrap         |  |
| 516-290-590 | Crimp - Loose     |  |
| 516-290-591 | Crimp - 1800      |  |
|             | Contacts per reel |  |

- 2) For contact installation, removal and crimping tools, refer to page 112.
- 3) Insulator design prevents improper mating of individual plug and receptacle.





PRINTED IN CANADA 10M98A



*an EDACOM company*

**40 TIFFIELD ROAD  
SCARBOROUGH, ONTARIO, CANADA M1V 5B6**

Telephone: (416) 754-3322 Facsimile: (416) 754-3299  
E-mail: [edac@edac.net](mailto:edac@edac.net) Web Page: <http://www.edac.net>