




- Common Mode Choke for EMI Reduction
- Add "-RC" after part number for RoHS Compliant


Electrical Parameters @ 25° C

OCL (μH Min.)	Interwinding Capacitance (pF Max.)	Leakage Inductance (μH Max.)	DCR (Ω Max.)
36	15	0.3	0.4

Package




Typical Common Mode Impedance (Ω)



Notes :	EPA3571G	EPA3571G-RC
1. Lead Finish	SnPb	Matte Tin
2. Peak Temperature Rating	225°C	260°C
3. Moisture Sensitive Levels	MSL = 3 (168 Hours, $\leq 30^\circ\text{C}/60\%\text{RH}$)	MSL = 4 (72 Hours, $\leq 30^\circ\text{C}/60\%\text{RH}$)
4. Weight	TBD grams	TBD grams
5. Packaging Information (Tube)	TBD pieces/tube	TBD pieces/tube
(Tape & Reel)	TBD pieces/13" reel (*EPA3571GTR)	TBD pieces/13" reel (*EPA3571GTR-RC)

Schematic



Unless Otherwise Specified Dimensions are in Inches /mm $\pm .010 / .25$