



PRODUCT NUMBER	SERIES NAME	PITCH
20020010-CXXXXXXLF	02-350	3.50 mm







N = Number of poles
 Dim A = $N \times 3.5$ [.138]
 Dim B = $(N-1) \times 3.5$ [.138]

POLES	TOLERANCE
2-6p	± 0.15 [.006]
7-12p	± 0.20 [.008]
13-18p	± 0.25 [.010]
19-24p	± 0.30 [.012]



mat'l. code	surface ASME Y14.5 ✓	tolerance ASME Y14.5	projection MM [INCH]	product family TERMINAL BLOCK
ltr	ecn no	dr	date	title
F				TERMINAL BLOCK PLUGGABLE PLUG, BACK SIDE HOOK
				dwg no
				20020010
				sheet 2 of 5
				size
				A4
				type
				CUSTOMER Drawing
sheet index	revision sheet			

PRODUCT NUMBER	SERIES NAME	PITCH
20020010-DXXXXXXLF	02-381	3.81 mm







2p to 6p with wedge, above 7p
without wedge (including 7p)

N = Number of poles
Dim A = $N \times 3.81$ [.150]
Dim B = $(N-1) \times 3.81$ [.150]

POLES	TOLERANCE
2-6p	± 0.15 [.006]
7-12p	± 0.20 [.008]
13-18p	± 0.25 [.010]
19-24p	± 0.30 [.012]

mat'l. code				surface ASME Y14.5 ✓	tolerance ASME Y14.5	projection 	product family TERMINAL BLOCK
ltr	ecn	no	dr	date			title
F							TERMINAL BLOCK
				angles	$X \pm 0.5$	MM [INCH]	PLUGGABLE PLUG, BACK SIDE HOOK
				linear	$X.X \pm 0.3$	scale	dwg no
				$X \pm 1^\circ$	$X.XX \pm 0.1$		sheet 3 of 5 size
			dr	JASON HSU	120909		20020010
			enr	JASON HSU	120909		A4
			chr	GARY HSIEH	120909		
			appd	JOSEPH HSIA	120909		
sheet	revision						type
index	sheet						CUSTOMER Drawing


PRODUCT NUMBER	SERIES NAME	PITCH
20020010-GXXXXXXLF	02-500	5.00 mm



SECTION P-P

N = Number of poles
 Dim A = $N \times 5.0$ [.197]
 Dim B = $(N-1) \times 5.0$ [.197]




POLES	TOLERANCE
2-6p	± 0.15 [.006]
7-12p	± 0.25 [.010]
13-18p	± 0.30 [.012]
19-24p	± 0.40 [.016]



mat'l. code				surface ASME Y14.5 ✓	tolerance ASME Y14.5	projection MM [INCH]	product family TERMINAL BLOCK
ltr	ecn no	dr	date	tolerances unless otherwise specified			title
F				angles	X.±0.5		TERMINAL BLOCK
				linear	X.X±0.3		PLUGGABLE PLUG, BACK SIDE HOOK
				X°±1°	X.XX±0.1	scale	dwg no
		dr	JASON HSU	120909			sheet 4 of 5
		enr	JASON HSU	120909			20020010
		chr	GARY HSIEH	120909			A4
		appd	JOSEPH HSIA	120909			type
sheet index	revision sheet						CUSTOMER Drawing




PRODUCT NUMBER	SERIES NAME	PITCH
20020010-HXXXXXXLF	02-508	5.08 mm




N = Number of poles
Dim A = $N \times 5.08$ [.200]
Dim B = $(N-1) \times 5.08$ [.200]

POLES	TOLERANCE
2-6p	± 0.15 [.006]
7-12p	± 0.25 [.010]
13-18p	± 0.30 [.012]
19-24p	± 0.40 [.016]



SECTION P-P



mat'l. code				surface ASME Y14.5 ✓	tolerance ASME Y14.5	projection MM [INCH]	product family TERMINAL BLOCK	
ltr	ecn	no	dr	date			title	
F							TERMINAL BLOCK	
				angles	linear		PLUGGABLE PLUG, BACK SIDE HOOK	
				X°±1°	X.XX±0.1	scale		
			dr	JASON HSU	120909	FCI	dwg no	
			enr	JASON HSU	120909		sheet 5 of 5 size	
			chr	GARY HSIEH	120909		20020010	
			appd	JOSEPH HSIA	120909		A4	
sheet index		revision sheet					type	
							CUSTOMER Drawing	