

THIS DRAWING IS UNPUBLISHED.  
DIFFUSION RESTREINTE AMPRELEASED FOR PUBLICATION  
LIBRE A LA DIFFUSION


2007

© COPYRIGHT 2007

BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.  
Tous droits réservésLOC  
FDIST  
00

REVISIONS



| P | LTR<br>REV | DESCRIPTION<br>MODIFICATIONS | DATE      | DWN<br>DESS. | APVD<br>APP. |
|---|------------|------------------------------|-----------|--------------|--------------|
|   | C          | MOLD DUPLICATION             | 10JAN2007 | LCi          | JDr          |
|   | D          | CHANGE LOGO TE               | 29SEP2010 | PFs          | JDr          |
|   |            |                              |           |              |              |
|   |            |                              |           |              |              |



| MATING FORCES SPECIFICATIONS |                            | TERMINAL HOUSING/TAB HOUSING |
|------------------------------|----------------------------|------------------------------|
| RECEPTACLE TERMINAL CuZn15   | RECEPTACLE TERMINAL CuNiSi |                              |
| 1544141                      | 1544128                    |                              |
| INSERTION FORCE < 60N        | INSERTION FORCE < 70N      |                              |

SECTION A-A

SECTION D-D

INDICE DE REVISION PIECE  
PART INDEX

RECEPTACLE TERMINAL 8MM PN

| TE        | PSA           | RENAULT      |
|-----------|---------------|--------------|
| 1544455-1 | 96 107 592 80 | -            |
| 1544141-1 | 96 107 593 80 | 7701 997 034 |
| 1544129-1 | -             | 7703 497 311 |
| 1544142-1 | -             | 7701 997 035 |
| 1544128-1 | -             | 7703 497 312 |

CE PLAN EST UN EXTRAIT DU  
PLAN DE DEFINITION. ON FERA  
REFERENCE AU PLAN DE  
DEFINITION POUR TOUT LITIGETHIS DRAWING IS EXTRACT FROM  
PRODUCT DRAWING, IN CASE  
PROBLEM, DRAWING REFERENCE IS  
PRODUCT DRAWING

## NOTES :

FI CLIP SANS VS < 30 N / TERMINAL INSERTION FORCE WITHOUT SECONDARY LOCK < 30N  
 FE CLIP SANS VS > 80 N / TERMINAL EXTRACTION FORCE WITHOUT SECONDARY LOCK > 80N  
 FE CLIP AVEC VS > 100 N / TERMINAL EXTRACTION FORCE WITH SECONDARY LOCK > 100N

| TE PN     | PSA PN        | RENAULT PN   | COLOR           | CODING |
|-----------|---------------|--------------|-----------------|--------|
| 1544458-1 | 96 107 597 80 | 7703 297 716 | NOIR<br>BLACK   |        |
| 1544458-2 | 96 107 598 80 | 7703 297 715 | GRIS<br>GREY    |        |
| 1544458-3 | 96 107 599 80 |              | MARRON<br>BROWN |        |
| 1544458-4 | 96 107 600 80 |              | BLANC<br>WHITE  |        |
| 1544458-5 | 96 107 601 80 |              | BLEU<br>BLUE    |        |

|                                                                                                                                                                                                |                                                                                                    |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION<br>IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION<br>SHOULD BE CONTACTED FOR THE LATEST REVISION. |                                                                                                    |
| CE PLAN EST UN DOCUMENT CONTRÔLÉ PAR AMP INCORPORATED.<br>IL EST SUSCEPTIBLE D'ÊTRE REVISÉ. CONTACTER LE SERVICE<br>TECHNIQUE D'AMP DE FRANCE POUR OBTENIR LA DERNIÈRE RÉVISION.               |                                                                                                    |
| DIMENSIONS:                                                                                                                                                                                    | TOLERANCES UNLESS<br>OTHERWISE SPECIFIED:<br>TOLERANCES NON SPECIFIÉES<br>(SUIV. NB DE DECIMALES): |
| mm                                                                                                                                                                                             | 1. P/LC/DEC: ±<br>2. P/LC/DEC: ±<br>3. P/LC/DEC: ±<br>4. P/LC/DEC: ±<br>ANGLES ±                   |
| MATERIAL<br>MATIERE                                                                                                                                                                            | PA 66/6                                                                                            |
| FINISH<br>FINITION                                                                                                                                                                             | -                                                                                                  |

|                                       |              |                                                                                                |                  |
|---------------------------------------|--------------|------------------------------------------------------------------------------------------------|------------------|
| DWN/DESSINE<br>L. CORONELLI           | 10JAN2007    | Tyco Electronics<br>Tyco Electronics France SAS<br>517, Avenue de la Boisse, 73 Chambéry       |                  |
| CHK/VERIFIE<br>P. FLORES              | 10JAN2007    |                                                                                                |                  |
| APVD/APPROUVE<br>J. DAHER             | 10JAN2007    | NAME<br>TITRE                                                                                  |                  |
| PRODUCT SPEC<br>SPEC. PRODUIT         |              | PORTE CLIP 2 VOIES 8mm A VS<br>2 W 8mm POSITIVE LOCK RECEPTACLE<br>HOUSING WITH SECONDARY LOCK |                  |
| APPLICATION SPEC<br>SPEC. APPLICATION |              | SIZE<br>FORMAT                                                                                 | CAGE CODE        |
| WEIGHT<br>MASSE APPROX.               | 3,3 g        | A3                                                                                             | 00779            |
| CUSTOMER DRAWING                      | /PLAN CLIENT | UNIQUEMENT<br>POUR REFERENCE                                                                   | SCALE<br>ECHELLE |
|                                       |              | SHEET<br>FEUILLE                                                                               | OF<br>DE         |
|                                       |              | REV                                                                                            | D                |