




BRASS

Finish: Zinc qq-z-325, type II, cl 3-Clear Chromate

LENGTH	FOR #4 SCREW A: .114 (2.9) B: 1/4 (6.4)	FOR #6 SCREW A: .140 (3.5) B: 1/4 (6.4)	FOR #8 SCREW A: .166 (4.2) B: 1/4 (6.4)	FOR #10 SCREW A: .192 (4.9) B: 3/8 (9.5)
1/4 (6.4)	BRSS4-2	BRSS6-2	BRSS8-2	BRSS10-2
3/8 (9.5)	BRSS4-3	BRSS6-3	BRSS8-3	BRSS10-3
1/2 (12.7)	BRSS4-4	BRSS6-4	BRSS8-4	BRSS10-4
5/8 (15.9)	BRSS4-5	BRSS6-5	BRSS8-5	BRSS10-5
3/4 (19.1)	BRSS4-6	BRSS6-6	BRSS8-6	BRSS10-6
1 (25.4)	BRSS4-8	BRSS6-8	BRSS8-8	BRSS10-8

ALUMINUM

Finish: Iridite MIL-C-5541 - Gold #14

LENGTH	FOR #4 SCREW A: .114 (2.9) B: 1/4 (6.4)	FOR #6 SCREW A: .140 (3.5) B: 1/4 (6.4)	FOR #8 SCREW A: .166 (4.2) B: 1/4 (6.4)	FOR #10 SCREW A: .192 (4.9) B: 3/8 (9.5)
1/4 (6.4)	ALSS4-2	ALSS6-2	ALSS8-2	ALSS10-2
3/8 (9.5)	ALSS4-3	ALSS6-3	ALSS8-3	ALSS10-3
1/2 (12.7)	ALSS4-4	ALSS6-4	ALSS8-4	ALSS10-4
5/8 (15.9)	ALSS4-5	ALSS6-5	ALSS8-5	ALSS10-5
3/4 (19.1)	ALSS4-6	ALSS6-6	ALSS8-6	ALSS10-6
1 (25.4)	ALSS4-8	ALSS6-8	ALSS8-8	ALSS10-8

A	CHANGED FILE NO. AND TITLE BLOCK	SM 03.22.02
REV	DESCRIPTION	ENGR DATE

TITLE: ROUND SPACERS					DWG IN IN (MM)	
TOLERANCES UNLESS NOTED .XX= ± 0.010 .XXX= ± 0.005 FRAC= $\pm 1/64$ ANG= $\pm 1^\circ$	FILE # ALSS-BRSS	DWN: J.B.	APP:	FINAL		
	MAT'L: SEE TABLE	DT: 09-31-95	DT:	PART #		
	RE: RICHCO, INC.	RICHCO INC. PO BOX 804238, CHICAGO, 60680 (773) 539-4060		SEE TABLE		
				PRINT TYPE CA		