




- 1 0.38μm[.000015] MIN GOLD ON MATING AREA,
1.27μm[.000050] MIN BRIGHT TIN-LEAD ON CRIMP AREA, BOTH OVER
1.27μm[.000050] MIN NICKEL.
- 2 2.54μm[.000100] MIN BRIGHT TIN-LEAD, OVER
1.27μm[.000050] MIN NICKEL.
- 3 GOLD FLASH ON CRIMP AREA,
2.54μm[.000100] MIN TIN ON MATING AREA, BOTH OVER
1.27μm[.000050] MIN NICKEL.
- 4 0.38μm[.000015] MIN GOLD ON MATING AREA,
GOLD FLASH ON CRIMP AREA, BOTH OVER
1.27μm[.000050] MIN NICKEL.
- 5 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 6 GOLD PLATING MAY OR MAY NOT BE PRESENT ON THE BOTTOM OF THE CRIMP BARREL

5 OBSOLETE	4	487923-5
3	6	487923-4
5 OBSOLETE	1	487923-3
	2	487923-1
FINISH		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.OBERMAN 3-7-90		 TE Connectivity						
		CHK R.STONE 3-8-90								
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME CONTACT, SOLDER TAB, .050 C/L -						
	0 PLC ± -		APVD -							
	1 PLC ± -		PRODUCT SPEC -							
	2 PLC ± 0.13[.005]		APPLICATION SPEC -							
	3 PLC ± -		SIZE							
4 PLC ± -		ANGLES ± -		CAGE CODE	DRAWING NO					
MATERIAL		FINISH		RESTRICTED TO						
PHOSPHOR BRONZE		SEE TABLE		WEIGHT -	A2	00779	C=487923	-		
CUSTOMER DRAWING				SCALE		10:1	SHEET	1 of 1	REV	D1