

STANDARD SUBMINATURE TVS ARRAYS

APPLICATIONS

- ✓ RS-232, RS-422 & RS-423
- ✓ Cellular Phones
- ✓ Control & Monitoring Systems
- ✓ Portable Electronics
- ✓ Wireless Bus Protection

IEC COMPATIBILITY (EN61000-4)


- ✓ 61000-4-2 (ESD): Air - 15kV, Contact - 8kV
- ✓ 61000-4-4 (EFT): 40A - 5/50ns
- ✓ 61000-4-5 (Surge): 12A, 8/20 μ s - Level 1(Line-Gnd) & Level 2(Line-Line)

FEATURES



- ✓ ESD Protection > 40 kilovolts
- ✓ 500 Watts Peak Pulse Power per Line (td=8/20 μ s)
- ✓ Low Clamping Voltage
- ✓ Available in Multiple Voltage Types Ranging from 3V to 36V

MECHANICAL CHARACTERISTICS

- ✓ Molded JEDEC SOT-23
- ✓ Weight 0.6 grams (Approximate)
- ✓ Flammability Rating UL 94V-0
- ✓ 8mm Tape and Reel Per EIA Standard 481-1-A
- ✓ Device Marking Code & Logo
- ✓ Pin One Defined By DOT on Top of Package



CIRCUIT DIAGRAMS



DEVICE CHARACTERISTICS

MAXIMUM RATINGS @ 25°C Unless Otherwise Specified			
PARAMETER	SYMBOL	VALUE	UNITS
Peak Pulse Power ($t_p = 8/20\mu s$) - See Figure 1	P_{PP}	500	Watts
Operating Temperature	T_J	-55°C to 150°C	°C
Storage Temperature	T_{STG}	-55°C to 150°C	°C
Forward Voltage @ 100mA, 300μs - Square Wave (Note 1)	V_F	1.5	Volts


Note 1: Applies to unidirectional devices only.

ELECTRICAL CHARACTERISTICS PER LINE @ 25°C Unless Otherwise Specified							
PART NUMBER (See Note 1)	DEVICE MARKING	RATED STAND-OFF VOLTAGE V_{WM} VOLTS	MINIMUM BREAKDOWN VOLTAGE @ 1mA $V_{(BR)}$ VOLTS	MAXIMUM CLAMPING VOLTAGE (See Fig. 2) @ $I_P = 1A$ V_C VOLTS	MAXIMUM CLAMPING VOLTAGE (See Fig. 2) @ 8/20μs $V_C @ I_{PP}$	MAXIMUM LEAKAGE CURRENT @ V_{WM} I_D μA	TYPICAL CAPACITANCE 0V @ 1 MHz C pF
PSOT03	03	3.3	4.0	6.5	10.9V @ 43.0A	125	500
PSOT03C	03C	3.3	4.5	7.0	10.9V @ 43.0A	125	300
PSOT05	05	5.0	6.0	9.8	13.5V @ 42.0A	20	350
PSOT05C	05C	5.0	6.0	9.8	13.5V @ 42.0A	20	210
PSOT08	08	8.0	8.5	13.4	16.9V @ 34.0A	10	250
PSOT08C	08C	8.0	8.5	13.4	16.9V @ 34.0A	10	150
PSOT12	12	12.0	13.3	19.0	25.9V @ 21.0A	2	150
PSOT12C	12C	12.0	13.3	19.0	25.9V @ 21.0A	2	90
PSOT15	15	15.0	16.7	24.0	30.0V @ 17.0A	1	100
PSOT15C	15C	15.0	16.7	24.0	30.0V @ 17.0A	1	60
PSOT24	24	24.0	26.7	43.0	49.0V @ 12.0A	1	88
PSOT24C	24C	24.0	26.7	43.0	49.0V @ 12.0A	1	63
PSOT36	36	36.0	40.0	51.0	76.8V @ 9.0A	1	80
PSOT36C	36C	36.0	40.0	51.0	76.8V @ 9.0A	1	60


Note 1: Part numbers with an additional "C" suffix are bidirectional devices, i.e., PSOT05C.

GRAPHS


**FIGURE 1
PEAK PULSE POWER VS PULSE TIME**



**FIGURE 2
PULSE WAVE FORM**





**FIGURE 3
POWER DERATING CURVE**



PSOT03 thru PSOT36C

PACKAGE OUTLINE & DIMENSIONS

PACKAGE OUTLINE 	SOT-23  <table><tr><th colspan="5">PACKAGE DIMENSIONS</th></tr><tr><th rowspan="2">DIM</th><th colspan="2">MILLIMETERS</th><th colspan="2">INCHES</th></tr><tr><th>MIN</th><th>MAX</th><th>MIN</th><th>MAX</th></tr><tr><td>A</td><td>2.80</td><td>3.04</td><td>0.1102</td><td>0.1197</td></tr><tr><td>B</td><td>1.20</td><td>1.40</td><td>0.0472</td><td>0.0551</td></tr><tr><td>C</td><td>0.89</td><td>1.11</td><td>0.0350</td><td>0.0440</td></tr><tr><td>D</td><td>0.37</td><td>0.50</td><td>0.0150</td><td>0.0200</td></tr><tr><td>G</td><td>1.78</td><td>2.04</td><td>0.0701</td><td>0.0807</td></tr><tr><td>H</td><td>0.013</td><td>0.100</td><td>0.0005</td><td>0.0040</td></tr><tr><td>J</td><td>0.085</td><td>0.177</td><td>0.0034</td><td>0.0070</td></tr><tr><td>K</td><td>0.45</td><td>0.60</td><td>0.0180</td><td>0.0236</td></tr><tr><td>L</td><td>0.89</td><td>1.02</td><td>0.0350</td><td>0.0401</td></tr><tr><td>S</td><td>2.10</td><td>2.50</td><td>0.0830</td><td>0.0984</td></tr><tr><td>V</td><td>0.45</td><td>0.60</td><td>0.0177</td><td>0.0236</td></tr></table>	PACKAGE DIMENSIONS					DIM	MILLIMETERS		INCHES		MIN	MAX	MIN	MAX	A	2.80	3.04	0.1102	0.1197	B	1.20	1.40	0.0472	0.0551	C	0.89	1.11	0.0350	0.0440	D	0.37	0.50	0.0150	0.0200	G	1.78	2.04	0.0701	0.0807	H	0.013	0.100	0.0005	0.0040	J	0.085	0.177	0.0034	0.0070	K	0.45	0.60	0.0180	0.0236	L	0.89	1.02	0.0350	0.0401	S	2.10	2.50	0.0830	0.0984	V	0.45	0.60	0.0177	0.0236
PACKAGE DIMENSIONS																																																																						
DIM	MILLIMETERS		INCHES																																																																			
	MIN	MAX	MIN	MAX																																																																		
A	2.80	3.04	0.1102	0.1197																																																																		
B	1.20	1.40	0.0472	0.0551																																																																		
C	0.89	1.11	0.0350	0.0440																																																																		
D	0.37	0.50	0.0150	0.0200																																																																		
G	1.78	2.04	0.0701	0.0807																																																																		
H	0.013	0.100	0.0005	0.0040																																																																		
J	0.085	0.177	0.0034	0.0070																																																																		
K	0.45	0.60	0.0180	0.0236																																																																		
L	0.89	1.02	0.0350	0.0401																																																																		
S	2.10	2.50	0.0830	0.0984																																																																		
V	0.45	0.60	0.0177	0.0236																																																																		
MOUNTING PAD 	NOTES: 1. Dimensioning and tolerances per ANSI Y14.5M, 1985. 2. Controlling Dimension: Inches 3. Pin 3 is the cathode (Unidirectional Only). 4. Dimensions are exclusive of mold flash and metal burrs. 06012 Rev 1 - 11/01																																																																					

TAPE & REEL PACKAGING:

Surface mount product is taped and reeled in accordance with EIA-481, reel quantities and sizes are as follows:

7 Inch Reel - 3,000 pieces per reel; 13 Inch Reel - Not Available

ProTek Devices

2929 South Fair Lane, Tempe, AZ 85282

Tel: 602-431-8101 Fax: 602-431-2288

E-Mail: sales@protekdevices.com

Web Site: www.protekdevices.com

COPYRIGHT © ProTek Devices 2001

SPECIFICATIONS: ProTek reserves the right to change the electrical and or mechanical characteristics described herein without notice (except JEDEC).

DESIGN CHANGES: ProTek reserves the right to discontinue product lines without notice, and that the final judgement concerning selection and specifications is the buyer's and that in furnishing engineering and technical assistance, ProTek assumes no responsibility with respect to the selection or specifications of such products.