


LOC		DIST		REVISIONS				
AF	50	P	F	ZONE	LTR	DESCRIPTION	DATE	APPD
					J1	REVISE PER ECR-12-022060	26DEC12	CX/LL

- 1 CONTINUOUS STRIP ON REELS WITH TERMINALS LOCATED ON 5.59±0.08 [.220±.003] CENTERS. SLOTS ACCEPTS EITHER A SINGLE OR DOUBLE MAGNET WIRE OF THE SAME SIZE AND TYPE COPPER RANGE: 0.32-0.51mm [#28-#24] AWG
- 2 POKE-IN ACCEPTS A 0.5-0.8mm² [#20-#18] AWG SOLID OR FUSED STRANDED LEAD WIRE.
- 3 AFTER INSERTION INTO PLASTIC HOLDER TAB PORTION MUST BE BENT OVER 45° TO 90° OR POTTED-IN TO PREVENT PULL-OUT WHEN MATING RECEPTACLE IS DISCONNECTED.
- 4



THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON :		DR	9/MAR/95 R.GRZYBOWSKI	NAME AMP AMP Incorporated Harrisburg, PA 17105-3608
2 PLC DEC ± 0.25 [.010]		CHK	16/MAR/95 M.S.FEHER	
3 PLC DEC ± -		APPD	16/MAR/95 NELSON E. NEFF	
ANGLES ± -		APPD	16/MAR/95 TERRY L. SHUTTER	
MATERIAL		PRODUCT SPEC	108-2012	TERMINAL, TAB, POKE-IN / 2.79 [.110] FASTON,™ COMBINATION, MAG-MATE™
4M PRE-MILLED BRASS		APPLICATION SPEC		
FINISH 0.002032 [.000080] MIN TIN PLATE		SIZE	CAGE CODE 00779	
		WEIGHT	SCALE 10:1	DRAWING NO 63062
				SHEET 1 OF 1