




LOC	DIST	REVISIONS					
CE	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			B	ECR-06-029231	23MAR2007	EJH	SB



PROTECTIVE COVER




9.9
[.39]
MAX



24.6
[.97]
MAX

28.7
[1.13]
MAX

PROTECTIVE CAP



NOMINAL ATTENUATION VALUE (dB)	PART NUMBER
1	5209948-1
2	5209948-2
3	5209948-3
4	5209948-4
5	5209948-5
6	5209948-6
7	5209948-7
8	5209948-8
9	5209948-9
10	1-5209948-0
12	1-5209948-2
13	1-5209948-3
14	1-5209948-4
15	1-5209948-5
18	1-5209948-8
20	2-5209948-0
25	2-5209948-5

PERFORMANCE REQUIREMENTS:
OPERATING WAVELENGTH : 1310/1550nm ±25nm
REFLECTANCE : ≤ -55dB
OPERATING TEMPERATURE : -40°C TO 75°C
ATTENUATION TOLERANCE, AMBIENT :
FOR ATTENUATORS ≥5dB: ±10% OF NOMINAL ATTENUATION VALUE
FOR ATTENUATORS <5dB: ±.50dB
MEASURED WITH REFERENCE QUALITY LAUNCH LEADS

△ TYCO LOGO, ATTENUATION VALUE, PART NUMBER,
AND SERIAL NUMBER ARE PRINTED ON THE LABEL

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN E. HOPKINS CHK E. HOPKINS APVD S. BUCHTER	19DEC2005 19DEC2005 19DEC2005	tyco Electronics Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS: mm[INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME ATTENUATOR, OPTICAL, BUILDOUT FC/UPC, SM, DUAL WINDOW	
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±2 FINISH		PRODUCT SPEC - APPLICATION SPEC - WEIGHT -	
		MATERIAL -		SIZE A2	
CUSTOMER DRAWING		SCALE 5:1		SHEET 1 OF 1	
				REV B	